



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YS4CLBOX #4 STR Cu Butt Splice

Burndy LLC

Catalog Number	YS4CLBOX
Manufacturer	Burndy LLC
Description	4 Awg Cu, Standard Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Gray Color Code, 8 or 346 Die Index.
Weight per unit	0.0200 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	8
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	GRAY
Finish	Tin-Plated

Descriptions

Description	#4 STR CU BUTT SPLICE
extra long description	BUR YS4CLBOX 4 STR. CU. BUTT SPLICE
Long Description	4 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, GRAY Color Code, 8 or 346 Die Index.
Product Type	Splice
Special Features	Features: Standard Barrel Length, Ideal For Limited Space Applications While Providing Ample Barrel Length For Proper Crimp, Four (4) Center Conductor Stops, Provides A Center Wire Stop For Proper Conductor Insertion, Conductor Type: Commercial Stranded Copper, Die Index: 8 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: Y1MRTC, Y2MR Tool, (2), MD7-34R Tool, W4CVT Die, (1), MD6, OUR840 Tool, X4CRT Die, (1), Y35, Y39, Y750, Y46 Tool, U4CRT Die, (1), Color Code: Gray, Dieless To

Manufacturer Information

Brand	BURNDY
GTIN	00781810555507
Manufacturers Part Number	YS4CLBOX
UPC	781810555507

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YS-L, Standard Barrel



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	50
Weight Per each	0.02

Uses, Certifications, and Standards

Application	Wire Splice
standard	UL 486A-486B