



Compact Fluorescent Lamps

		Nominal Length Order	Case Qty	Rated Life Hours	Lumens Initial Mean	Color Temp. K	Min. Start Temp. Power (°F) Factor THD	Additional Information	Warning Notices	Footnotes				
Base	Watts	in. Code Description												
SELF-BALLASTED LAMPS (CONTINUED)														
SPIRAL® (CONTINUED)														
	Med	26 5.2	00262 FLE26HT3/2/SW/3PK	3	120	8000	1750	1400	2700	82	5 0.6 120	 T3 Spiral®, Carded 3 Pack	153	1,7,8,9,10
			16254 FLE26HT3/2/6H/4PK	3	120	6000	1750	1400	2700	82	5 0.6 120	 6000 Hr Life, T3 Spiral®, Boxed Consumer 4 Pack	153	1,7,8,9,10
			21845 FLE26HT3/2/10PK	10	120	8000	1700	1365	2700	82	5 0.6 120	 T3 Spiral®, Consumer 10 Pack	153	1,7,8,9,10
			25195 FLE26HT3/2/841	10	120	8000	1750	1400	4100	82	5 0.6 120	 T3 Spiral®, Boxed	153	1,7,8,9,10
			85397 FLE26HT3/2/D/2PK	3	120	8000	1600	1315	6500	82	5 0.6 120	 T3 Spiral®, Carded Twin Pack	153	1,7,8,9,10
			80890 FLE26HT3/2/XL	10	120	12000	1700	1360	2700	82	5 0.6 120	 T3 Spiral®, Boxed	153	1,7,8,9,10
			47446 FLE26HT3/2/XL/CD	12	120	12000	1700	1360	2700	82	5 0.6 120	 T3 Spiral®, Carded Single Pack	153	1,7,8,9,10
			49685 FLE26HT3/2/XL2PK	3	120	12000	1700	1360	2700	82	5 0.6 120	 T3 Spiral®, Carded Twin Pack	153	1,7,8,9,10
	29 6.3	81514 FLE29HLX/2/XL/827	10	120	12000	2200	1760	2700	82	5 0.6	 T4 Spiral®, Boxed	153	1,7,8,9,10	
		47459 FLE29HLX/2/XL/CD	12	120	12000	2200	1760	2700	82	5 0.6	 T4 Spiral®, Carded Single Pack	153	1,7,8,9,10	
		81515 FLE29HLX/2D3/827	10	120	10000	600	480	2700	82	5 0.6	 T4 Spiral®, Boxed, 3-way	155	1,7,8,9,10	
						1600	1280							
			47448 FLE29HLX/2/D3/CD	12	120	10000	600	480	2700	82	5 0.6	 T3 Spiral®, Carded Single Pack, 3-way	155	1,7,8,9,10
						2200	1760							
	42 6.4	80891 FLE42HLX/2/XL	10	120	12000	2700	2160	2700	82	5 0.6 170	 T4 Spiral®, Boxed	153	1,7,8,9,10	
		47452 FLE42HLX/2/XL/CD	12	120	12000	2700	2160	2700	82	5 0.6 170	 T4 Spiral®, Carded Single Pack	153	1,7,8,9,10	
		16107 FLE42HLX/VT/827	10	120	10000	2650	2275	2700	82	14 0.6 170	 BASE DOWN OPERATION ONLY, T4 Spiral®, Boxed	154	1,7,10,15	
BIAX®														
	Med	12 4.4	20702 FLE12TT3/827	10	120	15000	600	480	2700	82	5 0.6 120	 T3 Triple Biax®, Boxed	153	1,7,8,9,10,12
		14 5.9	49884 FLE14TBX/2/SW/CD	12	120	8000	850	685	2700	82	5 0.6 120	 Triple Biax®, Carded Single Pack	153	1,7,8,9,10
		15 4.9	12004 FLE15TT3/827	10	120	15000	900	720	2700	82	5 0.6 145	 T3 Triple Biax®, Boxed	153	1,7,8,9,10,12
			12005 FLE15TT3/SW/CD	3	120	15000	900	720	2700	82	5 0.6 145	 T3 Triple Biax®, Carded Single Pack	153	1,7,8,9,10,12
		20 5.5	12008 FLE20TT3/827	10	120	15000	1200	960	2700	82	5 0.6 130	 T3 Triple Biax®, Boxed	153	1,7,8,9,10,12
			12009 FLE20TT3/SW/CD	3	120	15000	1200	960	2700	82	5 0.6 130	 T3 Triple Biax®, Carded Single Pack	153	1,7,8,9,10,12
		6.9	49885 FLE20TBX/2/SW/CD	12	120	8000	1200	965	2700	82	5 0.6 120	 Triple Biax®, Carded Single Pack	153	1,7,8,9,10
		24 5.6	23669 FLE24QBX/A/827	6	120	12000	1520	1290	2700	82	-9 0.6 170	 New Quad Biax® design, even shorter MOL, boxed	153	1,7,8,9,10,12
		27 6.9	49887 FLE27QBX/2/SW/CD	12	120	6000	1700	1365	2700	82	5 0.6 130	 Quad Biax®, Carded Single Pack	153	1,7,8,9,10
		28 5.9	40351 FLE28QBX/LL/CD	3	120	12000	1750	1485	2700	82	-9 0.6 170	 Soft White, Quad Biax®, Carded, Standard Shell Ballast	153	1,7,8,9,10,12
			46270 FLE28QBX/A/827	6	120	12000	1750	1485	2700	82	-9 0.6 170	 Shorter MOL	153	1,7,8,9,10,12
	29 6.3	41457 FLE29QBX/DV/827	6	120	10000	1750	1500	2700	82	-9 0.6 170	 Dimming, Standard Shell Ballast	156	1,7,8,9,12,14	
		45599 FLE29QBX/DV/827/CD	3	120	10000	1750	1500	2700	82	-9 0.6 170	 Dimming, Carded, Standard Shell Ballast	156	1,7,8,9,12,14	
REFLECTORS														
	Med	11 4.7	20704 FLE11/R20	10	120	10000	370	296	2700	82	5 0.6 120	 Soft White, R20 Glass Reflector	157	1,8,9,10,12
			80892 FLE11/2/R20XL	10	120	10000	400	320	2700	82	5 0.6 120	 Soft White, R20 Glass Reflector, Boxed	157	1,8,9,10,12
			47477 FLE11/2/R20XL/CD	12	120	10000	400	320	2700	82	5 0.6 120	 Soft White, R20 Glass Reflector, Carded Single Pack	157	1,8,9,10,12
	15 5.5	49917 FLE15/A2/R30	6	120	10000	550	445	2700	82	-22 0.6 170	 Soft White, R30 Glass Reflector	157	1,8,9,10,12	
	5.4	20708 FLE15/2/R30/SWCD	3	120	8000	720	580	2700	82	5 0.6 120	 Soft White, R30 Glass Reflector, Carded Single Pack	158	1,8,9,10,12	
	5.5	80893 FLE15/2/R30XL	10	120	10000	750	600	2700	82	5 0.6 120	 Soft White, R30 Glass Reflector, Boxed	157	1,8,9,10,12	
		47478 FLE15/2/R30XL/CD	12	120	10000	750	600	2700	82	5 0.6 120	 Soft White, R30 Glass Reflector, Carded Single Pack	157	1,8,9,10,12	
	5.6	21709 FLE15/2/DV/R30	6	120	6000	720	580	2700	82	5 0.6 110	 Dimming, Soft White, R30 Glass Reflector, Boxed	165	1,8,9,12,14	