



LVP-1



LVP-1 Installed

| Low Voltage Partition | Catalog Number | Component Description                                                                                                 | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|-----------------------|----------------|-----------------------------------------------------------------------------------------------------------------------|------------|----------------|----------------|
|                       | LVP-1          | Low voltage divider plate for use with 2302, 3303, 4304, 5305 Series and 9314 only.<br>See 2008 NEC 800.133(A)(1)(c). |            | 80000          | 50*            |

\* Consists of ten (10) packages of five (5) pieces each.



9312-EK



9312-EWC2



9312-EWC4





9312-EWK










9329-EWK



2TP

| Ears | Cu. In. Volume | Catalog Number | Component Description                                                                                                     | Exterior Dimensions |       |       | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|------|----------------|----------------|---------------------------------------------------------------------------------------------------------------------------|---------------------|-------|-------|------------|----------------|----------------|
|      |                |                |                                                                                                                           | D                   | W     | H     |            |                |                |
|      | 28.0           | 9312-E         |  Ears, Speed Klamps™- bulk packed        | 2-3/4               | 4-1/8 | 3-1/4 | 10064      | 50             | 23             |
|      | 28.0           | 9312-EK        |  Ears, Speed Klamps™- factory installed | 2-3/4               | 4-1/8 | 3-1/4 | 29112      | 50             | 24             |

| Ears & Wing Brackets | Cu. In. Volume | Catalog Number | Component Description                                                                                                                      | Exterior Dimensions |       |       | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|----------------------|----------------|----------------|--------------------------------------------------------------------------------------------------------------------------------------------|---------------------|-------|-------|------------|----------------|----------------|
|                      |                |                |                                                                                                                                            | D                   | W     | H     |            |                |                |
|                      | 28.0           | 9312-EW        |  Ears, wing brackets, Speed Klamps™- bulk packed        | 2-3/4               | 4-1/8 | 3-1/4 | 29100      | 50             | 25             |
|                      | 28.0           | 9312-EWC2      |  Ears, wing brackets, 2 wire clamps - factory installed | 2-3/4               | 4-1/8 | 3-1/4 | 29110      | 50             | 26             |
|                      | 28.0           | 9312-EWC4      |  Ears, wing brackets, 4 wire clamps - factory installed | 2-3/4               | 4-1/8 | 3-1/4 | 29120      | 50             | 28             |
|                      | 28.0           | 9312-EWK       |  Ears, wing brackets, Speed Klamps™- factory installed  | 2-3/4               | 4-1/8 | 3-1/4 | 29111      | 50             | 25             |
|                      | 32.5           | 9329-EW        |  Ears, wing brackets, Speed Klamps™- bulk packed        | 3-1/4               | 4-1/8 | 3-1/4 | 10801      | 50             | 27             |
|                      | 32.5           | 9329-EWK       |  Ears, wing brackets, Speed Klamps™- factory installed  | 3-1/4               | 4-1/8 | 3-1/4 | 10802      | 50             | 27             |

| Template | Catalog Number | Component Description                                                                                                                                      | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|----------|----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|----------------|----------------|
|          | 2TP            |  Metal template for two gang old work box: 9312-E series, 9329-E series | 88016      | 1              | 2              |

All dimensions are in inches unless otherwise noted.  
See page 7 for Attachment Coding suffix descriptions.

 Old Work/Manufactured Housing Boxes

 Flush-Device Box  
UL File No. E30594



3300-2Z2K



3300-Z2K



3303-2Z4K



3303-Z4K



3300-Z2BK

|                   | Cu. In. Volume | Catalog Number | Component Description                                                     | Exterior Dimensions |         |     | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|-------------------|----------------|----------------|---------------------------------------------------------------------------|---------------------|---------|-----|------------|----------------|----------------|
|                   |                |                |                                                                           | D                   | W       | H   |            |                |                |
| <b>"Z" Hanger</b> | 46.0           | 3300-2Z2       | ¼" offset, "Z" hanger each side of box, Speed Klamps™ - bulk packed       | 3                   | 5-11/16 | 3-¾ | 14700      | 25             | 29             |
|                   | 46.0           | 3300-2Z2K      | ¼" offset, "Z" hanger each side of box, Speed Klamps™ - factory installed | 3                   | 5-11/16 | 3-¾ | 14702      | 25             | 29             |
|                   | 46.0           | 3300-2Z4       | ½" offset, "Z" hanger each side of box, Speed Klamps™ - bulk packed       | 3                   | 5-11/16 | 3-¾ | 15120      | 25             | 29             |
|                   | 46.0           | 3300-2Z4K      | ½" offset, "Z" hanger each side of box, Speed Klamps™ - factory installed | 3                   | 5-11/16 | 3-¾ | 15121      | 25             | 29             |
|                   | 46.0           | 3300-Z2        | ¼" offset, "Z" hanger, Speed Klamps™ - bulk packed                        | 3                   | 5-11/16 | 3-¾ | 14560      | 25             | 24             |
|                   | 46.0           | 3300-Z2K       | ¼" offset, "Z" hanger, Speed Klamps™ - factory installed                  | 3                   | 5-11/16 | 3-¾ | 14562      | 25             | 24             |
|                   | 46.0           | 3300-Z4        | ½" offset, "Z" hanger, Speed Klamps™ - bulk packed                        | 3                   | 5-11/16 | 3-¾ | 14980      | 24             | 24             |
|                   | 46.0           | 3300-Z4K       | ½" offset, "Z" hanger, Speed Klamps™ - factory installed                  | 3                   | 5-11/16 | 3-¾ | 15017      | 24             | 24             |
|                   | 56.5           | 3303-2Z4       | ½" offset, "Z" hanger each side of box, Speed Klamps™ - bulk packed       | 3-9/16              | 5-11/16 | 3-¾ | 15222      | 25             | 33             |
|                   | 56.5           | 3303-2Z4K      | ½" offset, "Z" hanger each side of box, Speed Klamps™ - factory installed | 3-9/16              | 5-11/16 | 3-¾ | 15223      | 25             | 33             |
|                   | 56.5           | 3303-Z4        | ½" offset, "Z" hanger, Speed Klamps™ - bulk packed                        | 3-9/16              | 5-11/16 | 3-¾ | 15205      | 20             | 21             |
|                   | 56.5           | 3303-Z4K       | ½" offset, "Z" hanger, Speed Klamps™ - factory installed                  | 3-9/16              | 5-11/16 | 3-¾ | 15206      | 20             | 22             |

|                            | Cu. In. Volume | Catalog Number | Component Description                                                                | Exterior Dimensions |         |     | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|----------------------------|----------------|----------------|--------------------------------------------------------------------------------------|---------------------|---------|-----|------------|----------------|----------------|
|                            |                |                |                                                                                      | D                   | W       | H   |            |                |                |
| <b>"Z" Hanger with Bar</b> | 46.0           | 3300-Z2B       | ¼" offset, "Z" hanger, adjustable stabilizing bar, Speed Klamps™ - bulk packed       | 3                   | 5-11/16 | 3-¾ | 14595      | 20             | 25             |
|                            | 46.0           | 3300-Z2BK      | ¼" offset, "Z" hanger, adjustable stabilizing bar, Speed Klamps™ - factory installed | 3                   | 5-11/16 | 3-¾ | 14597      | 20             | 25             |



LVP-1



LVP-1 Installed






9313-EWC3



9313-EWK


|  | Catalog Number | Component Description | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|--|----------------|-----------------------|------------|----------------|----------------|
|  |                |                       |            |                |                |

\* Consists of ten (10) packages of five (5) pieces each.

|                                | Cu. In. Volume | Catalog Number | Component Description                                                                                                                      | Exterior Dimensions |         |     | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|--------------------------------|----------------|----------------|--------------------------------------------------------------------------------------------------------------------------------------------|---------------------|---------|-----|------------|----------------|----------------|
|                                |                |                |                                                                                                                                            | D                   | W       | H   |            |                |                |
| <b>Ears with Wing Brackets</b> | 42.5           | 9313-EW        |  Ears, wing brackets, Speed Klamps™- bulk packed        | 2-7/8               | 5-15/16 | 3-¼ | 10093      | 25             | 17             |
|                                | 42.5           | 9313-EWC3      |  Ears, wing brackets, 3 wire clamps - factory installed | 2-7/8               | 5-15/16 | 3-¼ | 10095      | 25             | 18             |
|                                | 42.5           | 9313-EWK       |  Ears, wing brackets, Speed Klamps™- factory installed  | 2-7/8               | 5-15/16 | 3-¼ | 10094      | 25             | 17             |

All dimensions are in inches unless otherwise noted.  
See page 7 for Attachment Coding suffix descriptions.

 Old Work/Manufactured Housing Boxes

 Flush-Device Box  
UL File No. E30594

# fiberglassBOX™ Four Gang Residential Switch or Receptacle Box



4300-2Z2K



4300-Z2K



4300-Z2BK



4304-Z4BK

|            | Cu. In. Volume | Catalog Number | Component Description                                                     | Exterior Dimensions |     |     | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|------------|----------------|----------------|---------------------------------------------------------------------------|---------------------|-----|-----|------------|----------------|----------------|
|            |                |                |                                                                           | D                   | W   | H   |            |                |                |
| "Z" Hanger | 60.0           | 4300-2Z2       | ¼" offset, "Z" hanger each side of box, Speed Klamps™ - bulk packed       | 3                   | 7-½ | 3-¾ | 16905      | 12             | 15             |
|            | 60.0           | 4300-2Z2K      | ¼" offset, "Z" hanger each side of box, Speed Klamps™ - factory installed | 3                   | 7-½ | 3-¾ | 16907      | 12             | 15             |
|            | 60.0           | 4300-Z2        | ¼" offset, "Z" hanger, Speed Klamps™ - bulk packed                        | 3                   | 7-½ | 3-¾ | 16725      | 12             | 14             |
|            | 60.0           | 4300-Z2K       | ¼" offset, "Z" hanger, Speed Klamps™ - factory installed                  | 3                   | 7-½ | 3-¾ | 16906      | 12             | 14             |
|            | 60.0           | 4300-Z4        | ½" offset, "Z" hanger, Speed Klamps™ - bulk packed                        | 3                   | 7-½ | 3-¾ | 18265      | 12             | 15             |
|            | 60.0           | 4300-Z4K       | ½" offset, "Z" hanger, Speed Klamps™ - factory installed                  | 3                   | 7-½ | 3-¾ | 17312      | 12             | 22             |
|            | 75.0           | 4304-2Z4       | ½" offset, "Z" hanger each side of box, Speed Klamps™ - bulk packed       | 3-9/16              | 7-½ | 3-¾ | 17560      | 12             | 17             |
|            | 75.0           | 4304-2Z4K      | ½" offset, "Z" hanger each side of box, Speed Klamps™ - factory installed | 3-9/16              | 7-½ | 3-¾ | 17561      | 12             | 17             |

|                     | Cu. In. Volume | Catalog Number | Component Description                                                                | Exterior Dimensions |     |     | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|---------------------|----------------|----------------|--------------------------------------------------------------------------------------|---------------------|-----|-----|------------|----------------|----------------|
|                     |                |                |                                                                                      | D                   | W   | H   |            |                |                |
| "Z" Hanger with Bar | 60.0           | 4300-Z2B       | ¼" offset, "Z" hanger, adjustable stabilizing bar, Speed Klamps™ - bulk packed       | 3                   | 7-½ | 3-¾ | 16770      | 6              | 9              |
|                     | 60.0           | 4300-Z2BK      | ¼" offset, "Z" hanger, adjustable stabilizing bar, Speed Klamps™ - factory installed | 3                   | 7-½ | 3-¾ | 16771      | 6              | 9              |
|                     | 75.0           | 4304-Z4B       | ½" offset, "Z" hanger, adjustable stabilizing bar, Speed Klamps™ - bulk packed       | 3-9/16              | 7-½ | 3-¾ | 17554      | 6              | 10             |
|                     | 75.0           | 4304-Z4BK      | ½" offset, "Z" hanger, adjustable stabilizing bar, Speed Klamps™ - factory installed | 3-9/16              | 7-½ | 3-¾ | 17555      | 6              | 10             |



LVP-1



9314-EWK

| Low Voltage Partition | Catalog Number | Component Description                                                                                              | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|-----------------------|----------------|--------------------------------------------------------------------------------------------------------------------|------------|----------------|----------------|
|                       | LVP-1          | Low voltage divider plate for use with 2302, 3303, 4304, 5305 Series and 9314 only. See 2008 NEC 800.133(A)(1)(c). | 80000      | 50*            | 3              |


\* Consists of ten (10) packages of five (5) pieces each.

| Ears w/ Wing Brackets | Cu. In. Volume | Catalog Number | Component Description                                               | Exterior Dimensions |         |     | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|-----------------------|----------------|----------------|---------------------------------------------------------------------|---------------------|---------|-----|------------|----------------|----------------|
|                       |                |                |                                                                     | D                   | W       | H   |            |                |                |
|                       | 70.0           | 9314-EWK       | Ears, wing brackets, ½" knockouts, Speed Klamps™- factory installed | 3-9/16              | 7-11/16 | 3-¾ | 31800      | 6              | 8              |

All dimensions are in inches unless otherwise noted.  
See page 7 for Attachment Coding suffix descriptions.

Old Work/Manufactured Housing Boxes

Flush-Device Box  
UL File No. E30594



|                              | Cu. In. Volume | Catalog Number        | Component Description                                                                                                 | Exterior Dimensions |        |       | UPC# 85339        | Std. Pkg. Qty.        | Std. Wt. (lb.)        |
|------------------------------|----------------|-----------------------|-----------------------------------------------------------------------------------------------------------------------|---------------------|--------|-------|-------------------|-----------------------|-----------------------|
|                              |                |                       |                                                                                                                       | D                   | W      | H     |                   |                       |                       |
| <b>Nail-On</b>               | 94.0           | 5305-NK               | Angled mid-nails, Speed Klamps™ - factory installed                                                                   | 3-9/16              | 9-5/16 | 3-3/4 | 18001             | 6                     | 9                     |
| <b>Nail-On with Bar</b>      | 94.0           | 5305-NBK              | Angled mid-nails, adjustable stabilizing bar, Speed Klamps™ - factory installed                                       | 3-9/16              | 9-5/16 | 3-3/4 | 18002             | 6                     | 10                    |
| <b>"Z" Hanger with Bar</b>   | 94.0           | 5305-Z4BK             | 1/2" offset, "Z" hanger, adjustable stabilizing bar, Speed Klamps™ - factory installed                                | 3-9/16              | 9-5/16 | 3-3/4 | 18003             | 6                     | 12                    |
| <b>Low Voltage Partition</b> |                | <b>Catalog Number</b> | <b>Component Description</b>                                                                                          |                     |        |       | <b>UPC# 85339</b> | <b>Std. Pkg. Qty.</b> | <b>Std. Wt. (lb.)</b> |
|                              |                | LVP-1                 | Low voltage divider plate for use with 2302, 3303, 4304, 5305 Series and 9314 only.<br>See 2008 NEC 800.133(A)(1)(c). |                     |        |       | 80000             | 50*                   | 3                     |

\* Consists of ten (10) packages of five (5) pieces each.

All dimensions are in inches unless otherwise noted.  
See page 7 for Attachment Coding suffix descriptions.

 Flush-Device Box  
UL File No. E30594

# Structured Cable/Low Voltage

Single Gang Boxes, Low Voltage Partitions, Plaster Rings



ALLIED MOULDED PRODUCTS, Inc.



LVBOW-1



LVB-1



LVPR-1



LVP-1



LVP-2

| Structured Cable/Low Voltage | Catalog Number | Component Description                                                                                                                                                                                    | Exterior Dimensions |        |         | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|------------------------------|----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|--------|---------|------------|----------------|----------------|
|                              |                |                                                                                                                                                                                                          | D                   | W      | H       |            |                |                |
|                              | LVBOW-1        | Single gang, old work, structured cable box with ears and wings                                                                                                                                          | 3-1/16              | 2-5/16 | 3-11/16 | 80003      | 24             | 5              |
|                              | LVB-1          | Single gang, angled mid-nails, structured cable box                                                                                                                                                      | 2-3/4               | 2-1/4  | 3-3/4   | 80002      | 48             | 9              |
|                              | LVPR-1         | Single gang plaster ring, 1/2" offset, structured cable bracket for steel or wood stud face mounting                                                                                                     | 5/8                 | 4      | 4       | 80001      | 50             | 4              |
|                              | LVP-1          | Low voltage divider plate for use with fiberglassBOX™ series 2302, 3303, 4304, 5305, and 9314 only                                                                                                       | 3/32                | 3-5/16 | 3-3/4   | 80000      | 50*            | 3              |
|                              | LVP-2          | Low voltage divider plate for use with SLIDERBOX® series SB-2, SB-3, and SB-4; and flexBOX® part numbers P-442, P-442QT, P-643, P-643QT, P-764, P-764QT, P-764B, P-764H, P-764HBQT, P-2400W, and P-3520W | 3-32                | 3-1/16 | 3-1/2   | 80005      | 50*            | 3              |

\* Consists of ten (10) packages of five (5) pieces each.


## LVBOW-1 Features and Benefits

- Old work structured cable box
- Sturdy construction with “box-like” strength and rigidity
- Molded thread device holes provide for secure mounting of structured cable devices and cover plates
- Eliminates the need to modify single gang outlet boxes
- Open back design for generous cable bend radius
- Holes in back section provide a means to secure the cable allowing cable accessibility later (Fig. A)
- U.S. Patents D531,128 and 7,179,994



## LVB-1 Features and Benefits


- New work structured cable box
- Sturdy construction with “box-like” strength and rigidity
- Eliminates need to modify single gang box
- Open back for generous cable bend radius
- Easy nail-on mounting design
- Holes on back provide a means to wire tie the cable allowing cable accessibility later (Fig. A)
- Open back channel to store and protect cable during drywall phase (Fig. B)
- US Patents D531,128 and 7,179,994



## LVP-1/LVP-2 Features and Benefits

- Separates line and low voltage within the same electrical box
- Use LVP-1 with Allied Moulded’s deep series 2302, 3303, 4304, 5305, and 9314 fiberglass boxes
- Use LVP-2 with Allied Moulded’s flexBOX® products and SLIDERBOX® products (see chart above for specific part numbers)
- Allows for a reduced number of wall box installations
- Fast, easy and convenient to install

- Complies with article 800.133(A)(1)(c) from 2008 NEC
- For low voltage applications in fire rated walls, utilize the LVP-1 partition with the Allied Moulded deep series fiberglass wall boxes which carry the industry exclusive rating for reduced horizontal separation in the same stud cavity



All dimensions are in inches unless otherwise noted.

Old Work/Manufactured Housing Boxes



UL File No. E245435 - Boxes  
UL File No. E30594 - Partitions



LVP-1



LVP-1 Installed

| Low Voltage Partition | Catalog Number | Component Description                                                                                                 | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|-----------------------|----------------|-----------------------------------------------------------------------------------------------------------------------|------------|----------------|----------------|
|                       | LVP-1          | Low voltage divider plate for use with 2302, 3303, 4304, 5305 Series and 9314 only.<br>See 2008 NEC 800.133(A)(1)(c). |            | 80000          | 50*            |

\* Consists of ten (10) packages of five (5) pieces each.



9312-EK



9312-EWC2



9312-EWC4





9312-EWK










9329-EWK



2TP

| Ears | Cu. In. Volume | Catalog Number | Component Description                                                                                                     | Exterior Dimensions |       |     | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|------|----------------|----------------|---------------------------------------------------------------------------------------------------------------------------|---------------------|-------|-----|------------|----------------|----------------|
|      |                |                |                                                                                                                           | D                   | W     | H   |            |                |                |
|      | 28.0           | 9312-E         |  Ears, Speed Klamps™- bulk packed        | 2-¾                 | 4-1/8 | 3-¼ | 10064      | 50             | 23             |
|      | 28.0           | 9312-EK        |  Ears, Speed Klamps™- factory installed | 2-¾                 | 4-1/8 | 3-¼ | 29112      | 50             | 24             |

| Ears & Wing Brackets | Cu. In. Volume | Catalog Number | Component Description                                                                                                                      | Exterior Dimensions |       |     | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|----------------------|----------------|----------------|--------------------------------------------------------------------------------------------------------------------------------------------|---------------------|-------|-----|------------|----------------|----------------|
|                      |                |                |                                                                                                                                            | D                   | W     | H   |            |                |                |
|                      | 28.0           | 9312-EW        |  Ears, wing brackets, Speed Klamps™- bulk packed        | 2-¾                 | 4-1/8 | 3-¼ | 29100      | 50             | 25             |
|                      | 28.0           | 9312-EWC2      |  Ears, wing brackets, 2 wire clamps - factory installed | 2-¾                 | 4-1/8 | 3-¼ | 29110      | 50             | 26             |
|                      | 28.0           | 9312-EWC4      |  Ears, wing brackets, 4 wire clamps - factory installed | 2-¾                 | 4-1/8 | 3-¼ | 29120      | 50             | 28             |
|                      | 28.0           | 9312-EWK       |  Ears, wing brackets, Speed Klamps™- factory installed  | 2-¾                 | 4-1/8 | 3-¼ | 29111      | 50             | 25             |
|                      | 32.5           | 9329-EW        |  Ears, wing brackets, Speed Klamps™- bulk packed        | 3-¼                 | 4-1/8 | 3-¼ | 10801      | 50             | 27             |
|                      | 32.5           | 9329-EWK       |  Ears, wing brackets, Speed Klamps™- factory installed  | 3-¼                 | 4-1/8 | 3-¼ | 10802      | 50             | 27             |

| Template | Catalog Number | Component Description                                                                                                                                      | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|----------|----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|----------------|----------------|
|          | 2TP            |  Metal template for two gang old work box: 9312-E series, 9329-E series | 88016      | 1              | 2              |

All dimensions are in inches unless otherwise noted.  
See page 7 for Attachment Coding suffix descriptions.

 Old Work/Manufactured Housing Boxes

 Flush-Device Box  
UL File No. E30594



3300-2Z2K



3300-Z2K



3303-2Z4K



3303-Z4K



3300-Z2BK

|                   | Cu. In. Volume | Catalog Number | Component Description                                                     | Exterior Dimensions |         |     | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|-------------------|----------------|----------------|---------------------------------------------------------------------------|---------------------|---------|-----|------------|----------------|----------------|
|                   |                |                |                                                                           | D                   | W       | H   |            |                |                |
| <b>"Z" Hanger</b> | 46.0           | 3300-2Z2       | ¼" offset, "Z" hanger each side of box, Speed Klamps™ - bulk packed       | 3                   | 5-11/16 | 3-¾ | 14700      | 25             | 29             |
|                   | 46.0           | 3300-2Z2K      | ¼" offset, "Z" hanger each side of box, Speed Klamps™ - factory installed | 3                   | 5-11/16 | 3-¾ | 14702      | 25             | 29             |
|                   | 46.0           | 3300-2Z4       | ½" offset, "Z" hanger each side of box, Speed Klamps™ - bulk packed       | 3                   | 5-11/16 | 3-¾ | 15120      | 25             | 29             |
|                   | 46.0           | 3300-2Z4K      | ½" offset, "Z" hanger each side of box, Speed Klamps™ - factory installed | 3                   | 5-11/16 | 3-¾ | 15121      | 25             | 29             |
|                   | 46.0           | 3300-Z2        | ¼" offset, "Z" hanger, Speed Klamps™ - bulk packed                        | 3                   | 5-11/16 | 3-¾ | 14560      | 25             | 24             |
|                   | 46.0           | 3300-Z2K       | ¼" offset, "Z" hanger, Speed Klamps™ - factory installed                  | 3                   | 5-11/16 | 3-¾ | 14562      | 25             | 24             |
|                   | 46.0           | 3300-Z4        | ½" offset, "Z" hanger, Speed Klamps™ - bulk packed                        | 3                   | 5-11/16 | 3-¾ | 14980      | 24             | 24             |
|                   | 46.0           | 3300-Z4K       | ½" offset, "Z" hanger, Speed Klamps™ - factory installed                  | 3                   | 5-11/16 | 3-¾ | 15017      | 24             | 24             |
|                   | 56.5           | 3303-2Z4       | ½" offset, "Z" hanger each side of box, Speed Klamps™ - bulk packed       | 3-9/16              | 5-11/16 | 3-¾ | 15222      | 25             | 33             |
|                   | 56.5           | 3303-2Z4K      | ½" offset, "Z" hanger each side of box, Speed Klamps™ - factory installed | 3-9/16              | 5-11/16 | 3-¾ | 15223      | 25             | 33             |
|                   | 56.5           | 3303-Z4        | ½" offset, "Z" hanger, Speed Klamps™ - bulk packed                        | 3-9/16              | 5-11/16 | 3-¾ | 15205      | 20             | 21             |
|                   | 56.5           | 3303-Z4K       | ½" offset, "Z" hanger, Speed Klamps™ - factory installed                  | 3-9/16              | 5-11/16 | 3-¾ | 15206      | 20             | 22             |

|                            | Cu. In. Volume | Catalog Number | Component Description                                                                | Exterior Dimensions |         |     | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|----------------------------|----------------|----------------|--------------------------------------------------------------------------------------|---------------------|---------|-----|------------|----------------|----------------|
|                            |                |                |                                                                                      | D                   | W       | H   |            |                |                |
| <b>"Z" Hanger with Bar</b> | 46.0           | 3300-Z2B       | ¼" offset, "Z" hanger, adjustable stabilizing bar, Speed Klamps™ - bulk packed       | 3                   | 5-11/16 | 3-¾ | 14595      | 20             | 25             |
|                            | 46.0           | 3300-Z2BK      | ¼" offset, "Z" hanger, adjustable stabilizing bar, Speed Klamps™ - factory installed | 3                   | 5-11/16 | 3-¾ | 14597      | 20             | 25             |



LVP-1



LVP-1 Installed






9313-EWC3



9313-EWK


| <b>Low Voltage Partition</b> | Catalog Number | Component Description                                                                                              | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|------------------------------|----------------|--------------------------------------------------------------------------------------------------------------------|------------|----------------|----------------|
|                              | LVP-1          | Low voltage divider plate for use with 2302, 3303, 4304, 5305 Series and 9314 only. See 2008 NEC 800.133(A)(1)(c). | 80000      | 50*            | 3              |

\* Consists of ten (10) packages of five (5) pieces each.

| <b>Ears with Wing Brackets</b> | Cu. In. Volume | Catalog Number | Component Description                                                                                                                      | Exterior Dimensions |         |     | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|--------------------------------|----------------|----------------|--------------------------------------------------------------------------------------------------------------------------------------------|---------------------|---------|-----|------------|----------------|----------------|
|                                |                |                |                                                                                                                                            | D                   | W       | H   |            |                |                |
|                                | 42.5           | 9313-EW        |  Ears, wing brackets, Speed Klamps™- bulk packed        | 2-7/8               | 5-15/16 | 3-¼ | 10093      | 25             | 17             |
|                                | 42.5           | 9313-EWC3      |  Ears, wing brackets, 3 wire clamps - factory installed | 2-7/8               | 5-15/16 | 3-¼ | 10095      | 25             | 18             |
|                                | 42.5           | 9313-EWK       |  Ears, wing brackets, Speed Klamps™- factory installed  | 2-7/8               | 5-15/16 | 3-¼ | 10094      | 25             | 17             |

All dimensions are in inches unless otherwise noted.  
See page 7 for Attachment Coding suffix descriptions.

 Old Work/Manufactured Housing Boxes

 Flush-Device Box  
UL File No. E30594

# fiberglassBOX™ Four Gang Residential Switch or Receptacle Box



4300-2Z2K



4300-Z2K



4300-Z2BK



4304-Z4BK

|            | Cu. In. Volume | Catalog Number | Component Description                                                     | Exterior Dimensions |     |     | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|------------|----------------|----------------|---------------------------------------------------------------------------|---------------------|-----|-----|------------|----------------|----------------|
|            |                |                |                                                                           | D                   | W   | H   |            |                |                |
| "Z" Hanger | 60.0           | 4300-2Z2       | ¼" offset, "Z" hanger each side of box, Speed Klamps™ - bulk packed       | 3                   | 7-½ | 3-¾ | 16905      | 12             | 15             |
|            | 60.0           | 4300-2Z2K      | ¼" offset, "Z" hanger each side of box, Speed Klamps™ - factory installed | 3                   | 7-½ | 3-¾ | 16907      | 12             | 15             |
|            | 60.0           | 4300-Z2        | ¼" offset, "Z" hanger, Speed Klamps™ - bulk packed                        | 3                   | 7-½ | 3-¾ | 16725      | 12             | 14             |
|            | 60.0           | 4300-Z2K       | ¼" offset, "Z" hanger, Speed Klamps™ - factory installed                  | 3                   | 7-½ | 3-¾ | 16906      | 12             | 14             |
|            | 60.0           | 4300-Z4        | ½" offset, "Z" hanger, Speed Klamps™ - bulk packed                        | 3                   | 7-½ | 3-¾ | 18265      | 12             | 15             |
|            | 60.0           | 4300-Z4K       | ½" offset, "Z" hanger, Speed Klamps™ - factory installed                  | 3                   | 7-½ | 3-¾ | 17312      | 12             | 22             |
|            | 75.0           | 4304-2Z4       | ½" offset, "Z" hanger each side of box, Speed Klamps™ - bulk packed       | 3-9/16              | 7-½ | 3-¾ | 17560      | 12             | 17             |
|            | 75.0           | 4304-2Z4K      | ½" offset, "Z" hanger each side of box, Speed Klamps™ - factory installed | 3-9/16              | 7-½ | 3-¾ | 17561      | 12             | 17             |

|                     | Cu. In. Volume | Catalog Number | Component Description                                                                | Exterior Dimensions |     |     | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|---------------------|----------------|----------------|--------------------------------------------------------------------------------------|---------------------|-----|-----|------------|----------------|----------------|
|                     |                |                |                                                                                      | D                   | W   | H   |            |                |                |
| "Z" Hanger with Bar | 60.0           | 4300-Z2B       | ¼" offset, "Z" hanger, adjustable stabilizing bar, Speed Klamps™ - bulk packed       | 3                   | 7-½ | 3-¾ | 16770      | 6              | 9              |
|                     | 60.0           | 4300-Z2BK      | ¼" offset, "Z" hanger, adjustable stabilizing bar, Speed Klamps™ - factory installed | 3                   | 7-½ | 3-¾ | 16771      | 6              | 9              |
|                     | 75.0           | 4304-Z4B       | ½" offset, "Z" hanger, adjustable stabilizing bar, Speed Klamps™ - bulk packed       | 3-9/16              | 7-½ | 3-¾ | 17554      | 6              | 10             |
|                     | 75.0           | 4304-Z4BK      | ½" offset, "Z" hanger, adjustable stabilizing bar, Speed Klamps™ - factory installed | 3-9/16              | 7-½ | 3-¾ | 17555      | 6              | 10             |



LVP-1



9314-EWK

| Low Voltage Partition | Catalog Number | Component Description                                                                                              | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|-----------------------|----------------|--------------------------------------------------------------------------------------------------------------------|------------|----------------|----------------|
|                       | LVP-1          | Low voltage divider plate for use with 2302, 3303, 4304, 5305 Series and 9314 only. See 2008 NEC 800.133(A)(1)(c). | 80000      | 50*            | 3              |

\* Consists of ten (10) packages of five (5) pieces each.


| Ears w/ Wing Brackets | Cu. In. Volume | Catalog Number | Component Description                                               | Exterior Dimensions |         |     | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|-----------------------|----------------|----------------|---------------------------------------------------------------------|---------------------|---------|-----|------------|----------------|----------------|
|                       |                |                |                                                                     | D                   | W       | H   |            |                |                |
|                       | 70.0           | 9314-EWK       | Ears, wing brackets, ½" knockouts, Speed Klamps™- factory installed | 3-9/16              | 7-11/16 | 3-¾ | 31800      | 6              | 8              |

All dimensions are in inches unless otherwise noted.  
See page 7 for Attachment Coding suffix descriptions.

Old Work/Manufactured Housing Boxes

Flush-Device Box  
UL File No. E30594





|                              | Cu. In. Volume | Catalog Number        | Component Description                                                                                                 | Exterior Dimensions |        |       | UPC# 85339        | Std. Pkg. Qty.        | Std. Wt. (lb.)        |
|------------------------------|----------------|-----------------------|-----------------------------------------------------------------------------------------------------------------------|---------------------|--------|-------|-------------------|-----------------------|-----------------------|
|                              |                |                       |                                                                                                                       | D                   | W      | H     |                   |                       |                       |
| <b>Nail-On</b>               | 94.0           | 5305-NK               | Angled mid-nails, Speed Klamps™ - factory installed                                                                   | 3-9/16              | 9-5/16 | 3-3/4 | 18001             | 6                     | 9                     |
| <b>Nail-On with Bar</b>      | 94.0           | 5305-NBK              | Angled mid-nails, adjustable stabilizing bar, Speed Klamps™ - factory installed                                       | 3-9/16              | 9-5/16 | 3-3/4 | 18002             | 6                     | 10                    |
| <b>"Z" Hanger with Bar</b>   | 94.0           | 5305-Z4BK             | 1/2" offset, "Z" hanger, adjustable stabilizing bar, Speed Klamps™ - factory installed                                | 3-9/16              | 9-5/16 | 3-3/4 | 18003             | 6                     | 12                    |
| <b>Low Voltage Partition</b> |                | <b>Catalog Number</b> | <b>Component Description</b>                                                                                          |                     |        |       | <b>UPC# 85339</b> | <b>Std. Pkg. Qty.</b> | <b>Std. Wt. (lb.)</b> |
|                              |                | LVP-1                 | Low voltage divider plate for use with 2302, 3303, 4304, 5305 Series and 9314 only.<br>See 2008 NEC 800.133(A)(1)(c). |                     |        |       | 80000             | 50*                   | 3                     |

\* Consists of ten (10) packages of five (5) pieces each.

All dimensions are in inches unless otherwise noted.  
See page 7 for Attachment Coding suffix descriptions.

 Flush-Device Box  
UL File No. E30594

# Structured Cable/Low Voltage

Single Gang Boxes, Low Voltage Partitions, Plaster Rings




ALLIED  
MOULDED  
PRODUCTS, Inc.



LVBOW-1



LVB-1



LVPR-1



LVP-1



LVP-2

Structured Cable/Low Voltage

| Catalog Number | Component Description                                                                                                                                                                                    | Exterior Dimensions |        |         | UPC# 85339 | Std. Pkg. Qty. | Std. Wt. (lb.) |
|----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|--------|---------|------------|----------------|----------------|
|                |                                                                                                                                                                                                          | D                   | W      | H       |            |                |                |
| LVBOW-1        | Single gang, old work, structured cable box with ears and wings                                                                                                                                          | 3-1/16              | 2-5/16 | 3-11/16 | 80003      | 24             | 5              |
| LVB-1          | Single gang, angled mid-nails, structured cable box                                                                                                                                                      | 2-3/4               | 2-1/4  | 3-3/4   | 80002      | 48             | 9              |
| LVPR-1         | Single gang plaster ring, 1/2" offset, structured cable bracket for steel or wood stud face mounting                                                                                                     | 5/8                 | 4      | 4       | 80001      | 50             | 4              |
| LVP-1          | Low voltage divider plate for use with fiberglassBOX™ series 2302, 3303, 4304, 5305, and 9314 only                                                                                                       | 3/32                | 3-5/16 | 3-3/4   | 80000      | 50*            | 3              |
| LVP-2          | Low voltage divider plate for use with SLIDERBOX® series SB-2, SB-3, and SB-4; and flexBOX® part numbers P-442, P-442QT, P-643, P-643QT, P-764, P-764QT, P-764B, P-764H, P-764HBQT, P-2400W, and P-3520W | 3-32                | 3-1/16 | 3-1/2   | 80005      | 50*            | 3              |

\* Consists of ten (10) packages of five (5) pieces each.


## LVBOW-1 Features and Benefits

- Old work structured cable box
- Sturdy construction with “box-like” strength and rigidity
- Molded thread device holes provide for secure mounting of structured cable devices and cover plates
- Eliminates the need to modify single gang outlet boxes
- Open back design for generous cable bend radius
- Holes in back section provide a means to secure the cable allowing cable accessibility later (Fig. A)
- U.S. Patents D531,128 and 7,179,994



## LVB-1 Features and Benefits


- New work structured cable box
- Sturdy construction with “box-like” strength and rigidity
- Eliminates need to modify single gang box
- Open back for generous cable bend radius
- Easy nail-on mounting design
- Holes on back provide a means to wire tie the cable allowing cable accessibility later (Fig. A)
- Open back channel to store and protect cable during drywall phase (Fig. B)
- US Patents D531,128 and 7,179,994



## LVP-1/LVP-2 Features and Benefits

- Separates line and low voltage within the same electrical box
- Use LVP-1 with Allied Moulded’s deep series 2302, 3303, 4304, 5305, and 9314 fiberglass boxes
- Use LVP-2 with Allied Moulded’s flexBOX® products and SLIDERBOX® products (see chart above for specific part numbers)
- Allows for a reduced number of wall box installations
- Fast, easy and convenient to install

- Complies with article 800.133(A)(1)(c) from 2008 NEC
- For low voltage applications in fire rated walls, utilize the LVP-1 partition with the Allied Moulded deep series fiberglass wall boxes which carry the industry exclusive rating for reduced horizontal separation in the same stud cavity



All dimensions are in inches unless otherwise noted.

Old Work/Manufactured Housing Boxes



UL File No. E245435 - Boxes  
UL File No. E30594 - Partitions