



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV1410LFM 14-18AWG #10STD Blue Insld LCK Fork TRML *Panduit Corporation*

Catalog Number	PV1410LFM
Manufacturer	Panduit Corporation
Description	Locking Fork Terminal, Vinyl Insulated, Funnel Entry, 18- 14 Awg, #10 Stud Size, Bulk Package.
Weight per unit	0.0026 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel Entry
insulation	Vinyl
Material	Copper
Voltage Rating	600
Wire Size	14

Material, Color, and Finish

Color	Blue
Finish	Tinned

Dimensions and Weight

Size	#10
------	-----

Descriptions

Description	14-18AWG #10STD BLUE INSLTD LCK FORK TRML
extra long description	PAN PV14-10LF-M Pan-Term® PV14-10LF
Long Description	Locking Fork Terminal, vinyl insulated, funnel entry, 18- 14 AWG, #10 stud size, bulk package.
Product Type	Pan-Term® PV14-10LF-M Fork Terminal, Blue, Vinyl, 14-18 Awg,

Manufacturer Information

Brand	Panduit®
GTIN	00074983808113
Manufacturers Part Number	PV14-10LF-M
UPC	074983808113

Taxonomies, Classifications, and Categories

Type	Ring Terminal
------	---------------

Availability

minimum qty	1000
-------------	------

Packaging

Carton	1000
Weight Per each	0.0026



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	Fork shape
Mounting	5/16
standard	CSA Certified LR31212;UL Listed 587H E52164
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)