ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



078573 4" SCH40 30D PVC ELBOW

MULTIFITTINGS/KRALOY

Catalog Number	078573
Manufacturer	MULTIFITTINGS/KRALOY
Description	40STD4030 4"x30D PVC STD ELBOW SPxSP SCH40 KRALOY
Weight per unit	4.2 (lbs/each)
Product Category	Boxes & Covers

Features

Material	PVC
Connection	SPxSP

Descriptions

Description	4" SCH40 30D PVC ELBOW
Features	PRODUCT LINE: Kraloy Rigid PVC Fittings includes adapters, couplings, elbows, access fittings, boxes, cover plates, expansion fittings and conduit spacers - virtually any fitting required to complete the PVC conduit system. Easy installations, the ability to perform in demanding environments and labor savings are the reasons nonmetallic conduit fittings are increasingly the fitting of choice. FEATURES: Lightweight yet offers high impact and tensile strength;Chemical resistant to a wide range of acids, al
Long Description	40STD4030 4"x30D PVC STD ELBOW SPxSP SCH40 KRALOY
Product Type	4"X30D PVC STD Elbow SPXSP SCH40 Kraloy
Extra Long Description	MFIT 078573 4"x30D PVC STD ELBOW SP

Manufacturer Information

Brand	Multi Fittings Corp
	Kraloy
GTIN	00622454785731
Manufacturers Part Number	078573
UPC	888636

Taxonomies, Classifications, and Categories

Category Description	PVC ELBOWS
Type	STD ELBOW

Trade Size

Trade Size	4"

Packaging

Carton	1
Package	12
Weight Per Each	4.2 (lbs/each)

Uses, Certifications, and Standards


Standard	UL 651

CSA C22.2 NO211.2 UL 651

RIGID PVC CONDUIT
CONDUIT RIGIDE EN PVC

30° SCH40 BEND PE / 30° SCH40 COUDE BU

ISSUE DATE: DATE D'EMISSION:	2009 02 20
SUPERSEDES: REMPLACE:	2003 04 02



	CODE	Size Grosseur	L Ref.	R Ref.	T Ref.
KRALOY	# 068626 * 069247 # 078570	63mm (2.5")	308mm (12.125")	267mm (10.50")	89mm (3.50")
KRALOY	# 068627 * 069248 # 078571	78mm (3.0")	379mm (14.938")	330mm (13.0")	102mm (4.0")
KRALOY	# 068628 * 069249 # 078572	91mm (3.50")	479mm (18.875")	381mm (15.0")	140mm (5.50")
KRALOY	# 068629 * 069250 # 078573	103mm (4.0")	508mm (20.0")	406mm (16.0")	152mm (6.0")
KRALOY	# 068631 * 069251 # 078574	129mm (5.0")	813mm (32.0")	610mm (24.0")	248mm (9.75")
KRALOY	# 068632 * 069252 # 078575	155mm (6.0")	1016mm (40.0")	762mm (30.0")	305mm (12.0")

#– UL APPROVED / APPROUVES
*– CSA CERTIFIED / CERTIFIE
L– LENGTH OF PIPE BEFORE BENDING / LONGUEUR DU TUYAU AVANT D'ETRE COURBE