ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



404010AST DOUBLE MC CONNECTORS

ARLINGTON INDUSTRIES

Catalog Number	404010AST
Manufacturer	ARLINGTON INDUSTRIES
Description	MC Cable Connector, 3/8 in Trade Size, Die-Cast Zinc Material, Silver, 2.467 in Length, 2.115 in Diameter, Insulated, Snap-In Connection, 0.187 lb/EA
Weight per unit	0.1900 (lbs/each)
Product Category	Liquid Tight Fittings

Features

Material	Zinc

Material, Color, and Finish

Color	Silver
Finish	Silver

Dimensions and Weight

Size	L(2.467) x W(2.115) x H(0.950)

Descriptions

Construction	Die-Cast
Description	DOUBLE MC CONNECTORS
Long Description	Duplex zinc die-cast, 3/8" Knockout MC cable connector snaps quickly on to the conduit with a removable screw in spring steel clip and then snaps into knockout with external spring steel clip, no tools required. Concrete tight when taped. Red tinted internal clip indicates easier insertion of conduit and comes with Insulated throat.
Product Type	SNAP2IT Snap In Duplex 4040
Special Features	Insulated Throat Duplex Connector
Extra Long Description	ARL 404010AST SNAP2IT SNAP IN DUPLE

Manufacturer Information

Brand	ARLINGTON
GTIN	00018997405333
UPC	801230

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	Snap-on

Trade Size

Trade Size	3/8

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Packaging

Carton	25
Package	100
Weight Per Each	0.1900 (lbs/each)

Uses, Certifications, and Standards

Application	AC/MC/HCF/MCI-A/AC90/ACG90/Flex/MC-PCS
Standard	cULus

Made in USA

SNAP2IT® MC Cable Connectors

Largest Line. Widest Cable Ranges. Fastest Installation.



CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	DESCRIPTION	CABLE OUTSIDE DIA (OD)	UNIT/STD PKG
4010AST	40355	Snap in, 1/2" KO w insulated throat	.405 to .610	50/500
5010AST	00517	Snap in, 1/2" KO w insulated throat	.580 to .780	25/250
505010AST	50720	Duplex Snap in, 3/4" KO w insulated throat	(2) .590 to .820	25/25
4110ST	00728	Snap in, 1/2" KO	.525 to .705	50/500
414110ST	00729	Duplex Snap in, 1/2" KO	(2) .525 to .640	25/100
4141107ST	22095	Duplex Snap in, 3/4" KO	(2) .525 to .690	25/25

c UL us



4141107ST

Arlington's zinc diecast **SNAP2IT®** fittings are the *easiest to insert* snap-on connectors. And they handle the widest variety of cables!

- **Easiest installation**
  New and improved design delivers the easiest cable insertion.
- **Widest total cable ranges**
  Our Snap2It® connector line accommodates cables from 14/2 to 3/3.
- **Widest variety of cables**
  For AC, MC, HCF, MC continuous corrugated aluminum cable, MCI-A cables (steel and aluminum), AC90 and ACG90.

These Snap2It connectors fit the NEW MC-PCS and MC-PCS HCF CABLE *(lighting and low voltage circuits in same cable)* **and offer the GREATEST TIME-SAVINGS.**

- Super-secure installation in new work or retrofit
- Connector is removable, reusable
- Fully assembled – Ready to use
- Concrete-tight when taped

Easiest cable insertion. NO TOOLS! Secure hold.

Arlington

www.aifittings.com

SNAP2IT® MC Cable Connectors

Largest Line. Widest Cable Ranges. Fastest Installation.

Snap2It Connectors with Insulated Throat and Angled Two-prong Clip

Our 3810AST through 7510AST **SNAP2IT®** connectors install just as fast and cost the same as our other Snap2It fittings, but **cable insertion is even easier!**

- **Easy installation** snap cable into fitting – assembly into box...No tools!
- Angled clip locks onto MC cable No pullout
- **Removal, reusable**
  From cable: Loosen screw on top of connector. Pull cable out.
  From box: Slip screwdriver under Snap-Tite ring and twist (photo on back).



4010AST
Exploded View/Components





7510AST
Back view



LARGER SIZES

CATALOG NUMBER / UPC/DCI/NAED MFG. #01 8997	CABLE (OD) OUTSIDE DIAMETER	CABLE TYPE	CABLE SIZES	UNIT PKG	STD PKG
3810AST 00385 	.370 to .510	**For steel and aluminum:** MC/HCF/AC *NEW* MC-PCS MCI-A	14/2 and 12/2 with and w/o ground; 14/3 and 12/3	50	500
	.370 to .510	AC90, ACG90	14/2, 14/3, 12/2, 12/3		
383810AST 10937 Duplex 		Flexible metal conduit	3/8" Flex* .560 to .610	25	100
4010AST 40355 	.405 to .610	**For steel and aluminum:** MC/HCF/AC *NEW* MC-PCS	14/2, 14/3, 14/4, 12/2, 12/3, 12/4, 10/2, 10/3	50	500
	.405 to .580	MCI-A			
404010AST 40533 Duplex 	.405 to .610	AC90, ACG90		25	100
		Flexible metal conduit	3/8" Flex* .560 to .610		
5010AST 1/2" KO 00517 	.580 to .780	**For steel and aluminum:** MC/HCF/AC *NEW* MC-PCS	10/3, 10/4, 8/2, 8/3, 8/4 6/2, 6/3	25	250
	.610 to .780	MCI-A			
	.550 to .850	AC90, ACG90	10/3, 10/4, 8/2, 8/3		
505010AST 50720 Duplex 3/4" KO 		Flexible metal conduit	1/2" Flex* .590 to .820	25	25
7510AST 3/4" KO 55090 	.895 to 1.035	**For steel and aluminum:** MC/HCF/AC MCI-A	8/4, 6/4, 6/3	25	25
	.900 to .970	AC90	6/3, 4/4, 4/3, 3/3		
		Flexible metal conduit	3/4" Flex* 1.045 to 1.035		

Check that the cable's outer diameter (OD) listed by the cable manufacturer is within the OD cable range listed for the fitting. The cable jacket should never be able to go through the end stop (of fitting.) *CSA Listed w/ anti-short bushing ONLY

Made in USA

Single (Straight & 90 degree) • **Duplex**

for New Work and Retrofit

90 Degree Snap2It® Connectors

Arlington's snap in connectors save time by eliminating the multiple steps required for a 90 degree 2-screw connector. And they COST THE SAME AS A TWO-SCREW, 90 degree connector.



CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	CABLE TYPE	CABLE (OD) OUTSIDE DIAMETER	CABLE SIZES	UNIT PKG	STD PKG
38900ST	04098	**MC-PCS CABLE**	.440 to .610	14/2 and 12/2 w/ and w/o ground 14/3, 14/4, 12/3, 12/4, 10/2, 10/3	25	250
		MC/HCF/AC Steel & Aluminum	.440 to .610			
38900AST with insulated throat	04093	**MCI-A** Steel & Aluminum	.440 to .550			
		AC90, ACG90	.440 to .550		25	250
		Flexible Metal Conduit Steel & Aluminum	3/8" Flex* .560 to .610			
Tinted red inside fitting		**MC-PCS CABLE**	.405 to .605			
40900ST	04099	**MC/HCF/AC** Steel & Aluminum	.480 to .610	14/3, 12/2 and 12/3 w/ and w/o ground 14/4, 12/4, 10/2, 10/3	25	250
40900AST with insulated throat	04092	**MCI-A** Steel & Aluminum	.480 to .580			
		AC90, ACG90	.480 to .550		25	250
		Flexible Metal Conduit Steel & Aluminum	3/8" Flex* .560 to .610			

*CSA Listed w/ anti-short bushing ONLY

38900ST


38900AST with insulated throat


40900ST RED Tint inside


40900AST with insulated throat, RED Tint inside

for use in INSTALLED BOXES • RETROFIT





Push assembly into box...



...snap it into the box. Fast and easy. No tools required!

Arlington's one-piece **RETROFIT SNAP2IT®** fittings are *easy to use in **OLD WORK** installations.* They're ideal for adding additional circuits to a load center. And you get the same time-savings in a retrofit installation as you do in new work!

Quick, easy installation – NO TOOLS required.

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	CABLE TYPE	CABLE (OD) OUTSIDE DIA	CABLE SIZES	UNIT/STD PKG
38RAST with insulated throat	13586	**MC/HCF/AC** Steel & Aluminum	.405 to .605	14/2 and 12/2 w/ and w/o ground 14/3, 14/4, 12/3, 12/4, 10/2, 10/3	25/25
		MCI-A Steel & Aluminum	.440 to .550		
		AC90, ACG90	.440 to .550		
		Flexible Metal Conduit Steel & Aluminum	3/8" Flex* .405 to .605		
40RAST with insulated throat Tinted RED inside fitting	13587	**MC/HCF/AC** Steel & Aluminum	.485 to .610	14/3, 12/2 and 12/3 w/ and w/o ground 14/4, 12/4, 10/2, 10/3	25/25
		MCI-A Steel & Aluminum	.480 to .610		
		AC90, ACG90	.480 to .550		
		Flexible Metal Conduit Steel & Aluminum	3/8" Flex* .405 to .610		

*CSA Listed w/ anti-short bushing ONLY


Front


Back 38RAST


Back 40RAST RED Tint inside

Check that the cable's outer diameter (OD) listed by the cable manufacturer is within the OD cable range listed for the fitting. The cable jacket should never be able to go through the end stop (of fitting).

Arlington

www.aifittings.com

Made in USA

SNAP2IT® MC Cable Connectors

for NEW WORK

Snap2It® Connectors

Designed for new construction, this **SNAP2IT®** series offers quick, easy snap-in installation into cable and into box. NO TOOLS required.

SAVE 17 seconds per connector

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	CABLE TYPE	CABLE (OD) OUTSIDE DIA	CABLE SIZES	UNIT/STD PKG
*** WITH INSULATED THROAT**					
		MC-PCS CABLE	.405 to .605	14/2 and 12/2 w/ and w/o ground 14/3, 14/4, 12/3, 12/4, 10/2, 10/3	
38AST *	00070	**MC/HCF/AC** Steel & Aluminum	.405 to .605		50/500
380ST	00381	**MCI-A** Steel & Aluminum	.405 to .605		50/500
380AST *	00382	**AC90, ACG90**	.405 to .605		50/500
3838AST* Duplex	36230	**Flexible Metal Conduit** Steel & Aluminum (RWFMC)	3/8" Flex** .405 to .605		25/100
WITH INSULATED THROAT, TINTED RED INSIDE OPEN TANG DESIGN					
		MC-PCS CABLE	.485 to .610	14/3, 12/2 and 12/3 w/ and w/o ground 14/4, 12/4, 10/2, 10/3	
40AST	00041	**MC/HCF/AC** Steel & Aluminum	.485 to .610		50/500
400AST	40347	**MCI-A** Aluminum	.485 to .610		50/500
4040AST* Duplex	40351	**AC90, ACG90**			25/100
		Flexible Metal Conduit Steel & Aluminum	3/8" Flex** .485 to .610		

**Flex CSA Listed w/ anti-short bushing ONLY



Snap fitting onto cable... twist clockwise



...snap assembly into the box!

EASY TO INSTALL

EASY TO REMOVE and REUSE...


To remove from box, lift Snap-Tite® ring with a screwdriver and twist off.

PRODUCT COMPARISON


38AST


40AST

RED TINT inside means OPEN TANG Design

More room inside for easy insertion of wires...redesigned snap ring makes it easier than ever to snap fitting into box


3838AST


38AST


40AST


RED Tint inside

4040AST

Check that the cable's outer diameter (OD) listed by the cable manufacturer is within the OD cable range listed for the fitting. The cable jacket should never be able to go through the end stop (of fitting).

Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Patented

©2015 Arlington Industries Inc. REV0318 50M

Distributed by