ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



595DC2 3/8" PVC JACKETED CABLE CONN

NSI INDUSTRIES

Catalog Number	595DC2
Manufacturer	NSI INDUSTRIES
Description	Mighty-Seal Jacketed MC Cable Connector3/8" PVC MC/TECK CABLE CONNECTOR
Weight per unit	0.1900 (lbs/each)
Product Category	Liquid Tight Fittings

Features

Connector Type	Jacketed MC/TECK
Material	Zinc Die Cast
Number Of Conductors	1 Cable
Angle	180 Deg
Media	Yes

Material, Color, and Finish

Finish	Ball burnish

Dimensions and Weight

Size	3/8

Descriptions

Description	3/8" PVC JACKETED CABLE CONN
Features	Time Saver: Ideal for Parking Decks/Lot Cable, or Teck cable to box or enclosure.
Long Description	Mighty-Seal Jacketed MC Cable Connector3/8" PVC MC/TECK CABLE CONNECTOR
Product Type	3/8 In PVC JCKTD MC Conn, Box Of 15
Special Features	Raintight/Concrete-Tight
Extra Long Description	BPT 595-DC2 3/8 IN Pvc Jcktd Mc Con

Manufacturer Information

Brand	Bridgeport
	Nsi Industries
GTIN	00781747155955
Manufacturers Part Number	595-DC2
	595DC2
UPC	884739

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	CONNECTOR

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Trade Size

Trade Size	3/8

Packaging

Carton	15
Package	60
Weight Per Each	0.1900 (lbs/each)

Uses, Certifications, and Standards

Application	Recommended cable types with 12/2 to 10/3 PVC Jacket MC Cable or TECK Cable .50 - .61. RainTight and ConcreteTight
Standard	cULus

Bridgeport Fittings Inc.
705 Lordship Blvd.
Stratford, CT 06615

Phone: 203-377-5944
Fax: 203-381-3488

Mighty-Seal JMC/Teck Connectors

Images





Download Photo Image Download Dimensional Image

Dimension A in Inches:	1-3/4
Dimension B in Inches:	17/32
Dimension C in Inches:	1-7/32

Application

Recommended cable types with 12/2 to 10/3 PVC Jacket MC Cable or TECK Cable .50 - .61. RainTight and ConcreteTight

Product Information

Material:	Zinc Die Cast
Finish:	Ball burnished, mirror smooth

Certifications & Codes:

CSA File Number:	A-A-50552
Federal Specification Number:	A-A-50552
NEMA Standard:	FB-1
UL File Number:	E20534
UL Standard:	UL-514B
UNSPSC:	39121419
Patent Number:	6,737,584

Catalog ID: 595-DC2

UPC Number: 781747155955

Description: Mighty-Seal® Jacketed MC Cable Connector3/8" PVC MC/TECK CABLE CONNECTOR

Application: Recommended cable types with 12/2 to 10/3 PVC Jacket MC Cable or TECK Cable .50 - .61. RainTight and ConcreteTight

Trade Size: 3/8

Std Pkg Qty: 60

Unit Qty: 15