ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
5617 Andrews Hwy
Odessa, TX 79762-0000
Phone: 4323660008
Fax: 4323666045

6150WH 6" FRST DM WHITE SF RNG WL

COOPER LIGHTING SOLUTIONS

Catalog Number	6150WH
Manufacturer	COOPER LIGHTING SOLUTIONS
Description	Frost Dome Glass Lens, Recessed Mount, 8.375 in Length, 8.0 in Width, 4.375 in Height, 0.87 lb
Weight per unit	0.8700 (lbs/each)
Product Category	Lighting Accessories

Features

Fixture Type	Trim
Material	POLYMER

Material, Color, and Finish

Style	(blank)

Dimensions and Weight

Diameter	6 INCH
Size	8.188 IN Length 4.438 IN Width 8.0 IN Height

Descriptions

Construction	N/A
Description	6" FRST DM WHITE SF RNG WL
Long Description	6" Frost Dome Glass Lens, White Plastic Self-Flange Ring, Showerlight
Product Type	6" Frost Lens Showerlight, WH Plastic SF
Special Features	Frost etched glass lens
Extra Long Description	ECL 6150WH 6" FROST LENS SHOWERLIGH

Manufacturer Information

Brand	HALO
	Cooper Lighting Solutions
GTIN	00080083743391
UPC	783363

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	6" 6100 and 6200 Trim

Packaging

Carton	1
Weight Per Each	0.8700 (lbs/each)

Uses, Certifications, and Standards

Mounting	Recessed
Standard	UL/cULus Listed;Wet Locations

E26 6" Trim Series


DESCRIPTION

Frost glass dome lens trim with self-flange in the 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.

Catalog #		Type	
Project			
Comments		Date	
Prepared by			

SPECIFICATION FEATURES

- Low profile frost dome glass lens
- Wet location showerlight
- Torsion spring retention
- Non-conductive "Dead Front" polymer (plastic) trim ring and glass lens
- Socket supporting internal reflector
- Self-flanged trim ring sized to hide gaps caused by construction tolerances.



Dimensions:
A: 5-1/8" [130mm]
H: 4-1/5" [107mm]
OD: 7-3/4" [197mm]

Housings		Max Lamp Compatibility
H7ICT	H7ICAT	29W A19, 39W PAR30S
H7RICT	H7RICAT	
E7ICAT	E7RICAT	
H7UICAT		43W A19, 50W PAR30S
H7ICTNB		29W A19, 39W PAR30S
H7ICATNB		
E7ICATNB		
H27ICAT	E27ICAT	29W A19, 39W PAR30S
H27RICAT	E27RICAT	
H7T	E7TAT	60W A19, 60W PAR30S
H7TCP		
H7RT	E7RTAT	
H7TNB	E7TATNB	60W A19, 60W PAR30S
H27T	E27TAT	60W A19, 60W PAR30S
H27RT	E27RTAT	

Compatible with Halogen, Incandescent, LED* or CFL* lamps.



6150WH
White Reflector



6150SN
Satin Nickel Reflector



6150TBZ
Tuscan Bronze Reflector

ORDERING INFORMATION

SAMPLE NUMBER: 6150WH

Trim	Finish
6150= 6" Frost Dome Glass Lens, Self-flange	**WH**=White trim **SN**=Satin nickel trim **TBZ**=Tuscan bronze trim

HALO HOUSING COMPATIBILITY

Trim #	Style	H7ICT	H7ICAT	H7RICT	H7RICAT	E7ICAT	E7RICAT	H7UICAT	H7ICTNB
6150	Showerlight	•	•	•	•	•	•	•	•

H7ICATNB	E7ICATNB	H27ICAT	H27RICAT	E27ICAT	E27RICAT		
•	•	•	•	•	•		

H7T	H7TCP	H7RT	E7TAT	E7RTAT	H7TNB	E7TATNB	H27T
•	•	•	•	•	•	•	•

H27RT	E27TAT	E27RTAT					
•	•	•					

For use in select other's housings, refer to U.L. classification list at www.eaton.com/lighting/legal.

*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Eaton does not warranty the lamp.

6150

6-Inch Frost Dome Glass Lens, Self-flange

Showerlight

c UL us LISTED
For use in Halo listed housings.

CLASSIFIED c UL us
Select trims are classified for use in others housings.
See www.eaton.com/lighting/legal.

Powering Business Worldwide

Eaton
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.eaton.com/lighting

Specifications and dimensions subject to change without notice.