Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



65931 20W LED BULLET SECURITY FLOOD W/SMART CAMERA - BLK

SATCO

Catalog Number	65931
Manufacturer	SATCO
Description	20 Watt Bullet Outdoor SMART Security Light with Camera - Starfish Enabled - 3K/4K/5K CCT Selectable - Black Finish
Weight per unit	1.4 (lbs/each)
Product Category	Lighting

Features

Lamp Type	LED
Number Of Lamps	2
Power Factor	N/A
Power Rating	20
Reflector Type	Semi-Frost
Socket Type	Integrated
Voltage Rating	120 to 277
Amperage Rating	0.167 to 0.722

Material, Color, and Finish

Style	Utility
Fixture Material	Die-Cast Aluminum / Plastic

Dimensions and Weight

Size	W:8.60 H:6.31 E:7.32

Descriptions

Description	20W LED BULLET SECURITY FLOOD W/SMART CAMERA - BLK
Long Description	20 Watt Bullet Outdoor SMART Security Light with Camera - Starfish Enabled - 3K/4K/5K CCT Selectable - Black Finish
Product Type	Bullet Sec LGT W/ Cam-Bla
Special Features	Warranty: 1-Year ; Installation Notes: Designed for Recessed or External Junction Boxes ; FCC Compliant: True ; Cct Selectable: True ; CCT (Kelvin Temp): 3000K/4000K/5000K ; Hours Rated: 50000 ; Beam Angle (degree): 70 ; Indoor Outdoor: Outdoor ; IP Rating: IP65 ; Lens Finish: Semi-Frost ; Lens Material: Polycarbonate (PC) ; Operating Temp: -20C (-4F) to +45C (+113F) ; Watts: 20W ; Lumens: 1600L/1750L ; Sensor Field Of View: 90 to 100 degrees
Extra Long Description	SATCO 65/931 BULLET SEC LGT W/ CAM-

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Manufacturer Information

Brand	Satco
	Nuvo
GTIN	00045923657603
Manufacturers Part Number	65/931
UPC	885860

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Commercial LED

Packaging

Carton	1
Weight Per Each	1.4 (lbs/each)

Uses, Certifications, and Standards

Application	Outdoor
Frequency Rating	50/60
Environmental Conditions	Wet
Standard	cETLus - Listed

Project Name

Location | Prepared By



NUVO 65-931

BULLET SEC LGT W/ CAM-BLA

Notes

[www] 10-30-2024 01:08:20

General

Status	Active
Finish	Black
Wattage	20W
CCT (Kelvin)	3000K/4000K/5000K
Color Temperature	Soft White to Natural Light
Width (in.)	8.6
Height (in.)	6.31
Extension (in.)	7.32
Indoor or Outdoor Fixture	Outdoor

Smart Product Info

IOT Enabled	Yes
Integrated Camera	Yes
Operational Humidity	5% - 95%
Communication Protocol	WiFi-2.4GHz; 802.11b/g/n; WPA/WPA2; WPA-PSK/WPA2-PSK
Voice Assistants Supported	Alexa; Google Home; Siri
Software Supported	Tuya/Starfish APP; AWS Cloud Security Servers
Storage Capacity	32GB SD Card Included; Optional 128GB Max SD Card

Specifications

Technology	LED
CRI	80
Lumen Output	1600L/1750L
Rated Hours	50000
Voltage	120V-277V
Dimmable	Yes-Dimmable
Dimming Note	Only with Starfish App
Beam Angle	70
Operating Temperature	-20C (-4F) to +45C (+113F)
Weight (lb.)	1.43
Fixture Material	Die-Cast Aluminum / Plastic
Fixture Type	Security Camera

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Additional Information	CCT Selectability is done via physical switch on unit at installation
Specification Note	3000K at 1600 Lumens; 4000K/5000K at 1750 Lumens
Installation Notes	Designed for Recessed or External Junction Boxes
Includes	Mounting hardware and accessories
Warranty	3 Year Limited - Fixtures

Copyright 2023 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
https://www.satco.com/