



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ABC10R 10A 250V 1/4X1-1/4 Fa Ceramic Fuse *Bussmann Fuses*

Catalog Number	ABC10R
Manufacturer	Bussmann Fuses
Description	Fuse, Fast Acting Fuse Speed, 4 H @ 100%;60 Min @ 135%;120 S @ 200% Response Time, Ferrule End X Ferrule End Connection, 10 A, 250 V Ac;125 V DC, Ceramic (Tube);Brass (End Cap) Material, Ferrule Terminal, 0.250 In Diameter, 1.292 In Overall Length, 0.01 LB
Weight per unit	0.0100 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	10 A
connection	Ferrule End X Ferrule End
dimensions	1.2500 IN X 0.2500 IN X 0.2500 IN
type of indicators	Non-Indicating

Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

Descriptions

Description	10A 250V 1/4X1-1/4 FA CERAMIC FUSE
extra long description	BUSS ABC-10-R ABC 10A BUSS FA 5-IN
Features	Fast-acting, ceramic tube 1/4" x 1-1/4" ferrule fuse designed to UL 248-14 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation. Eaton's ABC fast-acting, ceramic body tube 1/4" x 1-1/4" fuses are designed with higher interrupting ratings and voltage ratings to UL 248-14 for overcurrent protection of electronic circuits. This is a RoHS compliant fuse. Order in cartridge fuse form
Special Features	Interrupt Rating 200 Amp at 250 Vac, 10000 Amp at 125 Vac/Vdc, Material Ceramic Tube, Nickel Plated Brass Endcap, ROHS Compliant

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712646161
UPC	051712646161

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Fast-Acting Fuse



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	5
Weight Per each	0.01

Uses, Certifications, and Standards

standard	RoHS Compliant,CE Marked
----------	--------------------------