



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F032841XPEC03SL 32W T8 48" Oct XP 41K 85cri

Sylvania-Ledvance

Catalog Number	F032841XPEC03SL
Manufacturer	Sylvania-Ledvance
Description	32W, 48" Mol, T8 Octron XP Extended Performance Lamp, 4100K Color Temperature, Rare Earth Phosphor, 85 Cri, Suitable For Is or RS Operation, Ecologic, Safeline Shatter Resistant Coating to Help Contain Glass and Other Components Should The Lamp Break
Weight per unit	0.4500 (lbs/each)
Product Category	Shatter Resistant Fluorescent

Features

amperage rating	Ballast Dependent
average life	36000
Base	Medium Bipin
bulb type	T8
Lamp Type	RAPID START
lumens	2,940
Shape	T8
start type	Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	32

Material, Color, and Finish

color rendering index (cri)	85
color temperature	4100
Finish	Safeline

Dimensions and Weight

Diameter	1
Length	47.78

Descriptions

Description	32W T8 48" OCT XP 41K 85CRI
extra long description	SYL FO32/841/XP/ECO3/SL/22278 FO328
Long Description	32W, 48" MOL, T8 OCTRON XP Extended Performance lamp, 4100K color temperature, rare earth phosphor, 85 CRI, suitable for IS or RS operation, ECOLOGIC, SAFELINE shatter resistant coating to help contain glass and other components should the lamp break
Product Type	F032841XPEC03SL 30/CS 1/Sku



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135222788
Manufacturers Part Number	FO32/841/XP/ECO3/SL/22278
UPC	046135222788

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	30
Weight Per each	0.45

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------