



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NON100 100A 250V One-Time Class H Fuse

Bussmann Fuses

Catalog Number	NON100
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series Non Fuse, Supplemental One-Time Fuse, Non Current Limiting, Light Duty Circuit Locations, 100 A, Class H, Non-Indicating, Blade End X Blade End, 50 Kaic At 125 VDC, 10 Kaic At 250 Vac, Standard, 5, 250 V, 125 VDC
Weight per unit	0.3000 (lbs/each)
Product Category	Renewable & Non-Renewable

Features

amperage rating	100
class	Class H
connection	Blade End X Blade End
dimensions	1.1250 IN X 1.1250 IN X 5.8750 IN
interrupt rating	10:50
media	Yes
Voltage Rating	250 VAC, 125 VDC

Dimensions and Weight

Size	1.060 In Diameter X 5.88 In Length
------	------------------------------------

Descriptions

Description	100A 250V ONE-TIME CLASS H FUSE
extra long description	BUSS NON-100 BUSS ONE TIME FUSE
Features	Basic Protection 250Vac (NON) and 600Vac (NOS), 1/8a -600A General Purpose One-time fuses
Long Description	Eaton Bussmann series NON fuse, Supplemental one-time fuse, Non current limiting, Light duty circuit locations, 100 A, Class H, Non-indicating, Blade end x blade end, 50 kAIC at 125 Vdc, 10 kAIC at 250 Vac, Standard, 5, 250 V, 125 Vdc
Product Type	Buss One Time Fuse
Special Features	Non current limiting

Manufacturer Information

Brand	COOPER BUSSMANN
GTIN	00051712101684
Manufacturers Part Number	NON-100
UPC	051712101684

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FUSE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	5
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	CE Marked