ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



LR34 3/4" PVC TYPE LR CONDULET

CANTEX,INC

Catalog Number	LR34
Manufacturer	CANTEX,INC
Description	CANTEX 5133651 is a 3/4 in. Conduit Body Type LR which provides pull, splice, and tap access for conductors in a conduit system along with a change in direction
Weight per unit	0.4670 (lbs/each)
Product Category	PVC Conduit Fittings & Accy

Dimensions and Weight

Size	3/4

Descriptions

Description	3/4" PVC TYPE LR CONDULET
Features	CANTEX 5133651 is a 3/4 in. Conduit Body Type LR which provides pull, splice, and tap access for conductors in a conduit system along with a change in direction
Long Description	CANTEX 5133651 is a 3/4 in. Conduit Body Type LR which provides pull, splice, and tap access for conductors in a conduit system along with a change in direction
Product Type	3/4 Ul-LR Access FTG
Extra Long Description	CTX 5133651 3/4 UL-LR ACCESS FTG

Manufacturer Information

Brand	PVC & Accessories
	CANTEX INC.
GTIN	00088700567740
Manufacturers Part Number	5133651
UPC	881780

Taxonomies, Classifications, and Categories

Category Description	PVC CONDULETS
Type	3/4 in. Conduit Body Type LR

Trade Size

Trade Size	3/4

Packaging

Carton	15
Weight Per Each	0.4670 (lbs/each)

Uses, Certifications, and Standards

Standard	UL Listed;UL, Made in USA

Conduit Bodies

Conduit Bodies - Type LR

1/2"THROUGH 2"




Conduit Body Type LR provides pull, splice, and tap access for conductors in a conduit system along with a change in direction. Type LR Conduit Bodies are used to make a 90-degree turn in a conduit run with one opening on top and one opening exiting the right side of the cover.

- Durable non-conductive PVC will not rust or corrode
- For use with Schedule 40 & 80 conduit
- Includes lid, gasket, and screws
- UL listed
- Made in USA

2-1/2"THROUGH 4"





Part Number	Trade Size	Carton Quantity	"A"	"B"	"C"	"D'	"E"	Volume Cu. In.	3-Wire Fill
5133650	1/2	25	1.313	1.438	4.250	4.000	.875	4.3	#6 or smaller
5133651	3/4	15	1.500	1.625	4.938	4.625	1.063	6.5	#6 or smaller
5133652	1	10	1.750	2.000	6.000	5.375	1.313	11.8	#6 or smaller
5133653	1-1/4	10	2.438	2.438	7.625	7.188	1.625	25.0	XHHW #1
5133654	1-1/2	10	2.625	2.813	8.563	8.000	1.938	36.5	XHHW #2/0
5133655	2	5	3.063	3.438	9.875	9.500	2.375	63.5	XHHW #4/0
5133658	2-1/2	5	4.625	4.625	14.938	12.750	2.875	198.0	XHHW 500 MCM
5133656	3	5	4.625	4.625	15.000	12.813	3.500	198.0	XHHW 500 MCM
5133659	3-1/2	4	5.625	5.500	16.188	12.813	4.000	305.0	XHHW 500 MCM
5133657	4	4	5.625	5.500	15.938	12.813	4.500	305.0	XHHW 500 MCM

Dimensions are nominal



SINGLE SOURCE FOR PVC ELECTRICAL

CANTEX offers a complete line of PVC Conduit Bodies as part of a full line PVC electrical products. The CANTEX Conduit Body line includes multiple sizes of Type LB, Type LL, Type LR, Type T, Type C, and Type E Conduit Bodies.

With several decades of experience manufacturing PVC conduit, fittings and accessories, you can trust CANTEX to provide quality products. To see our complete line of PVC Conduit Bodies or our full line of PVC electrical products visit www.cantexinc.com.