ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

PF1112T 240V POOL TIME SW

INTERMATIC INC.

Catalog Number	PF1112T
Manufacturer	INTERMATIC INC.
Description	Swim Pool/Spa Controller, 240 V ac, DPST Switch Action, Wall Mount, +33 to +42 °F, 12 x 12 x 4-1/4 in Size, 10 lb
Weight per unit	11.2 (lbs/each)
Product Category	Temperature Controls

Features

Contact Configuration	2 NO
Contact Rating	30 AMP @ 120/208/240 VAC (Resistive, Inductive, Tungsten)
Poles	2
Voltage Rating	240
Action	DPST
Amperage Rating	92 (Per Leg) 168 Max
Motor Power	2 HP @ 120 VAC, 5 HP @ 240 VAC

Dimensions and Weight

Size	12H X 12 WIDTH X 4-1/4 DEPTH IN, 30.5 HEIGHT X 30.5 WIDTH X 10.8 DEPTH CM

Descriptions

Description	240V POOL TIME SW
Long Description	Freeze Protection Control Center with Timer and Thermostat for 240V Applications, Type 3R Metal Enclosure
Product Type	Freeze Protection Control Center With Timer and Thermostat F
Special Features	Features: Protects pool/spa equipment against freeze damage, GFCI and switch mounting capabilities, Heavy-duty Type 3R steel Indoor/Outdoor power and load centers, 1 Year Warranty
Extra Long Description	INT PF1112T Freeze Protection Contr

Manufacturer Information

Brand	Intermatic
GTIN	00078275071407
UPC	683341

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	Freeze Protection

Packaging

Carton	1
Weight Per Each	11.2 (lbs/each)

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Uses, Certifications, and Standards

Application	Pool/Spa Control
Enclosure	Type 3R Steel
Frequency Rating	60
Mounting	WALL MOUNT
Operating Temperature	+33 to +42 DEG F, +0.5 to +5.5 DEG C
Standard	cCSAus Certified

The Ultimate Ice Breaker



E.



F.



G.

Rating:
PF1112T, PF1202T
Power Center Rating: 92 A per leg, 168 A max. 120/ 240 VAC or 120/240 VAC single phase, 60 Hz.
Power Center Dimensions: 12" (30.5 cm) H x 12" (30.5 cm) W x 4 ¼" (10.8 cm) D

PF1222TB1
Load Center Rating: 85 A max., 120, 240 VAC or 120, 208 VAC single phase, 60 Hz.
Load Center Dimensions: 20 ¾" (52.7 cm) H x 12 ¾" (32.4 cm) W x 4 ¼" (10.8 cm) D

Thermostat Range: 33°F to 42°F (0.5°C to 5.5°C) with 5°F differential
Switch Rating:
- 30 A Resistive/Inductive, Tungsten or 1000 VA Pilot Duty each pole 120, 208, 240 VAC
- 2 HP (24 FLA), 120 VAC
- 5 HP (28 FLA), 240 VAC

Warranty: 1 year

PF1100 and PF1200 Series
Control System with Freeze Protection and Power or Load Center

- For pools/spas requiring one or two time switches
- Protects pool/spa equipment against freeze damage
- GFCI and switch mounting capabilities
- Turns pump and heater ON when outdoor temperature drops below user-adjustable setpoint on thermostat
- Heavy-duty Type 3R steel Indoor/Outdoor power and load centers

	Model #	Description	Input Voltage	HP	Heater Protection
E.	**PF1112T**	Power Center with (1) Time Switch	240 VAC	3	No
F.	**PF1202T**	Power Center with (2) Time Switches	240 VAC	3	No
G.	**PF1222TB1***	Load Center with (2) Time Switches	240 VAC	3	Yes

**4/8 Breaker base and heater protection*

For replacement parts, trippers and accessories see page 153

Wiring devices may be installed in this power or load center *(order (4) 21T156A standoffs for mounting). See page 154.*