

## 4000® SERIES RACEWAY




Single- and Dual-Channel, Steel Raceway. Easy-to-install and ideal for basic power or communication/low voltage installations.

## CODE REFERENCE

**cULus Listed Raceway:**  
File E4376 Guide RJBT.

**Fittings:**  
File E41751 Guide RJPR.  
Meets Article 386 of NEC.  
Meets Section 12-1600 of CEC.

## System Layout



**NOTE:** Illustration is for showing product applications only.

## KEY

- |   |   |  |  |
|---|---|--|--|
| A. 4010B Blank End Fitting                      | G. 4018 External Elbow                          | K. 4047RF Rectangular Receptacles and Modular Furniture Device Plate | N. 4075DA Bridge Fitting                 |
| B. 4010DFO Entrance End Fitting                 | H. 4018FO Radiused Full Capacity External Elbow | L. 4047RH Device Plate for Rectangular Receptacle and Mousehole      | O. 500 Series Raceway                    |
| C. 4011 Flat Elbow                              | I. 4047BX Duplex Receptacle Device Plate        | M. 4050 Device Mounting Plate with 5507 Series Faceplates            | P. 5507D Duplex Faceplate                |
| D. 4015D Divided Tee                            | J. 4047JX Single Receptacle & Device Plate      |  | Q. 5785 Combination Connector            |
| E. 4017 Internal Elbow                          |   |  | R. 5507RJ Device Plate with two RJ ports |
| F. 4017FO Radiused Full Capacity Internal Elbow |   |  |  |

## COLOR OPTIONS




4000® Series Raceway Part Numbers with a "V" prefix have an ivory finish. Part Numbers with a "G" prefix have a gray finish.

**Custom color options are also available. Consult the factory for more information.**

# 4000<sup>®</sup> SERIES RACEWAY

## 4000 Series Raceway Ordering Information (continued)

### V4050, G4050 Device Mounting Bracket



High impact plastic mounting bracket and trim plate. Overlaps raceway cover for a seamless transition with cover fittings. Accepts 5507 Faceplates, as well as, Wiremold Open System communication modules, Ortronics<sup>®</sup> TracJack and Series II inserts, and Pass & Seymour<sup>®</sup> Activate Series inserts.

For faceplate options, see 5507 Series<sup>™</sup> Faceplates.

### IWE-P, GWE-P Touch-Up Paint Pen



Used for touching up small areas. Contains 0.3 oz. of paint. Available in ivory (IWE-P) and gray (GWE-P).

### IWE-S, GWE-S Spray Paint




Used for touching up large areas. Contains 12 oz. of paint. Available in ivory (IWE-S) and gray (GWE-S).

**NOTE:** Can only be shipped via ground transportation.


## 4047 Series Faceplates Ordering Information

### V4046H-2, G4046H-2 Tap-Off Fitting




Four concentric 1/2" and 3/4" trade size KOs.

### V4047BX, G4047BX Two-Gang Cover One Duplex Receptacle




Accepts 15A or 20A duplex receptacles and 106 style frames when used for communications outlets.

### V4047AX, G4047AX Two-Gang Cover Single Round Opening



Accepts straight blade and locking single receptacles with face diameters of 1.38" to 1.39" [35mm to 36mm].

### V4047BB, G4047BB Two-Gang Cover Two Duplex Receptacles



Accepts 15A or 20A duplex receptacles and 106 style frames.

**NOTE:** Parts identified with this symbol are Certified to Canadian Safety Standards for sale in Canada. When ordering these products, change the "V" color prefix to "CV" or the "G" color prefix to "CG" to denote the Canadian versions.


**NOTE:** All 4047 Series Faceplates provide 1/4" [6.4mm] of overlap on each side of plate.

# 4000<sup>®</sup> SERIES RACEWAY

## 4047 Series Faceplates Ordering Information (continued)


### V4047-2WWTT, G4047-2WWTT

Four-Gang Cover with Two TracJack Mini Adapters



Includes two Pass & Seymour<sup>®</sup> 20A Duplex Receptacles with 12" wire leads installed on bracket. Includes Mini adapter that accepts two Ortronics<sup>®</sup> TracJack inserts.


### V4047UX, G4047UX Bump-Up Device Plate



Accepts four Extron<sup>®</sup> Electronics MAAP single space modules.

### V4047-2WWXX, G4047-2WWXX


Four-Gang Cover with Two Duplex Receptacles Installed



Includes two Pass & Seymour<sup>®</sup> 20A Duplex Receptacles with 12" wire leads installed on bracket.

### V4047VX, G4047VX

Bump-Up Extron<sup>®</sup> AAP Device Plate



Accepts two Extron<sup>®</sup> Electronics AAP single space modules.

## 4000 Series Raceway Interconnectivity Fittings

CONNECTION REQUIRED		USE CATALOG NUMBER
FROM	TO	
4000 Series Raceway	DS4000 Series Raceway	DS4089
4000 Series Raceway	3000 (Tee Connection)	G4074A
4000 Series Raceway	4000 (Tee Connection)	4015/4015FO
4000 Series Raceway w/Divider	4000 w/Divider (Tee Connection)	4015D
4000 Series Raceway	500 Series Raceway	V5785
6000 Series Raceway	4000 (Tee Connection)	6074A
1/2" or 3/4" trade size Conduit or Armored Cable	Cover of 4000 Series Raceway	4064H-2
1/2" trade size Conduit or Armored Cable	End of 4000 Series Raceway	4010B
3/4", 1", or 1 1/4" trade size Conduit or Armored Cable	Back, Side or End of 4000 Series Raceway	4010DFO
1" or 1 1/4" trade size Conduit or Armored Cable	Back or End of 4000 Series Raceway	4010DFC
1/2", 3/4", 1", or 1 1/4" trade size Conduit or Armored Cable	Back of 4000 Series Raceway	4014A
Flush Mounted Wall Box	Back of 4000 Series Raceway	4014A

## 4047 Configurable Cover Plates Number Logic

### 1. For "X", Choose one of the following options:

- V** Ivory & UL Listed      **CV** Ivory & cULus Listed (Canada only)
- G** Gray & UL Listed      **CG** Gray & cULus Listed (Canada only)

### 2. Choose a Plate Configuration:

Two-Gang Plate: **X 4047 Y Y** **Four-Gang Plate: X 4047-2 Y Y Y Y**

### 3. For "Y", Choose any combination of configurations from the options listed below:

- |   |   |
|---|---|
| <b>A.</b> 1.41" [35.8mm] Diameter, Single Round Receptacle        | <b>J.</b> 1.59" [40mm] Diameter, Single Round Receptacle  |
| <b>B.</b> Duplex Receptacle Opening                               | <b>M.</b> Pass & Seymour Activate 2A Mini Adapter Opening with Adapter                              |
| <b>F.</b> Combination Modular Furniture & 2 Keystone Twist Out    | <b>R.</b> Rectangular Receptacle  |
| <b>H.</b> Mouse Hole Twist Out & Grommet                          | <b>S.</b> Ortronics <sup>®</sup> Series II 2A Mini Adapter Opening with Adapter                     |
| <b>T.</b> Ortronics TracJack 2A Mini Adapter Opening with Adapter | <b>W.</b> P&S Light Almond 20 Amp Receptacle pre-pigtailed with 12" wire leads installed on Bracket |
| <b>X.</b> Blank   | <b>Z.</b> 3 Keystone Twist Out  |

### 4. Finished Part Number:

4047      4047-2

NOTE: JJ combination not available.  
For additional colors or configurations, call 1-800-621-0049, option 2.

**NOTE:** Parts identified with this symbol are Certified to Canadian Safety Standards for sale in Canada. When ordering these products, change the "V" color prefix to "CV" or the "G" color prefix to "CG" to denote the Canadian versions.

**NOTE:** All 4047 Series Faceplates provide 1/4" [6.4mm] of overlap on each side of plate.