ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



SI1 CABLE STACKER SI-1

MINNESOTA MINING (3M)

Catalog Number	SI1
Manufacturer	MINNESOTA MINING (3M)
Description	Cable Stacker, #14/2 to #10/2 AWG (Flat) Compatible Wire Size, White, Polypropylene Material, 0.3 in (Round Wire) Diameter, 0.03 lb
Weight per unit	0.7010 (lbs/each)
Product Category	Cable Hanging Mgmt & Accy

Descriptions

Description	CABLE STACKER SI-1
Features	3M™ Cable Stackers are made of plastic and feature a convenient design that is easy to install. RoHS 2011/65/EU Compliant.
Long Description	3M™ Cable Stackers SI-1 and SIFS-1 organize cable runs with convenient space management and aid in identification. The 3M™ Cable Stacker SI-1 centers multiple cables on a 2 X 4 framingmember. The 3M™ Furring Strip Cable Stacker SIFS-1 routes, fastens, and supports CATV, telephone, security and instrumentation cables.
Product Type	3M™ Cable Stackers
Extra Long Description	3M 7000132935 3M™ Cable Stackers

Manufacturer Information

Brand	3M Electrical Products
GTIN	00054007495543
Manufacturers Part Number	7000132935
UPC	054007

Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
Type	Stacker

Availability

Minimum Qty	25

Packaging

Carton	25
Package	250
Weight Per Each	0.7010 (lbs/each)

Uses, Certifications, and Standards

Application	centers multiple cables on a 2 X 4 framing member, allowing simplified compliance with article 300-4-(d) of the National Electrical Code

3M Science. Applied to Life.™

Electrical Solutions you can rely on.

Electrical Products Catalog



Cable Ties and Accessories

3M™ Cable Ties are designed to secure wire bundles and harness components quickly, without slipping. Featuring a self-locking head and a locking mechanism, they are designed to handle temperatures up to 185°F (85°C). Available in several strengths and lengths, including screw mount. Most are plenum rated and USA made.



Cable Ties Part Number Naming Convention

The product name has been changed to better identify the characteristics of each tie.

CT D C T X - P

Example:
Catalog Number: CT4BK18-C

CT	D	C	T	X	-	P

CT = Cable Ties CTB = Mounting Bases	D = Dimensions (inches) Ties = Length Bases = Length X Width	C = Color BK = Black NT = Natural RD = Red BG = Beige	T* = Tensile (pounds) 18 = Miniature 40 = Intermediate 50 = Standard 120 = Light Heavy Duty 175 = Heavy Duty	X = Special Features _ = Standard Tie (Blank) S = Screw Mount A = Adhesive Mount	P = Package Size *(Roman Numeral)* M = 1,000 D = 500 C = 100 L = 50

**Cable Tie Base Part Numbers do not include Tensile.*

Section Page

3M™ Standard Cable Ties....123-129
3M™ Miniature Ties (18 lb., 80 N) - Plenum Rated 123
3M™ Intermediate Ties (30-40 lb., 135-180 N) - Plenum Rated 124
3M™ Standard Ties (50 lb., 220 N) - Plenum Rated....125
3M™ Light Heavy Duty Ties (120 lb., 530 N) - Plenum Rated 126
3M™ Heavy Duty Ties (175 lb., 800 N) - Plenum Rated 127
3M™ Screw Mountable - Plenum Rated 128
3M™ Standard Cable Ties - Assortment Pack 129
3M™ Cable Bases and Stackers 129-130
3M™ Cable Stackers 129
3M™ Cable Tie Mounting Bases....130
3M™ Hook and Loop Reclosable Fasteners....131-132
3M™ Hook and Loop Reclosable Fasteners 131-132
3M™ Dual Lock™ Reclosable Fasteners 132-133
3M™ Dual Lock™ Reclosable Fasteners 132
3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4570....133

3M™ Miniature Ties (18 lb., 80 N) - Plenum Rated

3M™ Miniature Cable Ties are small lightweight cable ties for use in holding applications up to 18 lb. Ties come in UV-resistant black for outdoor and indoor use as well as natural (white) nylon for an economical solution indoors.

Tensile Strength	18 lb (80 N)
Min. Operating Temp.	-40°F (-40°C)
Max. Operating Temp.	185°F (85°C)
Min. Installation Temp.	32°F (0°C)
RoHS 2011/65/EU	Yes
Agency Approvals	
Country of Origin	



Order No.	UPC	Color	UV Resistance	Length	Width	Thickness	Max. Bundle Dia.	Tensile lbf (N)	Items per Bag (Case)
CT4BK18-C	051128-59273	Black	Yes	4.10" (104 mm)	0.10" (3,0 mm)	0.04" (1,0 mm)	0.75" (19,1 mm)	18 (80)	100 (1000)
CT4BK18-M	051128-59274	Black	Yes	4.10" (104 mm)	0.10" (3,0 mm)	0.04" (1,0 mm)	0.75" (19,1 mm)	18 (80)	1000 (10,000)
CT4NT18-C	051128-59275	Natural	No	4.10" (104 mm)	0.10" (3,0 mm)	0.04" (1,0 mm)	0.75" (19,1 mm)	18 (80)	100 (1000)
CT4NT18-M	051128-59276	Natural	No	4.10" (104 mm)	0.10" (3,0 mm)	0.04" (1,0 mm)	0.75" (19,1 mm)	18 (80)	1000 (10,000)
CT6BK18-C	051128-59277	Black	Yes	6.10" (155 mm)	0.10" (3,0 mm)	0.05" (1,3 mm)	1.25" (31,8 mm)	18 (80)	100 (1000)
CT6NT18-C	051128-59278	Natural	No	6.10" (155 mm)	0.10" (3,0 mm)	0.05" (1,3 mm)	1.25" (31,8 mm)	18 (80)	100 (1000)
CT6NT18-M	051128-59279	Natural	No	6.10" (155 mm)	0.10" (3,0 mm)	0.05" (1,3 mm)	1.25" (31,8 mm)	18 (80)	1000 (10,000)
CT8BK18-C	051128-59280	Black	Yes	8.10" (206 mm)	0.10" (3,0 mm)	0.05" (1,3 mm)	2.00" (50,8 mm)	18 (80)	100 (1000)
CT8BK18-M	051128-59281	Black	Yes	8.10" (206 mm)	0.10" (3,0 mm)	0.05" (1,3 mm)	2.00" (50,8 mm)	18 (80)	1000 (10,000)
CT8NT18-C	051128-59282	Natural	No	8.10" (206 mm)	0.10" (3,0 mm)	0.05" (1,3 mm)	2.00" (50,8 mm)	18 (80)	100 (1000)
CT8NT18-M	051128-59283	Natural	No	8.10" (206 mm)	0.10" (3,0 mm)	0.05" (1,3 mm)	2.00" (50,8 mm)	18 (80)	1000 (10,000)

3M™ Intermediate Ties (30-40 lb., 135-180 N) - Plenum Rated

3M™ Intermediate Cable Ties are a great solution for holding applications up to 40 lb. They provide an economical alternative to standard cable ties when higher tensile strength is not required. Ties come in UV-resistant black for outdoor and indoor use as well as natural (white) nylon for an economical solution indoors.

Tensile Strength	30-40 lb (135-180 N)
Min. Operating Temp.	-40°F (-40°C)
Max. Operating Temp.	185°F (85°C)
Min. Installation Temp.	-4°F (-20°C)
RoHS 2011/65/EU	Yes
Agency Approvals	
Country of Origin	



Order No.	UPC	Color	UV Resistance	Length	Width	Thickness	Max. Bundle Dia.	Tensile lbf (N)	Items per Bag (Case)
CT6BK40-C	051128-59284	Black	Yes	5.80" (147 mm)	0.14" (3,6 mm)	0.05" (1,3 mm)	1.25" (31,8 mm)	30 (135)	100 (1000)
CT6BK40-M	051128-59285	Black	Yes	5.80" (147 mm)	0.14" (3,6 mm)	0.05" (1,3 mm)	1.25" (31,8 mm)	30 (135)	1000 (10,000)
CT6NT40-C	051128-59286	Natural	No	5.80" (147 mm)	0.14" (3,6 mm)	0.05" (1,3 mm)	1.25" (31,8 mm)	30 (135)	100 (1000)
CT6NT40-M	051128-59287	Natural	No	5.80" (147 mm)	0.14" (3,6 mm)	0.05" (1,3 mm)	1.25" (31,8 mm)	30 (135)	1000 (10,000)
CT8BK40-C	051128-59288	Black	Yes	8.90" (226 mm)	0.14" (3,6 mm)	0.05" (1,3 mm)	2.00" (50,8 mm)	30 (135)	100 (1000)
CT8BK40-M	051128-59289	Black	Yes	8.90" (226 mm)	0.14" (3,6 mm)	0.05" (1,3 mm)	2.00" (50,8 mm)	30 (135)	1000 (10,000)
CT8NT40-C	051128-59290	Natural	No	8.90" (226 mm)	0.14" (3,6 mm)	0.05" (1,3 mm)	2.00" (50,8 mm)	30 (135)	100 (1000)
CT8NT40-M	051128-59291	Natural	No	8.90" (226 mm)	0.14" (3,6 mm)	0.05" (1,3 mm)	2.00" (50,8 mm)	30 (135)	1000 (10,000)

3M™ Standard Ties (50 lb., 220 N) - Plenum Rated

3M™ Standard Cable Ties are the most common sized ties and provide a standard level of performance for general-use holding applications up to 50 lb. Ties come in UV-resistant black for outdoor and indoor use as well as natural (white) nylon for an economical solution indoors.

Tensile Strength	50 lb (220 N)
Min. Operating Temp.	-40°F (-40°C)
Max. Operating Temp.	185°F (85°C)
Min. Installation Temp.	-4°F (-20°C)
RoHS 2011/65/EU	Yes
Agency Approvals	
Country of Origin	



Order No.	UPC	Color	UV Resistance	Length	Width	Thickness	Max. Bundle Dia.	Tensile lbf. (N)	Items per Bag (Case)
CT8BK50-C	051128-59293	Black	Yes	7.60" (193 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	1.87" (47,5 mm)	50 (220)	100 (1000)
CT8BK50-M	051128-59294	Black	Yes	7.60" (193 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	1.87" (47,5 mm)	50 (220)	1000 (10,000)
CT8NT50-C	051128-59297	Natural	No	7.60" (193 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	1.87" (47,5 mm)	50 (220)	100 (1000)
CT8NT50-M	051128-59299	Natural	No	7.60" (193 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	1.87" (47,5 mm)	50 (220)	1000 (10,000)
CT8RD50-C	051128-59559	Red	No	7.60" (193 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	2.00" (50,8 mm)	50 (220)	100 (1000)
CT11BK50-C	051128-59300	Black	Yes	11.10" (282 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	3.00" (76,2 mm)	50 (220)	100 (1000)
CT11BK50-D	051128-59301	Black	Yes	11.10" (282 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	3.00" (76,2 mm)	50 (220)	500 (5000)
CT11NT50-C	051128-59302	Natural	No	11.10" (282 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	3.00" (76,2 mm)	50 (220)	100 (1000)
CT11NT50-D	051128-59303	Natural	No	11.10" (282 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	3.00" (76,2 mm)	50 (220)	500 (5000)
CT11RD50-C	051128-59560	Red	No	11.10" (282 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	3.00" (76,2 mm)	50 (220)	100 (1000)
CT15BK50-C	051128-59304	Black	Yes	14.60" (371 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	4.00" (101,6 mm)	50 (220)	100 (500)
CT15BK50-D	051128-59305	Black	Yes	14.60" (371 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	4.00" (101,6 mm)	50 (220)	500 (2500)
CT15NT50-C	051128-59307	Natural	No	14.60" (371 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	4.00" (101,6 mm)	50 (220)	100 (500)
CT15NT50-D	051128-59309	Natural	No	14.60" (371 mm)	0.18" (4,6 mm)	0.05" (1,3 mm)	4.00" (101,6 mm)	50 (220)	500 (2500)

3M™ Light Heavy Duty Ties (120 lb., 530 N) - Plenum Rated

3M™ Light Heavy Duty Cable Ties are commonly used in more demanding commercial and industrial jobs when extra strength is required to hold up to 120 lb. Ties come in UV-resistant black for outdoor and indoor use as well as natural (white) nylon for an economical solution indoors.

Tensile Strength	120 lb (530 N)
Min. Operating Temp.	-40°F (-40°C)
Max. Operating Temp.	185°F (85°C)
Min. Installation Temp.	-4°F (-20°C)
RoHS 2011/65/EU	Yes
Agency Approvals	
Country of Origin	

Order No.	UPC	Color	UV Resistance	Length	Width	Thickness	Max. Bundle Dia.	Tensile lbf (N)	Items per Bag (Case)
CT8BK120-L	051128-59310	Black	Yes	9.00" (229 mm)	0.30" (7,6 mm)	0.07" (1,8 mm)	2.00" (50,8 mm)	120 (530)	50 (500)
CT8NT120-L	051128-59311	Natural	No	9.00" (229 mm)	0.30" (7,6 mm)	0.07" (1,8 mm)	2.00" (50,8 mm)	120 (530)	50 (500)
CT15BK120-C	051128-59312	Black	Yes	15.00" (381 mm)	0.30" (7,6 mm)	0.07" (1,8 mm)	4.00" (101,6 mm)	120 (530)	100 (500)
CT15BK120-D	051128-59313	Black	Yes	15.00" (381 mm)	0.30" (7,6 mm)	0.07" (1,8 mm)	4.00" (101,6 mm)	120 (530)	500 (2500)
CT15NT120-C	051128-59315	Natural	No	15.00" (381 mm)	0.30" (7,6 mm)	0.07" (1,8 mm)	4.00" (101,6 mm)	120 (530)	100 (500)
CT15NT120-D	051128-59317	Natural	No	15.00" (381 mm)	0.30" (7,6 mm)	0.07" (1,8 mm)	4.00" (101,6 mm)	120 (530)	500 (2500)

3M™ Heavy Duty Ties (175 lb., 800 N) - Plenum Rated

3M™ Heavy Duty Cable Ties provide an added level of strength plus a larger bundle diameter for heavy duty jobs up to 175 lb. Ties come in UV-resistant black for outdoor and indoor use as well as natural (white) nylon for an economical solution indoors.

The 24" and 36" ties are also suitable for use with UL non-metallic air ducts and air connectors. (Plenum)



Tensile Strength	175 lb (800 N)
Min. Operating Temp.	32°F (0°C)
Max. Operating Temp.	185°F (85°C)
Min. Installation Temp.	32°F (0°C)
RoHS 2011/65/EU	Yes

	CT24BK175-L	CT24NT175-L	CT36BK175-L
UPC	051128-59318	051128-59319	051128-59320
Color	Black	Natural	Black
UV Resistance	Yes	No	Yes
Length	24.00" (610 mm)	24.00" (610 mm)	36.00" (914 mm)
Width	0.34" (8,6 mm)	0.34" (8,6 mm)	0.34" (8,6 mm)
Thickness	0.09" (2,3 mm)	0.09" (2,3 mm)	0.09" (2,3 mm)
Max. Bundle Dia.	7.20" (183 mm)	7.20" (183 mm)	11.00" (279 mm)
Tensile lbf (N)	175 (800)	175 (800)	175 (800)
Items per Bag (Case)	50 (500)	50 (500)	50 (500)
Agency Aproval			
Country of Origin			

	CT36NT175-L	CT48BK175-L	CT48NT175-L
UPC	051128-59321	051128-59322	051128-59323
Color	Natural	Black	Natural
UV Resistance	No	Yes	No
Length	36.00" (914 mm)	47.90" (1217 mm)	47.90" (1217 mm)
Width	0.34" (8,6 mm)	0.36" (9,1 mm)	0.36" (9,1 mm)
Thickness	0.09" (2,3 mm)	0.07" (1,8 mm)	0.07" (1,8 mm)
Max. Bundle Dia.	11.00" (279 mm)	14.60" (372 mm)	14.60" (372 mm)
Tensile lbf (N)	175 (800)	175 (800)	175 (800)
Items per Bag (Case)	50 (500)	50 (500)	50 (500)
Agency Aproval		UL Pending - Not Plenum Rated	UL Pending - Not Plenum Rated
Country of Origin		-	-

3M™ Screw Mountable - Plenum Rated

3M™ Screw Mount Cable Ties allow precise and controlled positioning of standard and heavy duty cables up to 120 lb. The easy-to-use ties can be quickly mounted to walls and structures with screws, bolts or rivets for added security. Ties come in UV-resistant black for outdoor and indoor use as well as natural (white) nylon for an economical solution indoors.

3M™ Screw Mount Cable Ties are suitable for use in air handling spaces (plenum).

*NOTE: UL Listing is pending at this time for **CT15NT120S-D**.*

Stud Size	10
Min. Operating Temp.	-40°F (-40°C)
Max. Operating Temp.	185°F (85°C)
Min. Installation Temp.	-
RoHS 2011/65/EU	Yes
Agency Approvals	
Country of Origin	



Order No.	UPC	Color	UV Resistance	Length	Width	Thickness	Max. Bundle Dia.	Tensile lbf (N)	Items per Bag (Case)
CT8BK50S-C	051128-59292	Black	Yes	8.60" (218 mm)	0.18" (4,6 mm)	0.06" (1,5 mm)	2.00" (50,8 mm)	50 (220)	100 (1000)
CT8BK50S-M	051128-59295	Black	Yes	8.60" (218 mm)	0.18" (4,6 mm)	0.06" (1,5 mm)	2.00" (50,8 mm)	50 (220)	1000 (10,000)
CT8NT50S-C	051128-59296	Natural	No	8.60" (218 mm)	0.18" (4,6 mm)	0.06" (1,5 mm)	2.00" (50,8 mm)	50 (220)	100 (1000)
CT8NT50S-M	051128-59298	Natural	No	8.60" (218 mm)	0.18" (4,6 mm)	0.06" (1,5 mm)	2.00" (50,8 mm)	50 (220)	1000 (10,000)
CT15NT50S-L	051128-59306	Natural	No	15.10" (384 mm)	0.18" (4,6 mm)	0.06" (1,5 mm)	4.00" (102,6 mm)	50 (220)	50 (500)
CT15NT50S-D	051128-59308	Natural	No	15.10" (384 mm)	0.18" (4,6 mm)	0.06" (1,5 mm)	4.00" (102,0 mm)	50 (220)	500 (2500)
CT15NT120S-L	051128-59314	Natural	No	15.70" (399 mm)	0.30" (7,6 mm)	0.07" (1,8 mm)	4.00" (102,0 mm)	120 (530)	50 (500)
CT15NT120S-D	051128-59316	Natural	No	15.70" (399 mm)	0.30" (7,6 mm)	0.07" (1,8 mm)	4.00" (102,0 mm)	120 (530)	500 (2500)

3M™ Standard Cable Ties - Assortment Pack

3M™ Cable Tie Assortment Pack contains 100 of our most commonly used ties. Includes three sizes, four lengths and both colors.

Min. Operating Temp.	-40°F (-40°C)
Max. Operating Temp.	185°F (85°C)
Min. Installation Temp.	Varies
RoHS 2011/65/EU	Yes
Agency Approvals	UL
Country of Origin	MADE IN USA



Order No.	UPC	Product Name	Description	Items per Pack	Items per Case
CT06220	051128-59324	3M™ Cable Tie Assortment Pack 06220	Contains 15 each of natural nylon 6.6. ties: CT4NT18-, CT6NT30-, CT8NT50-, and CT11NT50- Contains 10 each of black, weather-resistant nylon 6.6 ties: CT4BK18-, CT6BK30-, CT8BK50-, and CT11BK50-	100	1000

3M™ Cable Bases and Stackers

3M™ Cable Stackers

3M™ Cable Stackers organize cable runs and aid in identification, putting an end to tangled wires and the potential heating that could occur when cables are held together tightly under a single fastener. Easy installation simplifies compliance with the spacing requirements of the National Electrical Code, article 300-4-(d) and the Canadian Electric Code Part I, Section 12-516. Made from reclaimed plastic.

Cable Tie Type	Stacker
Color	White
RoHS 2011/65/EU	Yes
Country of Origin	MADE IN USA



	SI-1	SIFS-1
		
UPC	054007-49554	054007-49918
Product Name	3M™ Cable Stacker SI-1	3M™ Furring Strip Cable Stacker SIFS-1
Description	The 3M™ Cable Stacker SI-1 centers multiple cables on a 2 X 4 framing member.	The 3M™ Furring Strip Cable Stacker SIFS-1 routes, fastens, and supports CATV, telephone, security and instrumentation cables.
Items per Bag	25	25
Items per Case	250	250

3M™ Cable Tie Mounting Bases

3M™ Cable Tie Bases make mounting wire and cable a quick, easy and secure process. 2-way and 4-way configurations as well as adhesive-backed and screw mount options offer flexible mounting alternatives to meet a variety of applications.

RoHS 2011/65/EU Yes



	CTB2X1BGA-C	CTB1X1BGA-C	CTB75X75NTA-C	CTB75X75BKA-C
				
UPC	054007-06290	054007-06292	054007-06294	054007-06295
Material	ABS	ABS	Nylon	Nylon
Mount Type	Foam Backed Adhesive	Foam Backed Adhesive (Screw Mount)	Foam Backed Adhesive	Foam Backed Adhesive
Color	Beige	Beige	Natural	Black (UV Resistant)
Length	2.0” (51 mm)	1.0” (25 mm)	0.74” (19 mm)	0.74” (19 mm)
Width	1.0” (25 mm)	1.2” (25 mm)	0.74” (19 mm)	0.74” (19 mm)
Height	0.35” (8,9 mm)	0.15” (3,8 mm)	0.22” (5,6 mm)	0.22” (5,6 mm)
Slot Width	0.21” (5,3 mm)	0.21” (5,3 mm)	0.21” (5,3 mm)	0.21” (5,3 mm)
Slot Height	0.18” (4,5 mm)	0.06” (1,5 mm)	0.06” (1,5 mm)	0.06” (1,5 mm)
Items per Bag	100	100	100	100
Items per Case	500	500	500	500
Country of Origin				

	CTB1X1NTA-C	CTB1X1BKA-C	CTB60X41NTS-C	CTB87X62NTS-C
				
UPC	054007-06296	054007-06297	054007-95667	054007-95668
Material	Nylon	Nylon	Nylon	Nylon
Mount Type	Foam Backed Adhesive	Foam Backed Adhesive	Screw Mount	Screw Mount
Color	Natural	Black (UV Resistant)	Natural	Natural
Length	0.99” (25 mm)	0.99” (25 mm)	0.60” (15 mm)	0.87” (22 mm)
Width	0.99” (25 mm)	0.99” (25 mm)	0.41” (10 mm)	0.62” (16 mm)
Height	0.22” (5,6 mm)	0.22” (5,6 mm)	0.28” (7,0 mm)	0.38” (10 mm)
Slot Width	0.21” (5,3 mm)	0.21” (5,3 mm)	0.21” (5,3 mm)	0.35” (8,9 mm)
Slot Height	0.06” (1,5 mm)	0.06” (1,5 mm)	0.06” (1,5 mm)	0.10” (2,5 mm)
Items per Bag	100	100	100	100
Items per Case	500	500	500	500
Country of Origin			-	-

3M™ Hook and Loop Reclosable Fasteners

3M™ Hook and Loop Reclosable Fasteners permit thousands of easy openings and secure closings. Stiff hooks on one side mesh with pliable loops on the other side to provide secure closure.

RoHS 2011/65/EU Yes



Order No.	UPC	Product Name	Description	Rolls per Case
SJ-3526N-Hook-Black-1-1/2	021200-86383	3M™ Fastener Hook SJ3526	Hook (Black) 1 1/2”x50 yd	2
SJ3526N-White-2”x50yd	021200-86247	3M™ Fastener Hook SJ3526	Hook (White) 2”x50yd	2
SJ3527N-1”x50yd-White	021200-86253	3M™ Fastener Loop SJ3527	Loop (White) 1”x50 yd Bulk	3
SJ3527N-2”x50yd-Black	021200-86255	3M™ Fastener Loop SJ3527	Loop (Black) 2”x50 yd Bulk	2
SJ3527N-2”x50yd-White	021200-86256	3M™ Fastener Loop SJ3527	Loop (White) 2”x50 yd Bulk	2
SJ3526N-Beige-1”x50yd	021200-86242	3M™ Fastener Hook SJ3526	Hook (Beige) 1”x50yd	3
SJ3526N-Beige-2”x50yd	021200-86246	3M™ Fastener Hook SJ3526	Hook (Beige) 2”x50yd	2
SJ3526N-Beige-5/8”x50yd	021200-86239	3M™ Fastener Hook SJ3526	Hook (Beige) 5/8”x50yd	4
SJ3401-1”x50yd-Black	021200-62538	3M™ Fastener Loop SJ3401	Loop (Black) 1”x50 yd	12
SJ3401-1”x50yd-White	021200-62539	3M™ Fastener Loop SJ3401	Loop (White) 1”x50 yd	12
SJ3401-2”x50yd	021200-62544	3M™ Fastener Loop SJ3401	Loop (Black) 2”x50 yd	6
SJ3402-1”x50yd-Black	021200-62553	3M™ Fastener Hook SJ3402	Hook (Black) 1”x50 yd	12
SJ3402-1”x50yd-White	021200-62554	3M™ Fastener Hook SJ3402	Hook (White) 1”x50 yd	12
SJ3402-2”x50yd	021200-62559	3M™ Fastener Hook SJ3402	Hook (Black) 2”x50 yd	6
SJ3402-3/4”x50yd-Black	021200-62550	3M™ Fastener Hook SJ3402	Hook (Black) 3/4”x50 yd	16
SJ-3522	021200-86236	3M™ Fastener Plasticizer Resistant Hook SJ3522	Hook (Black) 1”x50 yd	3
SJ-3523	021200-86238	3M™ Fastener Plasticizer Resistant Loop SJ3523	Loop (Black) 1”x50 yd	3
SJ3526N-2”x50yd	021200-86245	3M™ Fastener Hook SJ3526	Hook (Black) 2”x50 yd	2
SJ3526N-Black-5/8”x50yd	021200-86240	3M™ Fastener Hook SJ3526	Hook (Black) 5/8”x50yd	4
SJ-3526N-Hook-Black-1”	021200-86243	3M™ Fastener Hook SJ3526	Hook (Black) 1”x50 yd	3
SJ-3526N-Hook-White-5/8”	021200-86241	3M™ Fastener Hook SJ3526	Hook (White) 5/8”x50 yd	4
SJ3527N-Beige-1”x50yd	021200-86251	3M™ Fastener Loop SJ3527	Loop (Beige) 1”x50yd	3
SJ3527N-Beige-2”x50yd	021200-86254	3M™ Fastener Loop SJ3527	Loop (Beige) 2”x50yd	2
SJ3527N-Beige-5/8”x50yd	021200-86248	3M™ Fastener Loop SJ3527	Loop (Beige) 5/8”x50yd	4
SJ3527N-Black-1.5”x50yd	021200-86167	3M™ Fastener Loop SJ3527	Loop (Black) 1.5”x50yd	2
SJ-3527N-Loop-Black-1”	021200-86252	3M™ Fastener Loop SJ3527	Loop (Black) 1”x50 yd	3
SJ3527N-White-5/8”x50yd	021200-86250	3M™ Fastener Loop SJ3527	Loop (White) 5/8”x50yd	4
SJ-3532N-Hook-Black-1”	021200-86259	3M™ Fastener Hook SJ3532	Hook (Black) 1”x50 yd	3
SJ-3533N-Loop-Black-1”	021200-86266	3M™ Fastener Loop SJ3533	Loop (Black) 1”x50 yd	3
SJ-3571-1”x50yd-Black	021200-86285	3M™ Fastener Loop SJ3571	Loop (Black) 1”x50 yd	3
SJ3571-1”x50yd-White	021200-87277	3M™ Fastener Loop SJ3571	Loop (White) 1”x50 yd	3
SJ3571-5/8”x50yd-Black	021200-86289	3M™ Fastener Loop SJ3571	Loop (Black) 5/8”x50 yd	4
SJ3571-White-2”x50yd	021200-86467	3M™ Fastener Loop SJ3571	Loop (White) 2”x50yd	2
SJ-3572-1”x50yd-Black	021200-86286	3M™ Fastener Hook SJ3572	Hook (Black) 1”x50 yd	3
SJ3572-2”x50yd-Black	021200-86377	3M™ Fastener Hook SJ3572	Hook (Black) 2”x50 yd	2
SJ3572-5/8”x50yd-Black	021200-86290	3M™ Fastener Hook SJ3572	Hook (Black) 5/8”x50 yd	4
MP3401/MP3402-Black	051131-06465	3M™ Scotchmate™ Reclosable Fastener MP3401	Reclosable Fastener (Black) 1”x5 yd	5
MP-3526/27N-Black	051131-06481	3M™ Scotchmate™ Reclosable Fastener MP3526/MP3527	Hook & Loop Fastener (Black) 1”x5 yd Mini Pack, Roll	5

3M™ Hook and Loop Reclosable Fasteners (continued)

Order No.	UPC	Product Name	Description	Rolls per Case
MP-3526/27N-White	051131-06488	3M™ Scotchmate™ Reclosable Fastener MP3526/MP3527	Hook & Loop Fastener (White) 1”x5 yd Mini Pack, Roll	5

3M™ Dual Lock™ Reclosable Fasteners



Strong. Hidden. Removable. 3M™ Dual Lock™ Reclosable Fasteners are a fastening solution that can replace screws, bolts and rivets. The fasteners contain hundreds of mushroom-shaped stems that audibly “SNAP” together to form a secure attachment with strong adhesive backings that adhere to your substrate.

RoHS 2011/65/EU Yes

Order No.	UPC	Product Name	Description	Rolls per Case
MP-3541/42-Black	051131-06483	3M™ Dual Lock™ Reclosable Fastener MP3541/MP3542 400/170	Reclosable Fastener (Black) 400 stems per square inch, 1”x5 yd	5
MP-3551/52-Black	051131-06484	3M™ Dual Lock™ Reclosable Fastener MP3551/MP3552 400/170	Reclosable Fastener (Black) 400 stems per square inch., 1”x5 yd	5
MP-3560-Clear	051131-06463	3M™ Dual Lock™ Reclosable Fastener MP3560 250	Reclosable Fastener (Clear) 250 stems per square inch, 1”x5 yd	5
SJ-3463	021200-24993	3M™ Dual Lock™ Reclosable Fastener SJ3463 400	Reclosable Fastener (Black) rigid backed circle with hole, 400 stems per square inch, 13/16” diameter with 0.16 in hole.	1000
SJ3540-1”x50yd-Black	021200-65812	3M™ Dual Lock™ Reclosable Fastener 250 SJ3540	Reclosable Fastener (Black) 250 stems per square inch, 1”x50 yd	2
SJ-3541-1”x50yd-Black	021200-86277	3M™ Dual Lock™ Reclosable Fastener 400 SJ3541	Reclosable Fastener (Black) 400 stems per square inch, 1”x50 yd	2
SJ-3542-1”x50yd-Black	021200-86309	3M™ Dual Lock™ Reclosable Fastener SJ3542 170	Reclosable Fastener (Black) 170 stems per square inch, 1”x50 yd	2
SJ-3560-1”x50yd-Clear	021200-86282	3M™ Dual Lock™ Reclosable Fastener 250 SJ3560	Reclosable Fastener (Clear) 250 stems per square inch, 1”x50 yd	2
SJ-3748	021200-63628	3M™ Dual Lock™ Reclosable Fastener 400 SJ3748 Black	Pop-in, Christmas tree style reclosable fastener with a 16.2 mm stud, 400 stems per square inch, 1 inch x 1 inch.	5000
SJ-3755	021200-24129	3M™ Dual Lock™ Reclosable Fastener 250 SJ3755 Black	Black, polypropylene reclosable fastener with rigid backing, rigid backed circle with one hole, 250 stems per square inch, 1 1/8 inch (28.5 mm) outside diameter.	1000
SJ-3762	021200-24131	3M™ Dual Lock™ Reclosable Fastener 400 SJ3762 Black	Black, polypropylene reclosable fastener with rigid backing, rigid backed circle with one hole, 400 stems per square inch, 1 1/8 inch (28.5 mm) outside diameter.	1000
SJ-3767	021200-24128	3M™ Dual Lock™ Reclosable Fastener SJ3767 Black	Black, polyolefin plastic reclosable square fastener with two counter-sunk holes, 400 stem per square inch, 1 1/2 inch (38 mm).	1000

3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4570



Low to medium temperature performance. Bonds well to metals (aluminum, stainless steel), glass, many plastics (polypropylene, polyethylene, polycarbonate, ABS), powder coated paints and medium to low surface energy materials. Designed for indoor use. Products include SJ4570 and SJ4575.

RoHS 2011/65/EU Yes

Order No.	UPC	Product Name	Description	Rolls per Case
SJ4570-1”x50yd-Clear	021200-44883	3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4570	Low Profile Clear, 1 in x 50 yd 0.105 in (2,7 mm).	2
SJ4570-2”x50yd-Clear	021200-46070	3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4570	Low Profile Clear, 2 in x 50 yd 0.105 in (2,7 mm).	1
SJ4570-3/4”x50yd-Clear	021200-46239	3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4570	Low Profile Clear, 3/4 in x 50 yd 0.105 in (2,7 mm).	2
SJ4570-4”x50yd-Clear	021200-46071	3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4570	Low Profile Clear, 4 in x 50 yd 0.105 in (2,7 mm).	1
SJ4570-5/8”x50yd-Clear	021200-45075	3M™ Dual Lock™ Low Profile Reclosable Fastener SJ4570	Low Profile Clear, 5/8 in x 50 yd 0.105 in (2,7 mm).	3



3M, ARC Plug, Blasts, BX, Centurion, Classic, ComTac, Cool Flow, Dual Lock, Dynatel, E-A-R, E-A-Rflex, E-A-Rform, E-A-Rsoft, Elavation, Express, FireDam, FX, GoggleGear, Hear-Through, Highland, Interam, Lexa, Light Vision, Maxim, Metaliks, Moon Dawg, No-Touch, Novec, Nuvo, One Touch, PanelSafe, Peltor, Optime, Pistonz, PTL, Pod Plugs, Privo, Push-Ins, Refine, ReLoad, Scotch, Scotch-Brite, Scotchcast, ScotchCode, Scotchfil, Scotchgard, Scotchkote, Scotchlok, Scotchmate, Scotchpro, Scotchrap, Scotch-Seal, Scotch-Weld, SecureFit, Skull Screws, Smart Lens, SofTouch, Splash GoggleGear, Super 33+, Super-Clear, Swerve, Temflex, Thinsulate, Tour-Guard, Tri-Flange, UltraFit, Ultrathon, Uvicator, VFlex, Virtua, Yellow Neons are trademarks of 3M Company. All other trademarks are property of their respective owners.

Dymo is a trademark of Newell Rubbermaid.

Unishield is a registered trademark for General Cable Technologies Corporation.

Latchways, Latchways Personal Rescue Device and PRD are trademarks of Latchways plc.

DEUS is a trademark of DEUS Rescue.

Vectran is a trademark of Kuraray Co., Ltd.

The images, pictures, and illustrations found in this catalog are for illustration purposes only. Check the Product Technical Data Sheets for actual product details.

3M products listed in this publication that are associated with a U.S.A. flag are manufactured in the USA as of the date of publication. 3M products offered on a government contract that require country of origin representation must be certified by 3M's Trade Compliance Department (contact your customer service support team to request a certification).

"RoHS 2011/65/EU" means that the product or part does not contain any of the substances in excess of the maximum concentration values ("MCVs") in EU RoHS Directive 2011/65/EU. The MCVs are by weight in homogeneous materials. This information represents 3M's knowledge and belief, which may be based in whole or in part on information provided by third party suppliers to 3M.

Important Notice

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability.

3M's product warranty is stated in its Product Literature available upon request. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any direct, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**