ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
520 Equity Ave
Conway, AR 72032-0000
Phone: 5013368444
Fax: 5013295636



T114 1-1/4" PVC TYPE T CONDULET

CANTEX,INC

Catalog Number	T114
Manufacturer	CANTEX,INC
Description	CANTEX 5133566 is a 1-1/4 in. Conduit Body Type T which provides pull, splice, and tap access for conductors in a conduit system along with a change in direction
Weight per unit	1.0 (lbs/each)
Product Category	PVC Conduit Fittings & Accy

Dimensions and Weight

Size	1/2

Descriptions

Description	1-1/4" PVC TYPE T CONDULET
Features	CANTEX 5133566 is a 1-1/4 in. Conduit Body Type T which provides pull, splice, and tap access for conductors in a conduit system along with a change in direction
Long Description	CANTEX 5133566 is a 1-1/4 in. Conduit Body Type T which provides pull, splice, and tap access for conductors in a conduit system along with a change in direction
Product Type	1 1/4 Ul Access FTG T
Extra Long Description	CTX 5133566 1 1/4 UL ACCESS FTG T

Manufacturer Information

Brand	PVC & Accessories
	CANTEX INC.
GTIN	00088700567863
Manufacturers Part Number	5133566
UPC	881780

Taxonomies, Classifications, and Categories

Category Description	PVC CONDULETS
Type	1-1/4 in. Conduit Body Type T

Trade Size

Trade Size	1 1/4

Packaging

Carton	1
Package	10
Weight Per Each	1.0 (lbs/each)

Conduit Bodies

Conduit Bodies - Type T

1/2"THROUGH 2"




Conduit Body Type T provides pull, splice, and tap access for conductors in a conduit system along with a change in direction. Type T Conduit Bodies have three openings and are used to connect or add sections of a conduit run.

- Durable non-conductive PVC will not rust or corrode
- For use with Schedule 40 & 80 conduit
- Includes lid, gasket, and screws
- UL listed
- Made in USA

2-1/2"THROUGH 4"





Part Number	Trade Size	Carton Quantity	"A"	"B"	"C"	"D'	"E"	Volume Cu. In.	3-Wire Fill
5133563	1/2	25	1.938	1.500	4.625	4.000	.875	4.3	#6 or smaller
5133564	3/4	15	1.500	1.688	5.375	4.625	1.063	6.5	#6 or smaller
5133565	1	10	1.750	2.000	6.563	5.375	1.313	11.8	#6 or smaller
5133566	1-1/4	10	2.500	2.500	8.188	7.188	1.688	25.0	XHHW #1
5133567	1-1/2	10	2.625	2.813	9.250	8.000	1.938	36.5	XHHW #2/0
5133568	2	5	3.125	3.375	10.375	9.500	2.375	63.5	XHHW #4/0
5133569	2-1/2	2	4.625	4.625	19.000	12.875	3.500	198.0	XHHW 500 MCM
5133570	3	2	4.625	4.625	19.000	12.875	3.500	198.0	XHHW 500 MCM
5133572	3-1/2	1	5.563	5.563	20.375	13.750	4.000	305.0	XHHW 500 MCM
5133571	4	1	5.563	5.563	20.375	13.875	4.500	305.0	XHHW 500 MCM

Dimensions are nominal



SINGLE SOURCE FOR PVC ELECTRICAL

CANTEX offers a complete line of PVC Conduit Bodies as part of a full line PVC electrical products. The CANTEX Conduit Body line includes multiple sizes of Type LB, Type LL, Type LR, Type T, Type C, and Type E Conduit Bodies.

With several decades of experience manufacturing PVC conduit, fittings and accessories, you can trust CANTEX to provide quality products. To see our complete line of PVC Conduit Bodies or our full line of PVC electrical products visit www.cantexinc.com.