ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



UB9FK 2-1/2" SCH80 90D 36"R PVC ELBOW

ABB INSTALLATION PRODUCTS, INC

Catalog Number	UB9FK
Manufacturer	ABB INSTALLATION PRODUCTS, INC
Description	Schedule 80 Elbow, Size 2-1/2 Inches, Bend Radius 36 Inches, Bend Angle 90 Degrees, Material PVC
Weight per unit	9.1 (lbs/each)
Product Category	PVC Sch 80 Elbows

Features

Outside Diameter	2.875

Material, Color, and Finish

Color	Gray

Dimensions and Weight

Depth	54.62

Descriptions

Description	2-1/2" SCH80 90D 36"R PVC ELBOW
Long Description	Schedule 80 Elbow, Size 2-1/2 Inches, Bend Radius 36 Inches, Bend Angle 90 Degrees, Material PVC
Product Type	2-1/2 In SCH 80 90 Deg X 36IN Elbow
Extra Long Description	TB UB9FK 2-1/2 IN SCH 80 90 DEG X 3

Manufacturer Information

Brand	Carlon
	ABB - Installation Products
GTIN	00034481191209
Manufacturers Part Number	UB9FK
UPC	786210

Taxonomies, Classifications, and Categories

Category Description	PVC ELBOWS
Type	Rigid Non-Metallic Conduit-Schedule 80 Elbows

Trade Size

Trade Size	2-1/2

Packaging

Carton	1
Weight Per Each	9.1 (lbs/each)

Uses, Certifications, and Standards

Standard	UL E323335

Schedule 80 Elbows

UL LISTED E23018

Standard Radius

ITEM	PLAIN END CAT. NO.	BELLED END CAT. NO.	SIZE (IN.)	PLAIN END STD. CTN.	BELLED END STD. CTN.
90° ELBOW 	UB9AD	—	½	50	—
	UB9AE	—	¾	25	—
	UB9AF	—	1	25	—
	UB9AG	—	1¼	20	—
	UB9AH	—	1½	25	—
	UB9AJ	—	2	20	—
	UB9AK	—	2½	10	—
	UB9AL	—	3	5	—
	UB9AN	—	4	1	—
	UB9AP	UB9APB	5	1	1
	UB9AR	—	6	1	—
45° ELBOW 	UB7AD	—	½	50	—
	UB7AE-UPC	—	¾	25	—
	UB7AF-UPC	—	1	20	—
	UB7AG	—	1¼	20	—
	UB7AH	—	1½	20	—
	UB7AH-CAR	—	1½	5	—
	UB7AJ-UPC	—	2	20	—
	UB7AK	—	2½	20	—
	UB7AL	—	3	1	—
	UB7AN	—	4	1	—
	UB7AP	UB7APB	5	1	1
	UB7AR	—	6	1	—
30° ELBOW 	UB6AD	—	½	50	—
	UB6AE	—	¾	25	—
	UB6AF	—	1	25	—
	UB6AG	—	1¼	5	—
	UB6AH	—	1½	25	—
	UB6AJ	—	2	20	—
	UB6AK	—	2½	1	—
	UB6AL	—	3	1	—
	UB6AN	—	4	1	—
	UB6AP	—	5	1	—
	UB6AR	—	6	1	—
22½° ELBOW 	UB5AL	—	3	5	—
	UB5AN	—	4	1	—
	UB5AP	UB5APB	5	1	1
11¼° ELBOW 	UB3AL	—	3	1	—
	UB3AR	—	6	1	—

For use with non-metallic solvent weld fittings.

Special Radius

SEGMENT	PLAIN END CAT. NO.	BELLED END CAT. NO.	NOM. DIAM. (IN.)	RADIUS (IN.)	PLAIN END STD. CTN.	BELLED END STD. CTN.
90° ELBOW 	UB9CF	—	1	18	1	—
	UB9DF	—	1	24	1	—
	UB9FF	—	1	36	1	—
	UB9HF	—	1	48	1	—
	UB9CG	—	1¼	18	1	—
	UB9DG	—	1¼	24	1	—
	UB9FG	—	1¼	36	1	—
	UB9HG	—	1¼	48	1	—
	UB9CH	—	1½	18	1	—
	UB9DH-UPC	UB9DHB	1½	24	1	1
	UB9FH	—	1½	36	1	—
	UB9HH	—	1½	48	1	—
	UB9CJ	—	2	18	1	—
	UB9DJ-UPC	UB9DJB	2	24	1	1
	UB9FJ	UB9FJB	2	36	1	1
	UB9HJ	—	2	48	1	—
	UB9CK	—	2½	18	1	—
	UB9DK-UPC	UB9DKB	2½	24	1	1
	UB9FK	UB9FKB	2½	36	1	1
	UB9HK	—	2½	48	1	—
	UB9CL	—	3	18	1	—
	UB9DL	UB9DLB	3	24	1	1
	UB9FL	UB9FLB	3	36	1	1
	UB9HL	—	3	48	1	—
	UB9DN	UB9DNB	4	24	1	1
	UB9FN	UB9FNB	4	36	1	1
	UB9HN	UB9HNB	4	48	1	1
	UB9NN	—	4	120	1	—
	UB9FP	—	5	36	1	—
	UB9HP	—	5	48	1	—
	UB9IP	—	5	60	1	—
	UB9FR	—	6	36	1	—
	UB9HR	—	6	48	1	—
	UB9IR	—	6	60	1	—

***Note**: Elbows 72" and larger may be shipped in segments. Consult factory for specifics.*

Schedule 80 Elbows — Special Radius *(continued)*

SEGMENT	PLAIN END CAT. NO.	BELLED END CAT. NO.	NOM. DIAM. (IN.)	RADIUS (IN.)	PLAIN END STD. CTN.	BELLED END STD. CTN.
45° ELBOW	UB7CF	—	1	18	1	—
	UB7DF	—	1	24	1	—
	UB7FF	—	1	36	1	—
	UB7HF	—	1	48	1	—
	UB7DG	—	1¼	24	1	—
	UB7FG	—	1¼	36	1	—
	UB7HG	—	1¼	48	1	—
	UB7CH	—	1½	18	1	—
	UB7DH	UB7DHB	1½	24	1	1
	UB7FH	—	1½	36	1	—
	UB7HH	—	1½	48	1	—
	UB7CJ	—	2	18	1	—
	UB7DJ	UB7DJB	2	24	1	1
	UB7FJ	UB7FJB	2	36	1	1
	UB7HJ	—	2	48	1	—
	UB7DK	UB7DKB	2½	24	1	1
	UB7FK	—	2½	36	1	—
	UB7HK	—	2½	48	1	—
	UB7CL	—	3	18	1	—
	UB7DL	UB7DLB	3	24	1	1
	UB7FL	UB7FLB	3	36	1	1
	UB7HL	—	3	48	1	—
	UB7DN	UB7DNB	4	24	1	1
	UB7FN	UB7FNB	4	36	1	1
	UB7HN	—	4	48	1	—
	UB7FP	—	5	36	1	—
	UB7HP	—	5	48	1	—
	UB7FR	—	6	36	1	—
	UB7HR	—	6	48	1	—
	UB7IR	—	6	60	1	—
30° ELBOW	UB6FN	—	4	36	1	—
	UB6FR	—	6	36	1	—
22½° ELBOW	—	UB5DHB	1½	24	—	20
	—	UB5DJB	2	24	—	20
	—	UB5FJB	2	36	—	25
	—	UB5DKB	2½	24	—	15
	UB5DL	UB5DLB	3	24	1	10
	—	UB5FLB	3	36	—	1
	UB5DN	UB5DNB	4	24	1	5
	—	UB5FNB	4	36	—	1
	UB5FP	—	5	36	1	—
11¼° ELBOW	UB3FP	—	5	36	1	—
						

Note: *Elbows 72" and larger may be shipped in segments. Consult factory for specifics.*

Flexible PVC Elbows

UL LISTED E23018



- UL Listed for exposed and direct-burial applications in accordance with Article 356 of the NEC®
- 0°–90° bending and offset applications
- O-ring seal for moisture-tight connections
- Maintains round shape throughout bend
- Sunlight resistant
- Non-corrosive — all PVC and Neoprene material
- Fully assembled and ready to use

CAT. NO.	SIZE (IN.)	STD. CTN.	STD. WT. (LBS.)	LENGTH FULLY ASSEMBLED (IN.)
UAFAD	½	8	1.6	8.5
UAFAE	¾	6	1.9	9.6
UAFAF	1	6	2.4	11.9

NEC and National Electrical Code are registered trademarks of the National Fire Protection Association, Inc.

Thomas&Betts

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289

www.tnb.com