



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



077680195951 MC 10/4 SL BK/RD/BL/WH 250' *Southwire Company*

Catalog Number	077680195951
Manufacturer	Southwire Company
Description	10-4 Solid Black, Red, Blue, White, Green - MC Tuff®, Blue Interlocked Lightweight Galvanized Steel Armor With Phase Id - Type MC - 250' Coil
Weight per unit	0.3130 (lbs/ft)
Product Category	Teck

Features

Bend Radius	9.645
Conductor Size	10
gauge	10 AWG
Inside Diameter	0.467
Material	Galvanized Steel
Number of Conductors	5
outside diameter	0.643
Voltage Rating	600V

Material, Color, and Finish

Color	Blue
Conductor Material	Copper
Finish	Blue Paint
Insulation Material	THHN

Dimensions and Weight

Length	250
--------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	MC 10/4 SL BK/RD/BL/WH 250'
extra long description	AFC 1709B42T00 10-4 MCS 250C
Features	MC Tuff is a lightweight, high-strength Type MC Cable with blue galvanized steel interlocked armor that features ColorSpec®ID/ColorTrak® ID for easy identification. MC Tuff cables meet UL Standard 1569 and NEC 330, have no conductor count limit, and offer various conductor bundle combinations. These bundles consist of THHN/THWN rated conductors that are twisted and wrapped with polypropylene assembly tape. They also come with an insulated green equipment grounding conductor. Additionally, Atkore offers a G
Long Description	10-4 Solid Black, Red, Blue, White, Green - MC Tuff®, Blue Interlocked Lightweight Galvanized Steel Armor with phase ID - Type MC - 250' Coil
Product Type	10-4 MCS 250C
Short Description	10-4 MCS 250C
Special Features	Galvanized interlocking steel strip, utilizes ColorSpec® ID system

Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680195951
Manufacturers Part Number	1709B42T00
UPC	077680195951

Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	MC Tuff® Lightweight Steel Cable

Trade Size

Trade Size	10-4
------------	------

Packaging

Carton	250
Weight	0.3257
Weight Per foot	0.313

Uses, Certifications, and Standards

Temperature Rating	194
--------------------	-----