



## Open Switches T&B Catalog Number:

**UPC Number:** OT30FT3  
**Status:** 80432541552  
**Description:** Active

3 pole, 30 amps rated at 600 VAC, UL 98, door mounted open non-fusible disconnect switch

### Features

- Quick make, quick brake mechanism
- Extremely compact size
- Finger-proof construction with no hazardous exposed parts

### Application

- Suitable for use as motor disconnects or industrial control panel disconnects on service entrance equipment, panelboards, switchboards, industrial control equipment, motor control centers, etc.
- Motor feeder applications and motor feeder short circuit and ground fault protection

### General

|                 |              |
|-----------------|--------------|
| Style           | Door Mounted |
| Number of Poles | 3            |
| Series          | Non-fusible  |

### Approvals

|          |       |
|----------|-------|
| UL Class | UL 98 |
|----------|-------|

### Dimension Information

|                    |                   |
|--------------------|-------------------|
| H x W x D (inches) | 3.94 x 2.76 x .88 |
|--------------------|-------------------|

### Specifications

|                      |     |
|----------------------|-----|
| Rated Current (Amps) | 30  |
| Rated Voltage AC     | 600 |

### Packaging

|                    |                |
|--------------------|----------------|
| T&B Inner Pack     | 1              |
| Package in Units   | 10             |
| T&B Sold in UOM    | Each           |
| T&B Weight Per UOM | 0.97 lbs. Each |

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com



## Open Switches T&B Catalog Number:

**UPC Number:** OT30FT3  
80432541552  
**Status:** Active  
**Description:**

3 pole, 30 amps rated at 600 VAC, UL 98, door mounted open non-fusible disconnect switch

### Features

- Quick make, quick brake mechanism
- Extremely compact size
- Finger-proof construction with no hazardous exposed parts

### Application

- Suitable for use as motor disconnects or industrial control panel disconnects on service entrance equipment, panelboards, switchboards, industrial control equipment, motor control centers, etc.
- Motor feeder applications and motor feeder short circuit and ground fault protection

### General

|                 |              |
|-----------------|--------------|
| Style           | Door Mounted |
| Number of Poles | 3            |
| Series          | Non-fusible  |

### Approvals

|          |       |
|----------|-------|
| UL Class | UL 98 |
|----------|-------|

### Dimension Information

|                    |                   |
|--------------------|-------------------|
| H x W x D (inches) | 3.94 x 2.76 x .88 |
|--------------------|-------------------|

### Specifications

|                      |     |
|----------------------|-----|
| Rated Current (Amps) | 30  |
| Rated Voltage AC     | 600 |

### Packaging

|                    |                |
|--------------------|----------------|
| T&B Inner Pack     | 1              |
| Package in Units   | 10             |
| T&B Sold in UOM    | Each           |
| T&B Weight Per UOM | 0.97 lbs. Each |

#### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com