



## Open Switches T&B Catalog Number:

**UPC Number:** OT40FT3  
**Status:** 80432541557  
**Description:** Active

3 pole, 40 amps rated at 600 VAC, UL 508, door mounted open non-fusible disconnect switch

### Features

Quick make, quick brake mechanism  
 Extremely compact size  
 Finger-proof construction with no hazardous exposed parts

### Application

Industrial control panel disconnects  
 For use in motor controller and motor overload protection applications  
 Can be used as an OSHA lockout/tagout disconnect

### General

Style Door Mounted  
 Number of Poles 3  
 Series Non-fusible

### Approvals

UL Class UL 508

### Dimension Information

H x W x D (inches) 2.13 x 1.69 x 2.64

### Specifications

Rated Current (Amps) 40  
 Rated Voltage AC 600

### Packaging

T&B Inner Pack 1  
 Package in Units 10  
 T&B Sold in UOM Each  
 T&B Weight Per UOM 0.23 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com



## Open Switches T&B Catalog Number:

**UPC Number:**  
**Status:**  
**Description:**

OT40FT3  
80432541557  
Active

3 pole, 40 amps rated at 600 VAC, UL 508, door mounted open non-fusible disconnect switch

### Features

Quick make, quick brake mechanism  
Extremely compact size  
Finger-proof construction with no hazardous exposed parts

### Application

Industrial control panel disconnects  
For use in motor controller and motor overload protection applications  
Can be used as an OSHA lockout/tagout disconnect

### General

Style Door Mounted  
Number of Poles 3  
Series Non-fusible

### Approvals

UL Class UL 508

### Dimension Information

H x W x D (inches) 2.13 x 1.69 x 2.64

### Specifications

Rated Current (Amps) 40  
Rated Voltage AC 600

### Packaging

T&B Inner Pack 1  
Package in Units 10  
T&B Sold in UOM Each  
T&B Weight Per UOM 0.23 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com