



UTILITY & VALVE BOXES



- Etched polypropylene face
- Face anchored in concrete
- Ultra-violet inhibitor
- Exceeds ASTM-D1693 Standards for Environmental Stress Cracking Resistance

**R-Series Concrete Lid
No. N36R
76 lbs.**




N36RP


**Utility Box
No. N36 BOX
172 lbs.**




B36E




B36G



FL36D



B36-61D



B36-61G

A high density reinforced concrete box with non-setting shoulders positioned to maintain grade and facilitate back filling. Approximate dimensions and weight shown.

Oldcastle Ordering Code	Item	Approx. Shipping Weight	Description
N36BOX	BOX	172 lbs.	N30 Utility Box (17-1/8" X 30-1/4") - 8 per pallet
N36R	LID	76 lbs.	Reinforced Concrete Lid with Plastic Ring - (Order N90 Bolt Down Kit Separately)
FL36D	LID	35 lbs.	Fibrelyte Lid, Non-Concrete
FL36P	LID	38 lbs.	Fibrelyte lid non concrete with probe hole option
B36E	LID	96 lbs.	Reinforced concrete with 7" x 13-1/2" Concrete Reading Lid
B36G	LID	78 lbs.	Reinforced concrete with 5" x 8" cast iron, self-closing, reading lid with frame
B36GP	LID	79 lbs.	Concrete lid with 5" x 8" reader door with probe hole option
N36RP	LID	76 lbs.	R-Series Composite Lid with Polypropylene Ring w/ 2" Probe Hole - (Order N90 Bolt Down Kit Separately)
B36-61D	COVER	56 lbs.	Steel Checker Plate Cover with 8" Round, Self-Closing Reading Lid
B36-61G	COVER	60 lbs.	Steel Checker Plate Cover with 8" Round, Self-Closing Reading Lid
N36X12	EXTENSION	189 lbs.	12" Reinforced Concrete Box Extension - 8 per pallet
B36SL	SLAB	104 lbs.	Reinforced Concrete Slab (20" x 34")

Galvanizing available on all steel covers. Probe holes : badger, flexnet, orion, neptune



Oldcastle Enclosure Solutions

Phone: (800) 735-5566 Fax: (800) 486 6806

Copyright© 2017 Oldcastle, Inc.

N36 BOX

FILE NAME: B36_ISO

ISSUE DATE: January, 2011


OldcastleEnclosures.com

N36 UTILITY BOX 17-1/8" x 30-1/4"


CHRISTY

ELECTRICAL & TELEPHONE BOXES



- Etched polypropylene face
- Face anchored in concrete
- Ultra-violet inhibitor
- Exceeds ASTM-D1693 Standards for Environmental Stress Cracking Resistance
- Meets Caltrans #6 State Specifications




**R-Series Concrete Lid
No. N36R
76 lbs.**




**Electrical Box
No. N36 BOX
172 lbs.**



FL36T



B36-61D



N36-61J

A high density reinforced concrete box with non-setting shoulders positioned to maintain grade and facilitate back filling. Approximate dimensions and weight shown.

Oldcastle Ordering Code	Item	Approx. Shipping Weight	Description
N36BOX	BOX	172 lbs.	N36 Electrical Box (17 1/2" x 30 1/2") Meets #6 State Specifications - 8 per pallet
N36R	LID	76 lbs.	Reinforced Concrete Lid with Plastic Ring - (Order N90 Bolt Down Kit Separately)
FL36T	LID	35 lbs.	Fibrelyte lid, non-concrete Bolt Down (Order N90 Bolt Down Kit Separately)
B36-61D	COVER	56 lbs.	Steel Checker Plate
N36-61J	COVER	56 lbs.	Steel Checker Plate Bolt Down (Order N90 Bolt Down Kit Separately)
N36X12	EXTENSION	189 lbs.	12" Reinforced Concrete - 8 per pallet
B36SL	SLAB	104 lbs.	Reinforced concrete (20" x 34")
Galvanizing available on all steel covers			



Oldcastle® Enclosure Solutions

Phone: (800) 735-5566 Fax: (800) 486 6806

Copyright © 2017 Oldcastle, Inc.

N36 BOX

FILE NAME: N36_ISO

ISSUE DATE: January, 2011

OldcastleEnclosures.com

N36 ELECTRICAL BOX 17-1/8" x 30-1/4"

CHRISTY®