

TYPE 3 and 3R ENCLOSURES



Screw Cover – Powder Coated

- Designed for use as junction and pull boxes
- Stock inventory sizes from 4x4x4 to 48x48x18
- Custom sizes and modifications available

SPECIFICATIONS

- Manufactured from code gauge, low carbon steel
- Drip shield top, seam free sides
- Slip-on cover without gasket
- Available with and without knockouts

FINISH

- Standard: Gunsmoke Gray Powder Coated
- Optional powder coat colors and custom silkscreen printing available (see pg. 48)

INDUSTRY STANDARDS

- Type 3R - UL 50 and UL 50E: Intended for outdoor use primarily to provide a degree of protection against rain, sleet, and damage from external ice formation.
- RoHS compliant

CATALOG NUMBER	UPC (761515)	SIZE (W"xH"xD")	WGT	LIST PRICE
444RTSC	34010	4x4x4	1	\$27.56
464RTSC	34020	4x6x4	2	\$32.22
664RTSC	34050	6x6x4	3	\$32.22
684RTSC	34100	6x8x4	3	\$42.22
666RTSC	34070	6x6x6	3	\$42.22
884RTSC	34170	8x8x4	4	\$42.22
886RTSC	34200	8x8x6	5	\$54.44
10104RTSC	34280	10x10x4	6	\$60.00
10106RTSC	34300	10x10x6	7	\$71.11
12124RTSC	34380	12x12x4	8	\$73.33
12126RTSC	34390	12x12x6	10	\$88.89
12186RTSC	34510	12x18x6	14	\$120.00

CATALOG NUMBER	UPC (761515)	SIZE (W"xH"xD")	WGT	LIST PRICE
888RTSCNK	34210	8x8x8	6	\$77.78
12128RTSCNK	34410	12x12x8	11	\$108.89
121212RTSCNK	40025	12x12x12	15	\$222.22
16166RTSCNK	34600	16x16x6	14	\$168.89
18186RTSCNK	34660	18x18x6	19	\$168.89
18188RTSCNK	34680	18x18x8	20	\$200.00
181812RTSCNK	34690	18x18x12	25	\$333.33
24246RTSCNK	34790	24x24x6	30	\$297.78
24248RTSCNK	34800	24x24x8	34	\$333.33
242410RTSCNK	34810	24x24x10	37	\$400.00
242412RTSCNK	34820	24x24x12	41	\$428.18
30308RTSCNK	35020	30x30x8	51	\$577.78
303012RTSCNK	35120	30x30x12	61	\$768.89
36368RTSCNK	35040	36x36x8	73	\$800.00
363610RTSCNK	35090	36x36x10	79	\$844.44
363612RTSCNK	35140	36x36x12	87	\$888.89
363618RTSCNK	35092	36x36x18	105	\$1,144.00
484812RTSCNK	35124	48x48x12	220	\$1,563.16
484818RTSCNK	35126	48x48x18	276	\$1,920.00

WITH KNOCK-OUTS

WITHOUT KNOCK-OUTS

TYPE 1 ENCLOSURES

TYPE 3 AND 3R ENCLOSURES

CABLE MANAGEMENT SOLUTIONS

UTILITY AND STORAGE CABINETS

HARDWARE AND ACCESSORIES

CUSTOM ENCLOSURE SOLUTIONS

