

# Eaton 10250T34R

Catalog Number: 10250T34R

Eaton 10250T pushbutton, Heavy-duty watertight and oiltight Indicating Light, Standard actuator, Incandescent, Transformer, NEMA 3, 3R, 4, 4X, 12, 13, Red, Plastic, 120 V

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton 10250T pushbutton	10250T34R
<b>Product Length/Depth</b>	<b>Product Height</b>
2.4 in	3.2 in
<b>Product Width</b>	<b>Product Weight</b>
2.1 in	0.3 lb
<b>Warranty</b>	<b>Compliances</b>
1 year	CE Marked
<b>Certifications</b>	
CSA Certified	
UL Listed	

## defaultTaxonomyAttributeLabel

### Type

Heavy-Duty Watertight/Oiltight

### Light unit type

Incandescent, transformer

### Lens material

Plastic

### Light unit voltage

120 Vac

### Series

10250T

### Actuator

Standard

### Style

30.5 mm

### Lens color

Red

### Rating

NEMA 3R

NEMA 4X

NEMA 3

NEMA 4

NEMA 12

NEMA 13

## Resources

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Eaton Specification Sheet - 10250T34R](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton 10250T34R

Catalog Number: 10250T34R

Eaton 10250T pushbutton, Heavy-duty watertight and oiltight Indicating Light, Standard actuator, Incandescent, Transformer, NEMA 3, 3R, 4, 4X, 12, 13, Red, Plastic, 120 V

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton 10250T pushbutton	10250T34R
<b>Product Length/Depth</b>	<b>Product Height</b>
2.4 in	3.2 in
<b>Product Width</b>	<b>Product Weight</b>
2.1 in	0.3 lb
<b>Warranty</b>	<b>Compliances</b>
1 year	CE Marked
<b>Certifications</b>	
CSA Certified	
UL Listed	

## defaultTaxonomyAttributeLabel

### Type

Heavy-Duty Watertight/Oiltight

### Light unit type

Incandescent, transformer

### Lens material

Plastic

### Light unit voltage

120 Vac

### Series

10250T

### Actuator

Standard

### Style

30.5 mm

### Lens color

Red

### Rating

NEMA 3R

NEMA 4X

NEMA 3

NEMA 4

NEMA 12

NEMA 13

## Resources

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Eaton Specification Sheet - 10250T34R](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)