



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T5J63 Push-Pull Ma JMB MSHD Estop

Eaton Corp

Catalog Number	10250T5J63
Manufacturer	Eaton Corp
Description	Eaton 10250T Pushbutton, 10250T, 30.5 MM, Heavy-Duty, 65 MM, Nema 3, 3R, 4, 4X, 12, 13, Non-Illuminated, Two-Position, Maintained Push and Pull, Jumbo Mushroom Head, Red Actuator, Anodized Aluminum Bus, Emer. Stop
Weight per unit	0.4000 (lbs/each)
Product Category	Push Button Components

Features

actuator	Jumbo mushroom head
dimensions	1.0000 IN X 1.0000 IN X 1.0000 IN
media	Yes

Dimensions and Weight

Size	65 mm
------	-------

Descriptions

Description	PUSH-PULL MA JMB MSHD ESTOP
extra long description	ETN 10250T5J63 PUSH-PULL MA JMB MSH
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 10250T pushbutton, 10250T, 30.5 mm, Heavy-Duty, 65 mm, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Maintained push and pull, Jumbo mushroom head, Red actuator, Anodized aluminum bus, EMER. STOP
Product Type	Push-Pull Ma JMB MSHD Estop

Manufacturer Information

Brand	Eaton
GTIN	00782113381374
Manufacturers Part Number	10250T5J63
UPC	782113381374

Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
Type	PUSHBUTTON



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.4

Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
standard	UL Listed, CSA Certified, CE Marked