



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T4.51 Oiltight Push-Pull Operator

Eaton Corp

Catalog Number	10250T4.51
Manufacturer	Eaton Corp
Description	Eaton 30.5 MM Heavy-Duty Watertight/Oiltight Push-Pull Unit, Class I Division 2, Standard Actuator, 1NC, Non-Illuminated, Three-Position, Momentary Push and Pull, Maintained Intermediate, 40 MM Button, 10250T Series
Weight per unit	0.1000 (lbs/each)
Product Category	Push Button Components

Features

Contact Configuration	1 NC
dimensions	1.0000 IN X 1.0000 IN X 1.0000 IN
media	Yes

Dimensions and Weight

Size	40 mm
------	-------

Descriptions

Description	OILTIGHT PUSH-PULL OPERATOR
extra long description	ETN 10250T4-51 OILTIGHT PUSH-PULL O
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 30.5 mm Heavy-Duty Watertight/Oiltight Push-Pull Unit,Class I Division 2,Standard Actuator,1NC,Non-illuminated,Three-position,Momentary push and pull, maintained intermediate,40 mm button,10250T Series
Product Type	Oiltight Push-Pull Operator

Manufacturer Information

Brand	Eaton Corp
GTIN	00782113688916
Manufacturers Part Number	10250T4-51
UPC	782113688916

Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
Type	PUSHBUTTON



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.1

Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
standard	UL Listed, CSA Certified, CE Marked