



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 10864CHC Encl 10X8X6 N4 Encl *Cooper B-Line/Cable Tray*

Catalog Number	10864CHC
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Jic Panel Enclosure, 10" Height, 6" Length, 8" Width, Nema 4, Hinged Cover, 4CHC Enclosure, Wall Mount, Small Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	7.8 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

### Features

dimensions	6.0000 IN X 8.0000 IN X 10.0000 IN
Material	Carbon Steel
Mounting Type	Wall

### Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

### Dimensions and Weight

Size	8.00 In Width X 6.00 In Depth X 10.00 In Height
------	---

### Descriptions

Description	ENCL 10X8X6 N4 ENCL
extra long description	B-LINE 1086-4CHC TYPE 4 JIC CONTINU
Features	Eaton's B-Line series JIC panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments, but are also commonly used as industrial wiring, junction, pull, and termination boxes.
Long Description	Eaton B-Line series JIC panel enclosure, 10" height, 6" length, 8" width, NEMA 4, Hinged cover, 4CHC enclosure, Wall mount, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 4 Jic Continuous Hinge CVR Enc, 10X8X6
Special Features	Continous piano hinge with s.s. pin & door clamp

### Manufacturer Information

Brand	Eaton
GTIN	00782051701746
Manufacturers Part Number	1086-4CHC
UPC	782051701746

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	JIC panel enclosure



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	7.832

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems Ind Facilities & Factories - Facility: Power Distribution and Control Commercial / Institutional Buildings / Structures - Lighting and Lighting Controls Ind Facilities & Factories - Facility: Automation and Monitoring Commercial / Institutional Buildings / Structures - Critical Power Ind Facilities & Factories - Industrial Facilities/Factories - Other Ind Facilities & Factories - Mfg. Process Electrification and Control Commercial / Institutional
Mounting	EXTERNAL FEET, WALL
nema rating	4
standard	CSA C22.2, UL 50, NEMA