



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



121064XSCHC Encl 12X10X6 N4X CH *Cooper B-Line/Cable Tray*

Catalog Number	121064XSCHC
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Jic Panel Enclosure, 12" Height, 6" Length, 10" Width, Nema 4X, Hinged Cover, 4XSCHC Enclosure, Wall Mount, Small Single Door, External Mounting Feet, 304 Stainless Steel, Seamless Poured In-Place Gasket
Weight per unit	10.2 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

dimensions	6.0000 IN X 10.0000 IN X 12.0000 IN
Material	304 Stainless Steel
Mounting Type	Wall

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	10.00 In Width X 6.00 In Depth X 12.00 In Height
------	--

Descriptions

Description	ENCL 12X10X6 N4X CH
extra long description	B-LINE 12106-4XSCHC TYPE 4X SSL JIC
Features	Eaton's B-Line series JIC panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments, but are also commonly used as industrial wiring, junction, pull, and termination boxes.
Long Description	Eaton B-Line series JIC panel enclosure, 12" height, 6" length, 10" width, NEMA 4X, Hinged cover, 4XSCHC enclosure, Wall mount, Small single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket
Product Type	Type 4X SSL Jic Continuous Hinge CVR Enc, 12X10X6
Special Features	Cont. piano hinge,panel mount prov.,s.s.doorclamps

Manufacturer Information

Brand	Eaton
GTIN	00782051701982
Manufacturers Part Number	12106-4XSCHC
UPC	782051701982

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	JIC panel enclosure



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	10.175

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Mfg. Process Electrification and Control Commercial / Institutional Buildings / Structures - Lighting and Lighting Controls Ind Facilities & Factories - Industrial Facilities/Factories - Other Commercial / Institutional Buildings / Structures - Power Distribution and Controls Ind Facilities & Factories - Facility: Safety and Security Systems Ind Facilities & Factories - Facility: Critical Power Commercial / Institutional Buildings / Structures - Critical Power Ind Facilities & Factories
Mounting	EXTERNAL FEET, WALL
standard	CSA C22.2, NEMA, UL 50