



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



12126SDSS4 Encl 12X12X6 N4X SS4 1/4TRN LTCH HC *Cooper B-Line/Cable Tray*

Catalog Number	12126SDSS4
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 12" Height, 6" Length, 12" Width, Nema 4X, Hinged Cover, SDSS4 Enclosure, Wall Mount, Medium Single Door, Thru Holes, Opt. External Mounting Feet, 304 Stainless Steel, Seamless Poured In-Place Gasket
Weight per unit	10.8 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

dimensions	6.0000 IN X 12.0000 IN X 12.0000 IN
Material	304 Stainless Steel
Mounting Type	Wall

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	12.00 In Width X 6.00 In Depth X 12.00 In Height
------	--

Descriptions

Description	ENCL 12X12X6 N4X SS4 1/4TRN LTCH HC
extra long description	B-LINE 12126-SDSS4 TYPE 4X SSL SGL-
Features	Eaton's B-Line series wall mounted panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments.
Long Description	Eaton B-Line series wall mounted panel enclosure, 12" height, 6" length, 12" width, NEMA 4X, Hinged cover, SDSS4 enclosure, Wall mount, Medium single door, Thru holes, opt. external mounting feet, 304 stainless steel, Seamless poured in-place gasket
Product Type	Type 4X SSL SGL-Solid Door Enc, 12X12X6
Special Features	Stainless 1/4 turn latches

Manufacturer Information

Brand	Cooper B-Line/Cable Tray
GTIN	00782051093506
Manufacturers Part Number	12126-SDSS4
UPC	782051093506

Taxonomies, Classifications, and Categories

Type	Wall mounted panel enclosure
------	------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	10.8

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative EnergyCommercial / Institutional Buildings / Structures - Safety and Security SystemsCommercial / Institutional Buildings / Structures - Commercial/Inst Bldg Strctures - AftermarketCommercial / Institutional Buildings / Structures - Critical PowerUtility - Substations, Utility Transmission and DistributionDatacenters - IT Space: CI and Hyper ConvergedCommercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherOther
Mounting	WALL
nema rating	4X
standard	CSA C22.2.,NEMA,UL 50