



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 1414N4SSG 8X6X3.5 N4X Lo CLMP CVR

*Hammond MFG.*

Catalog Number	1414N4SSG
Manufacturer	Hammond MFG.
Description	N4X J Box, Lift Off Cover W/Panel - 8 X 6 X 3.5 - 304 SS
Weight per unit	8.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

### Features

Material	Stainless Steel
----------	-----------------

### Material, Color, and Finish

Color	Unpainted
-------	-----------

### Dimensions and Weight

Size	8 in x 6 in x 3.5 in
------	----------------------

### Descriptions

Description	8X6X3.5 N4X LO CLMP CVR
extra long description	HMND 1414N4SSG 8X6X3.5 CLAMP COVER
Long Description	N4X J Box, Lift Off Cover w/panel - 8 x 6 x 3.5 - 304 SS
Product Type	8X6X3.5 Clamp Cover 304SS Jic
Special Features	Formed from 14 gauge 304 stainless steel. Smooth, continuously welded seams. Welded brackets provide for enclosure mounting. Lift-Off cover is secured with stainless steel clamps and screws. Seamless poured-in place gasket. All models larger than 4" x 4" include a removable 14 gauge inner panel. Tapped studs are provided for mounting inner panels. A bonding stud is provided on the door and a grounding stud is provided in the enclosure.

### Manufacturer Information

Brand	Hammond MFG.
GTIN	00623980295244
Manufacturers Part Number	1414N4SSG
UPC	623980295244

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	N4X J Box, Lift Off Cover w/panel

### Packaging

Carton	1
Weight Per each	8



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Designed for use as instrument enclosures, electric, hydraulic or pneumatic control housings, electrical junction boxes or terminal wiring enclosures. Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion may be a problem.

Mounting

WALL

nema rating

13;3R;4X

standard

CSA, UL, CE