

BI-METAL SHIP AUGER BITS

Tougher than Nails

EXTREME DURABILITY

High speed steel cutting edge for superior durability in nail-embedded wood

LONGER LIFE

High speed steel screw tip increases wear resistance for extended life

FAST, EASY DRILLING

Unique parabolic screw tip pulls the bit through material quickly and effortlessly

RESHARPENABLE

Resharpener with LENOX Diamond File product no. 25312DIAF1



Our bi-metal technology fuses two premium steels together.



High Speed Steel Screw Tip



Cuts Nails



High Speed Steel Cutting Edge



	1 PER PACK PROD NO	HOLE DIAMETER		OVERALL LENGTH		TWIST LENGTH	
		IN	MM	IN	MM	IN	MM
		7-1/2" SHIP AUGER BITS					
1455507A1016	5/8	16	7-1/2	191	4	102	
1455607A1116	11/16	18	7-1/2	191	4	102	
1455707A1216	3/4	19	7-1/2	191	4	102	
1455807A1316	13/16	21	7-1/2	191	4	102	
1455907A1416	7/8	22	7-1/2	191	4	102	
1456007A1516	15/16	24	7-1/2	191	4	102	
1456107A1616	1	25	7-1/2	191	4	102	
1456207A1716	1-1/16	27	7-1/2	191	4	102	
1456307A1816	1-1/8	29	7-1/2	191	4	102	
1456407A2016	1-1/4	32	7-1/2	191	4	102	
1456507A2216	1-3/8	35	7-1/2	191	4	102	
1456607A2416	1-1/2	38	7-1/2	191	4	102	



	1 PER BOX PROD NO	HOLE DIAMETER		OVERALL LENGTH		TWIST LENGTH	
		IN	MM	IN	MM	IN	MM
		18" SHIP AUGER BITS					
145390080616*	3/8	10	18	457	12	305	
145400080716*	7/16	11	18	457	12	305	
145410080816	1/2	13	18	457	12	305	
145420080916	9/16	14	18	457	12	305	
145430081016	5/8	16	18	457	12	305	
145440081116	11/16	18	18	457	12	305	
145450081216	3/4	19	18	457	12	305	
145460081316	13/16	21	18	457	12	305	
145470081416	7/8	22	18	457	12	305	
145480081516	15/16	24	18	457	12	305	
145490081616	1	25	18	457	12	305	
145500081716	1-1/16	27	18	457	12	305	
145510081816	1-1/8	29	18	457	12	305	
145520082016	1-1/4	32	18	457	12	305	
145530082216	1-3/8	35	18	457	12	305	
145540082416	1-1/2	38	18	457	12	305	

*3/8" shank—all others 1/2" shank



31700K31700

16 PIECE, LENOX LEADER® / AUGER KIT

Augers: 7/8", 1-1/8", 1-1/4". Length: 7-1/2"
 LENOX LEADER bits: 1-1/2", 1-3/4", 2-1/8", 2-9/16"
 Extension: 5-1/2". Five lead screws
 Slim Taper File. Hex Wrench Set
 LARGE KIT

BI-METAL SHIP AUGER BITS

Tougher than Nails

EXTREME DURABILITY

High speed steel cutting edge for superior durability in nail-embedded wood

LONGER LIFE

High speed steel screw tip increases wear resistance for extended life

FAST, EASY DRILLING

Unique parabolic screw tip pulls the bit through material quickly and effortlessly

RESHARPENABLE

Resharpener with LENOX Diamond File product no. 25312DIAF1



Our bi-metal technology fuses two premium steels together.



High Speed Steel Screw Tip



Cuts Nails



High Speed Steel Cutting Edge



	1 PER PACK PROD NO	HOLE DIAMETER		OVERALL LENGTH		TWIST LENGTH	
		IN	MM	IN	MM	IN	MM
7-1/2" SHIP AUGER BITS	1455507A1016	5/8	16	7-1/2	191	4	102
	1455607A1116	11/16	18	7-1/2	191	4	102
	1455707A1216	3/4	19	7-1/2	191	4	102
	1455807A1316	13/16	21	7-1/2	191	4	102
	1455907A1416	7/8	22	7-1/2	191	4	102
	1456007A1516	15/16	24	7-1/2	191	4	102
	1456107A1616	1	25	7-1/2	191	4	102
	1456207A1716	1-1/16	27	7-1/2	191	4	102
	1456307A1816	1-1/8	29	7-1/2	191	4	102
	1456407A2016	1-1/4	32	7-1/2	191	4	102
	1456507A2216	1-3/8	35	7-1/2	191	4	102
	1456607A2416	1-1/2	38	7-1/2	191	4	102



	1 PER BOX PROD NO	HOLE DIAMETER		OVERALL LENGTH		TWIST LENGTH	
		IN	MM	IN	MM	IN	MM
18" SHIP AUGER BITS	145390080616*	3/8	10	18	457	12	305
	145400080716*	7/16	11	18	457	12	305
	145410080816	1/2	13	18	457	12	305
	145420080916	9/16	14	18	457	12	305
	145430081016	5/8	16	18	457	12	305
	145440081116	11/16	18	18	457	12	305
	145450081216	3/4	19	18	457	12	305
	145460081316	13/16	21	18	457	12	305
	145470081416	7/8	22	18	457	12	305
	145480081516	15/16	24	18	457	12	305
	145490081616	1	25	18	457	12	305
	145500081716	1-1/16	27	18	457	12	305
	145510081816	1-1/8	29	18	457	12	305
	145520082016	1-1/4	32	18	457	12	305
	145530082216	1-3/8	35	18	457	12	305
	145540082416	1-1/2	38	18	457	12	305

*3/8" shank—all others 1/2" shank



31700K31700

16 PIECE, LENOX LEADER® / AUGER KIT

Augers: 7/8", 1-1/8", 1-1/4". Length: 7-1/2"
 LENOX LEADER bits: 1-1/2", 1-3/4", 2-1/8", 2-9/16"
 Extension: 5-1/2". Five lead screws
 Slim Taper File. Hex Wrench Set
 LARGE KIT