

---

## 20A, 125V RUBBER DUST-TIGHT CONNECTOR, YELLOW

1533 | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

#### Straight Blade Rubber Connector 20amp 125volt 5-20r

- Rubber body construction stands up to impacts, oils, chemicals, heat, and weather.
- Floating blades allow self-alignment with contacts for a firm, even electrical connection.
- Terminal screws backed-out, ready-to-wire, saving time and money.
- Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.
- Quick-drive assembly screws allow for fast installation, saving time and money.
- Self-centering cord clamps provide superior strain relief.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Yellow

Number Of Poles: 2

Number Of Wires: 3

Special Features: Rubber, Dust-Tight

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42M

CSA Standard: Yes

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121402

UR: No

#### DIMENSIONS

Depth (US): 3.74"

Diameter (US): 1.58"

Height (US): 2.07"  
Length (US): 3.10"

#### TECHNICAL INFORMATION

Amps: 20A  
NEMA Configuration Number: 5-20  
Volts (AC): 125

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant



---

## 20A, 125V RUBBER DUST-TIGHT CONNECTOR, YELLOW

1533 | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

#### Straight Blade Rubber Connector 20amp 125volt 5-20r

- Rubber body construction stands up to impacts, oils, chemicals, heat, and weather.
- Floating blades allow self-alignment with contacts for a firm, even electrical connection.
- Terminal screws backed-out, ready-to-wire, saving time and money.
- Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.
- Quick-drive assembly screws allow for fast installation, saving time and money.
- Self-centering cord clamps provide superior strain relief.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Yellow

Number Of Poles: 2

Number Of Wires: 3

Special Features: Rubber, Dust-Tight

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42M

CSA Standard: Yes

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121402

UR: No

#### DIMENSIONS

Depth (US): 3.74"

Diameter (US): 1.58"

Height (US): 2.07"  
Length (US): 3.10"

#### TECHNICAL INFORMATION

Amps: 20A  
NEMA Configuration Number: 5-20  
Volts (AC): 125

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

