ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

317 S Mercedes Ave
Casa Grande, AZ 85122-0000
Phone: 5206771167
Fax: 0000000000



165YL4A TEMFLEX VINYL ELECTRICAL TAPE, YL, 3/4" X 60'

MINNESOTA MINING (3M)

Catalog Number	165YL4A
Manufacturer	MINNESOTA MINING (3M)
Description	3M™ Temflex™ Vinyl Electrical Tape 165, Yellow, 3/4 in x 60 ft (19 mm x 18 m), 100 Rolls/Case
Weight per unit	0.1860 (lbs/each)
Product Category	Tools & Testers

Features

Adhesive Type	Rubber
Dielectric Strength	1000
Elongation At Break	2
Voltage Rating	600

Material, Color, and Finish

Backing Material	Polyvinyl Chloride PVC

Dimensions and Weight

Thickness	6

Descriptions

Description	TEMFLEX VINYL ELECTRICAL TAPE, YL, 3/4" X 60'
Features	3M™ Temflex™ Vinyl Electrical Tape 165 is a 6-mil thick, multi-purpose vinyl insulating tape available in 10 colors. It is designed to perform in ambient temperatures up to 194°F (90°C). The tape is conformable for cold weather application down to 32°F (0°C). It has excellent resistance to abrasion, moisture, alkalies, acid, copper corrosion and varying weather conditions. The combination of an elastic PVC backing and pressure-sensitive rubber-based adhesive provides electrical and mechanical protection w
Long Description	3M™ Temflex™ Vinyl Electrical Tape 165, Yellow, 3/4 in x 60 ft (19 mm x 18 m), 100 Rolls/Case
Product Type	3M™ Temflex™ Vinyl Electrical Tape 165
Extra Long Description	3M 7100169490 3M™ Temflex™ Vinyl E

Manufacturer Information

Brand	Temflex
	3M Electrical Products
GTIN	00076308925772
Manufacturers Part Number	165YL4A
	7100169490
UPC	054007

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
317 S Mercedes Ave
Casa Grande, AZ 85122-0000
Phone: 5206771167
Fax: 0000000000

Taxonomies, Classifications, and Categories

Category Description	TAPE

Packaging

Carton	1
Package	10
Weight Per Each	0.1860 (lbs/each)

Uses, Certifications, and Standards

Application	Insulation