



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



168020 1/2" Super Hawg - Tool Only

Milwaukee Electric Tool

Catalog Number	168020
Manufacturer	Milwaukee Electric Tool
Description	The 1/2 In. Super Hawg Has Power and Speed For Drilling Holes Of All Sizes In Wood Frame Construction. The 13 Amp Motor Has Two Operating Speeds Of 1750 and 450 RPM With A Clutch In The Low Gear Range. Speed Shifting Is Easy. The Comfort Grip Roto-Lok Handle Features 3 Positions With 90 Degree Left-Right Rotation For Maximum Operator Comfort For All Applications.
Weight per unit	16.3 (lbs/each)
Product Category	Power Tools - Corded

Features

Cord Length	8.0
idea granular category code	2288
Switch Type	Trigger
Voltage	120.0

Material, Color, and Finish

Handle Material	Metal
Housing Material	Metal

Dimensions and Weight

Height	5.25
Length	8.0
Width	25.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	1/2" SUPER HAWG - TOOL ONLY
extra long description	MILW 1680-20 Super Hawg Drill
Features	1/2 in. Super Hawg Drill
Long Description	The 1/2 in. Super Hawg has power and speed for drilling holes of all sizes in wood frame construction. The 13 amp motor has two operating speeds of 1750 and 450 RPM with a clutch in the low gear range. Speed shifting is easy. The comfort grip Roto-Lok handle features 3 positions with 90 degree left-right rotation for maximum operator comfort for all applications.
Product Type	Super Hawg Drill
Short Description	Super Hawg Drill
Special Features	Features: Clutch In Low Speed; High Operating Speeds For Maximum Productivity; 90 DEG Left-Right; Roto-Lok Handle For Maximum Operating Comfort; Easy Turn Gear Shift Knob; Comfort Grip Switch Handle And Gear Case With Front T-Bar Handle; Chuck Type: Keyed; Cord Type: 8 FT Fixed; Tool Weight: 14.700 LB; Capacity In Wood: 6 IN Hole Saw; Spindle Lock: No; Metal Capacity: 1/2 IN Twist Bit; Spindle Size: 5/8-16 IN; Gear Train: Triple; Construction Type: Grounded; Length: 22 IN; Clutch:

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242001972
Manufacturers Part Number	1680-20
UPC	045242001972

Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
Type	Super Hawg Drill

Packaging

Carton	1
Package	3
Weight	14.7
Weight Per each	16.335

Uses, Certifications, and Standards

Application	For Drilling Holes Of All Sizes In Wood Frame Construction
-------------	--