



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1895V Switch Tog SP 3POS 15A 120/277V Mom Iv

Eaton Wiring Devices

Catalog Number	1895V
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Industrial Grade Toggle Switch, Momentary Toggle, #14-10 Awg, 15A, Flush, 120/277V, Back and Side, Screw, Ivory, Load Type: Motor Control, Fan, Led, Incandescent, Elv, MLV, CFL, Flourescent, Halogen, 1P, Brass, Polycarbonate
Weight per unit	0.4500 (lbs/each)
Product Category	Gen Purpose Switches

Features

amperage rating	15
dimensions	1.3100 IN X 1.0000 IN X 3.2800 IN
Material	Polycarbonate
media	Yes
Poles	1
Voltage Rating	120/277 V

Descriptions

Description	SWITCH TOG SP 3POS 15A 120/277V MOM IV
extra long description	EWD 1895V Switch Tog SP 3Pos 15A 12
Features	Eaton's Arrow Hart broad line of extra heavy-duty industrial grade switches feature superior engineering, reliable performance and ease of installation. Available in toggle, lighted, pilot light, Corbin and locking versions.
Long Description	Eaton Arrow Hart industrial grade toggle switch, Momentary toggle, #14-10 AWG, 15A, Flush, 120/277V, Back and side, Screw, Ivory, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, 1P, Brass, Polycarbonate
Product Type	Switch Tog SP 3POS 15A 120/277V Mom Iv
Special Features	Momentary toggle

Manufacturer Information

Brand	Eaton Wiring Devices
GTIN	00040893613499
Manufacturers Part Number	1895V
UPC	040893613499

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	Industrial grade toggle switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.45

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility - Other
standard	UL Listed, CSA certified, cULus Listed