



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 1MCB400R 400A 1PH Main Service Module Main Breaker

Eaton Corp

Catalog Number	1MCB400R
Manufacturer	Eaton Corp
Description	Eaton Main Circuit Breaker, 400A, Aluminum, Nema 3R, Overhead/Underground, 65 Kaic, KD, Three-Wire, Single-Phase, 120/240V, (2) #3/0 Awg-250 Kcmil, (1) #2/0 Awg-500 Kcmil
Weight per unit	101.0 (lbs/each)
Product Category	Main Circuit Breaker Modules

### Features

amperage rating	400 A
dimensions	15.0000 IN X 24.0000 IN X 15.0000 IN
Phase	Single-phase
Voltage Rating	120/240 V

### Descriptions

Description	400A 1PH MAIN SERVICE MODULE MAIN BREAKER
extra long description	ETN 1MCB400R MAIN SERVICE MOD 400A
Features	Eaton's main service modules are part of Gangable Metering, which consists of a main service module used in conjunction with meter stacks to make a custom metering lineup. Gangable metering is used in large condominiums, strip malls or other applications where more than six units are metered.
Long Description	Eaton main circuit breaker, 400A, Aluminum, NEMA 3R, Overhead/underground, 65 kAIC, KD, Three-wire, Single-phase, 120/240V, (2) #3/0 AWG-250 kcmil, (1) #2/0 AWG-500 kcmil
Product Type	Main Service Mod 400A 1 Phase Main BRK

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786849053192
Manufacturers Part Number	1MCB400R
UPC	786849053192

### Taxonomies, Classifications, and Categories

Category Description	Meter Socket Accessories
Type	Main circuit breaker

### Availability

Status	Inactive
--------	----------

### Packaging

Carton	1
Weight Per each	101



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Building

Automation and Monitoring

standard

UL Listed