



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2008B 480V 1000W Turnlock

*Nsi Industries*

|                  |                                   |
|------------------|-----------------------------------|
| Catalog Number   | 2008B                             |
| Manufacturer     | Nsi Industries                    |
| Description      | Turnlock Relay Electronic 480V Ir |
| Weight per unit  | 0.2100 (lbs/each)                 |
| Product Category | Electronic Time Switches          |

### Features

|                |             |
|----------------|-------------|
| supply voltage | 400-550 VAC |
| Timing Range   | Instant On  |

### Dimensions and Weight

|      |                   |
|------|-------------------|
| Size | H=2.187 - W=3.187 |
|------|-------------------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 480V 1000W TURNLOCK  |
| extra long description | TORK 2008B 36 Crct Stacked Neutral   |
| Features               | Electronic Instant Response TurnLock, On 1.3-1.7, Off/On Ratio 1.5:1, 400-550V, 1000W Tungsten, 1800VA Ballast, 4A LED |
| Long Description       | TurnLock Relay Electronic 480V IR  |
| Product Type           | 36 CRCT Stacked Neutral  |
| Special Features       | 360 Joule MOV (Metal Oxide Varistor) Surge Arrestor - Instant On - 3-5 Seconds Off                                     |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00786261620170 |
| Manufacturers Part Number | 2008B          |
| UPC                       | 786261620170   |

### Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | Commercial dimmers, motion sensors, & photo cells |
| Type                 | Instant Response Turn Lock Photocontrol           |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 0.21 |

### Uses, Certifications, and Standards

|                          |                         |
|--------------------------|-------------------------|
| Application              | Street-Highway Lighting |
| Enclosure                | Polycarbonate           |
| environmental conditions | -40 to + 158 F          |
| Frequency Rating         | 50-60 Hz                |
| Mounting                 | TURN LOCK               |
| Operating Temperature    | -40 to + 158 F          |