



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2097TRGRY Radiant Self Test TR Gfci 20A 125V Gy *Pass & Seymour/Legrand*

| | |
|------------------|---|
| Catalog Number | 2097TRGRY |
| Manufacturer | Pass & Seymour/Legrand |
| Description | 20A 125V Self-Test Tamper-Resistant Gfci Gray |
| Weight per unit | 0.2750 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|------------------|---------------------|
| actuator | Control Circuit |
| amperage rating | 20 |
| connection | Back and side wire |
| interrupt rating | 4 to 6 mA |
| Material | Thermoplastic |
| media | Yes |
| Poles | 2 |
| trip range | 4 to 6 mA |
| Trip Type | .025 Second Nominal |
| Voltage Rating | 125 |

Dimensions and Weight

| | |
|--------|------|
| Height | 4.2 |
| Length | 1.03 |
| Width | 1.73 |

Descriptions

| | |
|------------------------|---|
| Description | RADIANT SELF TEST TR GFCI 20A 125V GY |
| extra long description | P&S 2097TRGRY RADIANT SELF TEST TR |
| Long Description | 20A 125V Self-Test Tamper-Resistant GFCI Gray |
| Product Type | Radiant Self Test TR Gfci 20A 125V Gry |
| Special Features | Pass & Seymour invented the GFCI receptacle, and at Legrand, we're constantly reinventing it to ensure the highest level of safety possible. From the most advanced self-testing device to audible alarms to nightlight combos, we're continuously resetting the bar on GFCI innovation and safety. |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007036282 |
| Manufacturers Part Number | 2097-TRGRY |
| UPC | 785007036282 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential Switches |
| Type | Specification Grade Tamper-Resistant 20A Self-Test Duplex GFCI |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.275 |

Uses, Certifications, and Standards

| | |
|--------------------------|------------------------|
| Application | Commercial/Residential |
| environmental conditions | 95% Humidity, UL 94 V2 |
| Frequency Rating | 60 Hz |
| Operating Temperature | -35°C to +66°C |
| standard | cULus, UL Listed, FSUL |