



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2097TRWRGRY Radiant Self Test TR WR GFI 20A 125V Gy

*Pass & Seymour/Legrand*

Catalog Number	2097TRWRGRY
Manufacturer	Pass & Seymour/Legrand
Description	Gfci Receptacles From The Radiant Registered Collection Self-Test Automatically Every Three Seconds to Ensure Reliable Protection From Shock Due to Ground Fault Occurrences. Meeting National Electrical Code Requirements For Ground Fault Protection, Gfci Receptacles Make It Easier to Recognize and Fix Trips Right Where They Happen – No More Confusion At The Breaker Box. Also Including Tamper and Weather* Resistance, This Model Was Designed For Use In Outdoor Spaces. Maximize Safety, In Style, With Gfci Prot
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

actuator	Control Circuit
amperage rating	20
connection	Back and side wire
indoor/outdoor	Outdoor
interrupt rating	4 to 6 mA
Material	Thermoplastic
Mounting Type	Box
Number of Gangs	1.0
Outlet Type	Weather-Resistant, GFCI, Tamper-Resistant, Self-Test
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage Rating	125

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Height	4.2
Length	1.03
Width	1.73



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	RADIANT SELF TEST TR WR GFI 20A 125V GY
extra long description	P&S 2097TRWRGRY RADIANT SLF TST TR
Long Description	GFCI receptacles from the radiant Registered Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. Also including tamper and weather* resistance, this model was designed for use in outdoor spaces. Maximize safety, in style, with GFCI prot
Product Type	Radiant SLF TST TR WR GFI 20A 125V Gry
Special Features	Spec Grade, Weather Resistant

## Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007036312
Manufacturers Part Number	2097TRWRGRY
UPC	785007036312

## Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Outlet

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	10
Weight Per each	0.275

## Uses, Certifications, and Standards

Application	Commercial/Residential
environmental conditions	95% Humidity, UL 94 V2
Frequency Rating	60 Hz
nema rating	20A
Operating Temperature	-35°C to +66°C
standard	CULUS, UL, cULus, UL Listed, FSUL