



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

PRODUCT
IMAGE
COMING
SOON

2107A 120/277V 2000W SPST Conduit Mo *Nsi Industries*

| | |
|------------------|---|
| Catalog Number | 2107A |
| Manufacturer | Nsi Industries |
| Description | Spec Grade 1/2" Stem Diecast Zinc, On 1-5FC/Off 3-15FC, 6"Leads, 120/208-277 Vac, 2000W Tungsten, 1800VA Ballast, 600VA Led |
| Weight per unit | 0.6000 (lbs/each) |
| Product Category | Lighting Controls |

Features

| | |
|----------------|------------------|
| supply voltage | 120 /208-277 VAC |
| Timing Range | 0-2 min |

Dimensions and Weight

| | |
|------|-----------------------|
| Size | .500 Conduit Mount IN |
|------|-----------------------|

Descriptions

| | |
|------------------------|--|
| Description | 120/277V 2000W SPST CONDUIT MO |
| extra long description | TORK 2107A Photocontrol Stem Alumin |
| Long Description | Spec Grade 1/2" Stem DieCast Zinc, On 1-5fc/Off 3-15fc, 6"Leads, 120/208-277 VAC, 2000W Tungsten, 1800VA Ballast, 600VA LED |
| Product Type | Photocontrol Stem Aluminum 208-277V |
| Special Features | 1/2 Conduit Mount - Time Delay On And Off - Cadmium Sulphide Epoxy Coated 1 Diameter Cell IN |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | 98010027731 |
| GTIN | 00786261620347 |
| Manufacturers Part Number | 2107A |
| sub brand | Photocontrols |
| UPC | 786261620347 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | Commercial dimmers, motion sensors, & photo cells |
| Type | Die Cast Zinc Photocontrol |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 0.6 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Parking Lot-Building Perimeter-Outdoor Signage Lighting |
| Enclosure | Zinc Diecast |
| environmental conditions | -40 to 140 F |
| Frequency Rating | 50-60 Hz |
| Mounting | Conduit Mount |
| Operating Temperature | -40 to + 140 F |
| standard | UL-CSA |