



Auto Voltage/Continuity Tester W/ Resistance

2213-20



What's Included

- (1) Auto Voltage/Continuity Tester W/ Resistance (2213-20)
- (1) Belt Clip
- (1) Test Lead Set
- (2) AAA Batteries
- (1) Manual

Where to Buy

-  Shop Online
-  Find Local

The Milwaukee Auto Voltage/Continuity Tester W/ Resistance combines the features you get from high performance electrical meters into an accurate, simple, and productive tester. While traditional testers only indicate broad voltage ranges that mask electrical issues like voltage drops, the Milwaukee Auto Voltage/Continuity Tester W/ Resistance delivers measurements down to the decimal and displays them on an easy to read LCD. The tester also automatically determines whether to test for Voltage or Continuity and is compatible with common threaded carrying and mounting accessories like belt clips and magnets. The LED worklight provides visibility in low-lit areas and test lead holders conveniently store the probes for when the job is done. This Auto Voltage/Continuity Tester w/ Resistance is the ideal tester for use on outlets, switches, wires, and breaker panels; perfect for any Residential, Apprentice or Journeymen Electrician looking for an accurate, simple and productive tester at an affordable price.


Accessory Attachments: ¼”-20 Thread Compatible, Belt Clip (Included), Magnet (Sold Separately 49-24-2351)

Features

- Backlit LCD display for easy-to-read measurements
- Belt clip eliminates holding the meter while you work
- LED worklight for low-lit areas
- Dual LED and audible indicators for fast and convenient test results
- Built-in test lead holders for quick storage
- Auto-ranging for simple use
- Replaceable test leads for greater flexibility
- Rugged over-molding protects your meter in any environment

Specifications

Safety Category Rating	CAT IV 600V AC/DC
Voltage AC/DC	600V
Resistance	Up to 20kΩ
Continuity	Yes
Backlight	Yes
Rugged Overmolding	Yes
Tool Warranty	5 Years
Battery Type	Alkaline (AAA)
LED Light	Yes
Auto-Ranging	Yes
Alerts	Audible/LED
Replaceable Leads	Yes
Accessory	¼”-20 Thread



© 2018 by Milwaukee Tool. All rights reserved.



Auto Voltage/Continuity Tester W/ Resistance

2213-20



What's Included

- (1) Auto Voltage/Continuity Tester W/ Resistance (2213-20)
- (1) Belt Clip
- (1) Test Lead Set
- (2) AAA Batteries
- (1) Manual

Where to Buy

-  Shop Online
-  Find Local

The Milwaukee Auto Voltage/Continuity Tester W/ Resistance combines the features you get from high performance electrical meters into an accurate, simple, and productive tester. While traditional testers only indicate broad voltage ranges that mask electrical issues like voltage drops, the Milwaukee Auto Voltage/Continuity Tester W/ Resistance delivers measurements down to the decimal and displays them on an easy to read LCD. The tester also automatically determines whether to test for Voltage or Continuity and is compatible with common threaded carrying and mounting accessories like belt clips and magnets. The LED worklight provides visibility in low-lit areas and test lead holders conveniently store the probes for when the job is done. This Auto Voltage/Continuity Tester w/ Resistance is the ideal tester for use on outlets, switches, wires, and breaker panels; perfect for any Residential, Apprentice or Journeymen Electrician looking for an accurate, simple and productive tester at an affordable price.


Accessory Attachments: ¼”-20 Thread Compatible, Belt Clip (Included), Magnet (Sold Separately 49-24-2351)

Features

- Backlit LCD display for easy-to-read measurements
- Belt clip eliminates holding the meter while you work
- LED worklight for low-lit areas
- Dual LED and audible indicators for fast and convenient test results
- Built-in test lead holders for quick storage
- Auto-ranging for simple use
- Replaceable test leads for greater flexibility
- Rugged over-molding protects your meter in any environment

Specifications

Safety Category Rating	CAT IV 600V AC/DC
Voltage AC/DC	600V
Resistance	Up to 20kΩ
Continuity	Yes
Backlight	Yes
Rugged Overmolding	Yes
Tool Warranty	5 Years
Battery Type	Alkaline (AAA)
LED Light	Yes
Auto-Ranging	Yes
Alerts	Audible/LED
Replaceable Leads	Yes
Accessory	¼”-20 Thread



© 2018 by Milwaukee Tool. All rights reserved.