


### Wallplate Accessories

Description	Finish/Material	Color Suffix	Catalog No.	
GFCI Extension Ring for use with GFCIs, 7/8" spacer, cULus Certified	Polypropylene	B, BLK, LA, V, W	<input type="checkbox"/> <b>GFER</b> __	
Adapter – Decorator to Blank	Polycarbonate	B, LA, V, W	<input type="checkbox"/> <b>2160</b> __	•
Adapter – Decorator to Toggle	Polycarbonate	V, W	<input type="checkbox"/> <b>2161</b> __	•
Toggle & Receptacle Wallplate Screws #6-32 x 1/2"	Metal, Baked Enamel Head	A, B, LA, V, W	<input type="checkbox"/> <b>231</b> __	
	Nylon	RD, V, W	<input type="checkbox"/> <b>232</b> __	•
Toggle & Receptacle Wallplate Screws #6-32 x 5/16"	Metal, Baked Enamel Head	LA, V, W	<input type="checkbox"/> <b>2231</b> __	



**GFER**



**2161**



**231**



 **UL** GFER: cULus Listed to UL514C, certified to CSA C22.2, no. 18-98

### Louwer Wallplate Accessories

Description	Material	Catalog No.	
Recessed Pilot Light Lamp Holder with 6 Watt Clear S-6 Bulb	Urea	<input type="checkbox"/> <b>153</b>	•



**153**


  Listed to UL496, file no. E18522; CSA certified to C22.2, no. 43

### LED Steplight

Description	Color Suffix	Catalog No.
15A, 120V/AC LED Steplight, Includes Vertical & Horizontal Louvered Wallplates	A, LA, W	<input type="checkbox"/> <b>7739-BOX</b>



**7739-BOX**

 **UL** cULus Listed to UL1598, file no. E328628; CSA certified to C22.2, no. 43

**Color Ordering Information:** For ordering devices, include Cat. No. followed by the color code: A (Almond), B (Brown), BLK (Black), LA (Light Almond), RD (Red), V (Ivory), W (White)

**Dimensional Information:** C-5 – C-6

**Specification Information:** Please visit [www.cooperwiringdevices.com](http://www.cooperwiringdevices.com)

 **NAFTA Compliant:** See page F-21

Wallplate Accessories

Description	Finish/Material	Color Suffix	Catalog No.	
GFCI Extension Ring for use with GFCIs, 7/8" spacer, cULus Certified	Polypropylene	B, BLK, LA, V, W	<input type="checkbox"/> <b>GFER</b> __	
Adapter – Decorator to Blank	Polycarbonate	B, LA, V, W	<input type="checkbox"/> <b>2160</b> __	•
Adapter – Decorator to Toggle	Polycarbonate	V, W	<input type="checkbox"/> <b>2161</b> __	•
Toggle & Receptacle Wallplate Screws #6-32 x 1/2"	Metal, Baked Enamel Head	A, B, LA, V, W	<input type="checkbox"/> <b>231</b> __	
	Nylon	RD, V, W	<input type="checkbox"/> <b>232</b> __	•
Toggle & Receptacle Wallplate Screws #6-32 x 5/16"	Metal, Baked Enamel Head	LA, V, W	<input type="checkbox"/> <b>2231</b> __	



GFER



2161



231

GFER: cULus Listed to UL514C, certified to CSA C22.2, no. 18-98

Louwer Wallplate Accessories

Description	Material	Catalog No.	
Recessed Pilot Light Lamp Holder with 6 Watt Clear S-6 Bulb	Urea	<input type="checkbox"/> <b>153</b>	•



153

Listed to UL496, file no. E18522; CSA certified to C22.2, no. 43

LED Steplight

Description	Color Suffix	Catalog No.
15A, 120V/AC LED Steplight, Includes Vertical & Horizontal Louvered Wallplates	A, LA, W	<input type="checkbox"/> <b>7739-BOX</b>



7739-BOX

cULus Listed to UL1598, file no. E328628; CSA certified to C22.2, no. 43

**Color Ordering Information:** For ordering devices, include Cat. No. followed by the color code: A (Almond), B (Brown), BLK (Black), LA (Light Almond), RD (Red), V (Ivory), W (White)

**Dimensional Information:** C-5 – C-6

**Specification Information:** Please visit [www.cooperwiringdevices.com](http://www.cooperwiringdevices.com)

**NAFTA Compliant:** See page F-21