



## RECTORSEAL® PIPE THREAD SEALANTS

### RectorSeal No. 5®

Multi-purpose pipe thread sealant

Code	Description	Qty.
25790	1-¾ oz.	24
25631	¼ pt.	24
25551	½ pt.	24
25431	1 pt.	12
25300	1 qt.	12
25271	1 gal.	4
25191	5 gal.	1
25112	55 gal.	1



#### FEATURES

- Soft set / Slow drying
- Lead free
- Smooth application
- 2 year shelf life
- Certified to NSF/ANSI 61-G

**Application** • Lubricates and protects threaded pipe and fittings • Can be pressurized immediately up to 100 psi for piping up to 2" diameter • Ideal for a wide variety of fluids and gases including potable water

#### Recommended for

- Galvanized Steel
- Iron • Brass
- Copper
- Aluminum
- Stainless Steel
- Polyethylene
- RTRP • PVC



Also available in 55 gal. container.

### RectorSeal T plus 2®

PTFE enriched pipe thread sealant

Code	Description	Qty.
23710	1-¾ oz.	24
23631	¼ pt.	24
23551	½ pt.	24
23431	1 pt.	12
23391	1 qt.	12
23271	1 gal.	4
23191	5 gal.	1
23112	55 gal.	1



#### FEATURES

- Non-setting
- Lead free
- 2 year shelf life
- Certified to NSF/ANSI 61-G

**Application** • Contains PTFE & synthetic fibers for superior performance • Can be pressurized immediately following application

#### Recommended for

- Galvanized Steel • Iron
- Brass • Copper
- Aluminum
- Stainless Steel
- Polyethylene
- RTRP • PVC
- CPVC • ABS



Also available in 55 gal. container.

\*FBC™ System Compatible™ indicates that this product has been tested, and is monitored on an ongoing basis, to assure its chemical compatibility with FlowGuard Gold®, BlazeMaster® and Corzan® pipe and fittings. \*\*FBC™, FlowGuard Gold®, BlazeMaster® and Corzan® are licensed trademarks of the Lubrizol Corporation.

Contact: RectorSeal® P 713-263-8001 | 800-231-3345 F 713-263-7577 | 800-441-0051 W www.rectorseal.com



## RECTORSEAL® PIPE THREAD SEALANTS

### RectorSeal No. 5®

Multi-purpose pipe thread sealant

Code	Description	Qty.
25790	1-¾ oz.	24
25631	¼ pt.	24
25551	½ pt.	24
25431	1 pt.	12
25300	1 qt.	12
25271	1 gal.	4
25191	5 gal.	1
25112	55 gal.	1



#### FEATURES

- Soft set / Slow drying
- Lead free
- Smooth application
- 2 year shelf life
- Certified to NSF/ANSI 61-G

**Application** • Lubricates and protects threaded pipe and fittings • Can be pressurized immediately up to 100 psi for piping up to 2" diameter • Ideal for a wide variety of fluids and gases including potable water

#### Recommended for

- Galvanized Steel
- Iron • Brass
- Copper
- Aluminum
- Stainless Steel
- Polyethylene
- RTRP • PVC



Also available in 55 gal. container.

### RectorSeal T plus 2®

PTFE enriched pipe thread sealant

Code	Description	Qty.
23710	1-¾ oz.	24
23631	¼ pt.	24
23551	½ pt.	24
23431	1 pt.	12
23391	1 qt.	12
23271	1 gal.	4
23191	5 gal.	1
23112	55 gal.	1



#### FEATURES

- Non-setting
- Lead free
- 2 year shelf life
- Certified to NSF/ANSI 61-G

**Application** • Contains PTFE & synthetic fibers for superior performance • Can be pressurized immediately following application

#### Recommended for

- Galvanized Steel • Iron
- Brass • Copper
- Aluminum
- Stainless Steel
- Polyethylene
- RTRP • PVC
- CPVC • ABS



Also available in 55 gal. container.

\*FBC™ System Compatible™ indicates that this product has been tested, and is monitored on an ongoing basis, to assure its chemical compatibility with FlowGuard Gold®, BlazeMaster® and Corzan® pipe and fittings. \*\*FBC™, FlowGuard Gold®, BlazeMaster® and Corzan® are licensed trademarks of the Lubrizol Corporation.

Contact: RectorSeal® P 713-263-8001 | 800-231-3345 F 713-263-7577 | 800-441-0051 W www.rectorseal.com