



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



24168SDSS4 Encl 24X16X8 N4X SS4 SLD HC, QTR TRN LTCH *Cooper B-Line/Cable Tray*

Catalog Number	24168SDSS4
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 24" Height, 8" Length, 16" Width, Nema 4X, Hinged Cover, SDSS4 Enclosure, Wall Mount, Medium Single Door, Thru Holes, Opt. External Mounting Feet, 304 Stainless Steel, Seamless Poured In-Place Gasket
Weight per unit	24.6 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

dimensions	8.0000 IN X 16.0000 IN X 24.0000 IN
Material	304 Stainless Steel
Mounting Type	Wall

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	16.00 In Width X 8.00 In Depth X 24.00 In Height
------	--

Descriptions

Description	ENCL 24X16X8 N4X SS4 SLD HC,QTR TRN LTCH
extra long description	B-LINE 24168-SDSS4 TYPE 4X SSL SGL-
Features	Eaton's B-Line series wall mounted panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments.
Long Description	Eaton B-Line series wall mounted panel enclosure,24" height,8" length,16" width,NEMA 4X,Hinged cover,SDSS4 enclosure,Wall mount,Medium single door,Thru holes,opt. external mounting feet,304 stainless steel,Seamless poured in-place gasket
Product Type	Type 4X SSL SGL-Solid Door Enc, 24X16X8
Special Features	Stainless 1/4 turn latches

Manufacturer Information

Brand	Eaton
GTIN	00782051093605
Manufacturers Part Number	24168-SDSS4
UPC	782051093605

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Wall mounted panel enclosure



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	24.612

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative EnergyCommercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherDatacenters - IT Space: CI and Hyper ConvergedUtility - Substations, Utility Transmission and DistributionCommercial / Institutional Buildings / Structures - Lighting and Lighting ControlsCommercial / Institutional Buildings / Structures - Building Automation and MonitoringCommercial / Institutional Buildings / Structures - Power Distribution and Con
Mounting	WALL
nema rating	4X
standard	NEMA,UL 50,CSA C22.2.