



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



240122 M12 1/4" Hex Screwdriver Kit

Milwaukee Electric Tool

Catalog Number	240122
Manufacturer	Milwaukee Electric Tool
Description	Optimized For The Professional Who Frequently Encounters Precision Fastening Applications, The Milwaukee® M12™ 1/4 In. Hex Screwdriver Delivers Unmatched Precision, Power and Portability Along With A Slimmer, More Ergonomic Grip. A Variable Speed Trigger and 0-500RPM Give The User Unrivaled Fastening Control, 15+1 Clutch Settings Prevent Over Tightening Fasteners, and 175 In-LBS. Of Torque Provides The Ability to Accomplish Tough Applications. At 6-1/2 In. Long and Weighing Only 2.0 LBS; Its Compact, Light
Weight per unit	4.6 (lbs/each)
Product Category	Battery Driven Tools

Features

Battery Voltage	12
Switch Type	Trigger

Material, Color, and Finish

Housing Material	Glass-filled Nylon
------------------	--------------------

Dimensions and Weight

Length	6.5
Width	3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	M12 1/4" HEX SCREWDRIVER KIT
extra long description	MILW 2401-22 M12 Screwdriver Kit
Features	The M12 series offers solutions that deliver portable productivity. They take on the tightest spaces and are specifically built to go anywhere. They are trade focused, system wide, lightweight with ergonomic design make portability easy, and operation faster and more productive.
Long Description	Optimized for the professional who frequently encounters precision fastening applications, the Milwaukee® M12™ 1/4 in. hex screwdriver delivers unmatched precision, power and portability along with a slimmer, more ergonomic grip. A variable speed trigger and 0-500RPM give the user unrivaled fastening control, 15+1 clutch settings prevent over tightening fasteners, and 175 in-lbs. Of torque provides the ability to accomplish tough applications. At 6-1/2 in. long and weighing only 2.0 lbs; its compact, light
Product Type	M12 Screwdriver Kit
Special Features	Quick Bit-Loading 1/4 IN Hex Chuck For Bit Insertion And Release With One Hand; Battery Fuel Gauge For Displaying Remaining Run-Time; Metal Gear Housing For Job Site Durability; Built-In Led For Illumination Of Dark Work Spots; Variable Speed Trigger For Output Power Control; Over-Mold Side And Grip For Secure Grip And Work Surface Protection; Number Of Batteries: 2; Chuck Size: 1/4 IN; Chuck Type: Hex; Clutch Settings: 14 + 1; Spindle Lock: Yes; Tool Weight: 2 LB; Reversible Battery: No; Capacity In Steel

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242293025
Manufacturers Part Number	2401-22
UPC	045242293025

Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
Type	CORDLESS

Packaging

Carton	1
Package	5
Weight Per each	4.62