



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 242464XS Encl 24X24X6 N4X SS4 CH Clamp CVR

Cooper B-Line/Cable Tray

Catalog Number	242464XS
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 24" Height, 6" Length, 24" Width, Nema 4X, Hinged Cover, 4XS Enclosure, Wall Mount, Medium Single Door, External Mounting Feet, 304 Stainless Steel, Seamless Poured In-Place Gasket
Weight per unit	43.8 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

### Features

dimensions	6.0000 IN X 24.0000 IN X 24.0000 IN
Material	304 Stainless Steel
Mounting Type	Wall

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Size	24.00 In Width X 6.00 In Depth X 24.00 In Height
------	--

### Descriptions

Description	ENCL 24X24X6 N4X SS4 CH CLAMP CVR
extra long description	B-LINE 24246-4XS TYPE 4X SSL SGL-DO
Features	Eaton's B-Line series wall mounted panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments.
Long Description	Eaton B-Line series wall mounted panel enclosure, 24" height, 6" length, 24" width, NEMA 4X, Hinged cover, 4XS enclosure, Wall mount, Medium single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket
Product Type	Type 4X SSL SGL-Door Enc, 24X24X6
Special Features	Stainless door clamps

### Manufacturer Information

Brand	Eaton
GTIN	00782051096705
Manufacturers Part Number	24246-4XS
UPC	782051096705

### Taxonomies, Classifications, and Categories

Type	Wall mounted panel enclosure
------	------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	43.8

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial/Inst Bldg Structures - AftermarketOther IT and Datacom - IT and Datacomm - OtherUtility - Substations, Utility Transmission and DistributionGeneration - Renewable Energy - Alternative EnergyCommercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherDatacenters - IT Space: CI and Hyper ConvergedCommercial / Institutional Buildings / Structures - Lighting and Lighting ControlsCommercial / Instituti
Mounting	EXTERNAL FEET, WALL
nema rating	4X
standard	UL 50,NEMA,CSA C22.2.