



Catalog Number: 24248-SC1-NK
Item Description: N1 SCREW COVER ENCL NK
UPC Code: 784572104358


Brand Name: Milbank
Type: Screw Cover
Special Features: Cover Secured with Plated Screws
Application: Enclosure for Mounting Electrical Equipment
Standard: UL Listed
Number Of Outlet: 0
Material: Steel with Powder Coat Finish
Color: ANSI 61 Gray
Mounting: Wall Mount
NEMA Rating: Type 1




Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

CATALOG#	LABEL#
24248-SC1-()	1002135
RC-24248-SC1-()	1125021
SPSC-24248()	1132714

ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	(SEE CHART)	BACK WELDMENT
2	1	(SEE CHART)	COVER PLATE
3	4	1001290	SCREW, 10-32 X 5/16
4	1	(SEE CHART)	U/L LISTING LABEL
5	1	1002475	BAG ASSY (GROUND SCREW)



NOTES:
 1.) PLACE BAG ASS'Y INSIDE ENCLOSURE (NOT SHOWN).
 2.) USE CARTON #1002955 FOR SHIPPING. (1 PER)



SUFFIX	MATERIAL	FINISH	INSTALL K.O.s	WELDMENT NO.	COVER NO.
-SC1	GALV. STEEL 16 GA. SHELL 14 GA. COVER	MILBANK LIGHT GRAY	YES	1154452	1153621
-SC1-NK			NO	1154453	
-SC1-NP		YES	1154454		
-SC1-NK-NP	.064 ALUM. SHELL .081 ALUM COVER	NONE	NO	1154455	1003267
-SC1XA		MILBANK LIGHT GRAY	YES	1154456	1154451
-SC1XA-NK			NO	1154457	
-SC1XA-NP	NONE	YES	1154458	1154450	
-SC1XA-NK-NP	NO	1154459			

Material:	(SEE CHART)		General Offices: Kansas City, MO		
Finish:	(SEE CHART)		Title:	24248 SCREW COVER TYPE 1 ENCLOSURE	
Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2*				Catalog No.:	(SEE CHART)
		Customer:		EALER ELECTRIC	
Scale: NTS		Checked By:		Drawing No.:	
Drawn By: DY		Approved By:		Date: 04/26/01	
				Sheet 1 of 1	

NEMA DWG.: #152

D4	7/14/11	CHART VERSIONS (ECO #20959)	DF			
----	---------	-----------------------------	----	--	--	--



Catalog Number: 24248-SC1-NK
Item Description: N1 SCREW COVER ENCL NK
UPC Code: 784572104358


Brand Name: Milbank
Type: Screw Cover
Special Features: Cover Secured with Plated Screws
Application: Enclosure for Mounting Electrical Equipment
Standard: UL Listed
Number Of Outlet: 0
Material: Steel with Powder Coat Finish
Color: ANSI 61 Gray
Mounting: Wall Mount
NEMA Rating: Type 1




Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

CATALOG#	LABEL#
24248-SC1-()	1002135
RC-24248-SC1-()	1125021
SPSC-24248()	1132714

ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	(SEE CHART)	BACK WELDMENT
2	1	(SEE CHART)	COVER PLATE
3	4	1001290	SCREW, 10-32 X 5/16
4	1	(SEE CHART)	U/L LISTING LABEL
5	1	1002475	BAG ASSY (GROUND SCREW)



NOTES:
 1.) PLACE BAG ASSY INSIDE ENCLOSURE (NOT SHOWN).
 2.) USE CARTON #1002955 FOR SHIPPING. (1 PER)



SUFFIX	MATERIAL	FINISH	INSTALL K.O.s	WELDMENT NO.	COVER NO.
-SC1	GALV. STEEL 16 GA. SHELL 14 GA. COVER	MILBANK LIGHT GRAY	YES	1154452	1153621
-SC1-NK			NO	1154453	
-SC1-NP		YES	1154454		
-SC1-NK-NP	.064 ALUM. SHELL .081 ALUM COVER	NONE	NO	1154455	1003267
-SC1XA		MILBANK LIGHT GRAY	YES	1154456	1154451
-SC1XA-NK			NO	1154457	
-SC1XA-NP	NONE	YES	1154458	1154450	
-SC1XA-NK-NP	NO	1154459			

Material:	(SEE CHART)		General Offices: Kansas City, MO	
Finish:	(SEE CHART)		Title:	24248 SCREW COVER TYPE 1 ENCLOSURE
Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2°			Catalog No.:	(SEE CHART)
		Projection	Customer:	EALER ELECTRIC
Scale:	NTS	Checked By:	Drawing No.:	1001915
Drawn By:	DY	Approved By:	Date:	04/26/01 Sheet 1 of 1

NEMA DWG.: #152

D4	7/14/11	CHART VERSIONS (ECO #20959)	DF			
----	---------	-----------------------------	----	--	--	--