



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



24241612 24X24X16 N12 CH Clamp CVR

Cooper B-Line/Cable Tray

Catalog Number	24241612
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 24" Height, 16" Length, 24" Width, Nema 12, Hinged Cover, 12 Enclosure, Wall Mount, Medium Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	60.8 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

dimensions	16.0000 IN X 24.0000 IN X 24.0000 IN
Mounting Type	Wall

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	24.00 In Width X 16.00 In Depth X 24.00 In Height
------	---

Descriptions

Description	24X24X16 N12 CH CLAMP CVR
extra long description	B-LINE 242416-12 TYPE 12 SGL-DOOR E
Features	Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids.
Long Description	Eaton B-Line series wall mounted panel enclosure, 24" height, 16" length, 24" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 SGL-Door Enc, 24X24X16
Special Features	Plated door clamps

Manufacturer Information

Brand	Cooper B-Line/Cable Tray
GTIN	00782051804904
Manufacturers Part Number	242416-12
UPC	782051804904

Taxonomies, Classifications, and Categories

Type	Type 12 panel enclosures
------	--------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	60.8

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Building Automation and Monitoring Commercial / Institutional Buildings / Structures - Critical Power Commercial / Institutional Buildings / Structures - Commercial/Inst Bldg Structures - Aftermarket Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other Other IT and Datacom - IT and Datacomm - Other Utility - Substations, Utility Transmission and Distribution Commercial / Institutional Buildings / Structure
Mounting standard	EXTERNAL FEET, WALL UL 508A, NEMA, CSA C22.2.