


[Home](#) > ... > [M12™ 2-Tool Combo Kits](#) > M12 Cordless LITHIUM-ION 2-Tool Combo Kit

M12 Cordless LITHIUM-ION 2-Tool Combo Kit

2494-22

[PRINT](#)

 Be the first to [Write a Review](#)

The 2494-22 M12™ Cordless LITHIUM-ION 2-Tool Combo Kit includes the 3/8" Drill Driver and the 1/4" Hex Impact Driver (2450-20). The innovative M12™ cordless LITHIUM-ION system is designed to deliver the power and torque required for professional applications, in a size that reaches the tightest and toughest places. Powered by REDLITHIUM™, the M12™ cordless LITHIUM-ION system offers unmatched power, speed, and tool belt portability.

Includes

- 2410-20 M12™ 3/8" Drill Driver
- 2450-20 M12™ 1/4" Hex Impact Driver
- (2) 48-11-2401 M12™ REDLITHIUM™ Batteries
- 48-59-2401 M12™ 30-Minute Charger
- Contractor Bag

[FIND RETAILERS](#)

FEATURES

- M12™ 3/8" Drill Driver delivers best-in-class 275 in.-lbs. of peak torque, 0-400 / 0-1,500 RPM at just 2.6 lbs.
- M12™ 1/4" Hex Impact Driver delivers best-in-class 850 in.-lbs. of torque at only 2.3 lbs. and 0-2000 RPM for fast driving.

SPECIFICATIONS

Voltage	12V
Battery	LITHIUM-ION
Bag/Case Type	Contractor Bag
Shipping Weight	9.0 lbs

REVIEW SNAPSHOT® by PowerReviews

 Not yet rated. Be the first to [Write a Review](#)

RELATED ITEMS


 M12™ RED LITHIUM™
Battery

 M12™ LITHIUM-ION
AC/DC Wall and Vehicle
Charger

 M12™ Cordless
LITHIUM-ION Multi-Tool -
Bare Tool Only

[MORE RELATED ITEMS](#)

Sign Up for the
Heavy Duty Club



SUBMIT ▶

Products

New Products & Offers
Tools
Accessories
Test & Measurement
Milwaukee Gear
Print Current Catalog

Parts & Service

e-SERVICE Tool Repair
Test & Measure Service
Find a Service Center
Download Manuals
Parts Pricing
Milwaukee Warranty
Lightning Max Repair
FAQ's

News & Media

Press Releases
MilwaukeeCain.com
Product Reviews
Media Center
Media Inquiries

About Us

Milwaukee Story
Careers
Locations
Buy Now
Contact Us