

Nothing but **HEAVY DUTY**™

Search Milwaukeeeetool.com

NEW PRODUCTS &amp; OFFERS

TOOLS ▾

ACCESSORIES ▾

TEST &amp; MEASUREMENT ▾

HAND TOOLS


PARTS &amp; SERVICE ▾

BUY NOW

Home > ... > [M12™ 2-Tool Combo Kits](#) > M12 Cordless LITHIUM-ION 2-Tool Combo Kit

# M12 Cordless LITHIUM-ION 2-Tool Combo Kit 2494-22

PRINT

Be the first to [Write a Review](#)

The 2494-22 M12™ Cordless LITHIUM-ION 2-Tool Combo Kit includes the 3/8" Drill Driver and the 1/4" Hex Impact Driver (2450-20). The innovative M12™ cordless LITHIUM-ION system is designed to deliver the power and torque required for professional applications, in a size that reaches the tightest and toughest places. Powered by REDLITHIUM™, the M12™ cordless LITHIUM-ION system offers unmatched power, speed, and tool belt portability.

### Includes

- 2410-20 M12™ 3/8" Drill Driver
- 2450-20 M12™ 1/4" Hex Impact Driver
- (2) 48-11-2401 M12™ REDLITHIUM™ Batteries
- 48-59-2401 M12™ 30-Minute Charger
- Contractor Bag

FIND RETAILERS

### FEATURES

- M12™ 3/8" Drill Driver delivers best-in-class 275 in.-lbs. of peak torque, 0-400 / 0-1,500 RPM at just 2.6 lbs.
- M12™ 1/4" Hex Impact Driver delivers best-in-class 850 in.-lbs. of torque at only 2.3 lbs. and 0-2000 RPM for fast driving.

### SPECIFICATIONS

Voltage	12V
Battery	LITHIUM-ION
Bag/Case Type	Contractor Bag
Shipping Weight	9.0 lbs

### REVIEW SNAPSHOT® by PowerReviews

Not yet rated. Be the first to [Write a Review](#)

### RELATED ITEMS



M12™ RED LITHIUM™  
Battery



M12™ LITHIUM-ION  
AC/DC Wall and Vehicle  
Charger



M12™ Cordless  
LITHIUM-ION Multi-Tool -  
Bare Tool Only

MORE RELATED ITEMS

Sign Up for the  
Heavy Duty Club



SUBMIT ▶

### Products

New Products & Offers  
Tools  
Accessories  
Test & Measurement  
Milwaukee Gear  
Print Current Catalog

### Parts & Service

e-SERVICE Tool Repair  
Test & Measure Service  
Find a Service Center  
Download Manuals  
Parts Pricing  
Milwaukee Warranty  
Lightning Max Repair  
FAQ's

### News & Media

Press Releases  
MilwaukeeCain.com  
Product Reviews  
Media Center  
Media Inquiries

### About Us

Milwaukee Story  
Careers  
Locations  
**Buy Now**  
Contact Us

Nothing but **HEAVY DUTY**™

Search Milwaukeeetool.com

NEW PRODUCTS &amp; OFFERS

TOOLS ▾

ACCESSORIES ▾

TEST &amp; MEASUREMENT ▾

HAND TOOLS


PARTS &amp; SERVICE ▾

BUY NOW

Home > ... > [M12™ 2-Tool Combo Kits](#) > M12 Cordless LITHIUM-ION 2-Tool Combo Kit

# M12 Cordless LITHIUM-ION 2-Tool Combo Kit 2494-22

PRINT

Be the first to [Write a Review](#)

The 2494-22 M12™ Cordless LITHIUM-ION 2-Tool Combo Kit includes the 3/8" Drill Driver and the 1/4" Hex Impact Driver (2450-20). The innovative M12™ cordless LITHIUM-ION system is designed to deliver the power and torque required for professional applications, in a size that reaches the tightest and toughest places. Powered by REDLITHIUM™, the M12™ cordless LITHIUM-ION system offers unmatched power, speed, and tool belt portability.

### Includes

- 2410-20 M12™ 3/8" Drill Driver
- 2450-20 M12™ 1/4" Hex Impact Driver
- (2) 48-11-2401 M12™ REDLITHIUM™ Batteries
- 48-59-2401 M12™ 30-Minute Charger
- Contractor Bag

FIND RETAILERS

### FEATURES

- M12™ 3/8" Drill Driver delivers best-in-class 275 in.-lbs. of peak torque, 0-400 / 0-1,500 RPM at just 2.6 lbs.
- M12™ 1/4" Hex Impact Driver delivers best-in-class 850 in.-lbs. of torque at only 2.3 lbs. and 0-2000 RPM for fast driving.

### SPECIFICATIONS

Voltage	12V
Battery	LITHIUM-ION
Bag/Case Type	Contractor Bag
Shipping Weight	9.0 lbs

### REVIEW SNAPSHOT® by PowerReviews

Not yet rated. Be the first to [Write a Review](#)

### RELATED ITEMS



M12™ RED LITHIUM™  
Battery



M12™ LITHIUM-ION  
AC/DC Wall and Vehicle  
Charger



M12™ Cordless  
LITHIUM-ION Multi-Tool -  
Bare Tool Only

MORE RELATED ITEMS

Sign Up for the  
Heavy Duty Club



SUBMIT ▶

### Products

New Products & Offers  
Tools  
Accessories  
Test & Measurement  
Milwaukee Gear  
Print Current Catalog

### Parts & Service

e-SERVICE Tool Repair  
Test & Measure Service  
Find a Service Center  
Download Manuals  
Parts Pricing  
Milwaukee Warranty  
Lightning Max Repair  
FAQ's

### News & Media

Press Releases  
MilwaukeeCain.com  
Product Reviews  
Media Center  
Media Inquiries

### About Us

Milwaukee Story  
Careers  
Locations  
**Buy Now**  
Contact Us